






Copyright FCI.



PLATING CONTACT AREA:	
DASH NR:	PERFORMANCE LEVEL
-1YY	TELCORDIA CO
-2YY	CUSTOMER SPECIAL
-3YY	CUSTOMER SPECIAL
-9YY	TELCORDIA CO
-2YYLF	CUSTOMER SPECIAL
-9YYLF	TELCORDIA CO
-1YYLF	TELCORDIA CO
-3YYLF	CUSTOMER SPECIAL

OBSELETE
OBSELETE
OBSELETE
OBSELETE
OBSELETE
OBSELETE
OBSELETE

PC BOARD VERSIONS		
PRODUCTNR:	PCB THICKNESS	DIM'A"
70231-X01LF	1.6	2.90
70231-X11LF	2.4	3.53



PRODUCT AFTER HOT RIVETTING.



RECOMMENDED HOLE PATTERN, COMPONENT SIDE.

- NOTES:
- 1 BODY MAT'L: LIQUID CRYSTAL POLYMER 30% GLASS FLAME RETARDANT ACC. UL 94-V0
 - 2 TERMINAL MATERIAL: PHOSPHOR BRONZE.
 - 3 INDICATED HOLES ARE UNPLATED.
 - 4 PRODUCT MARKING: PARTNUMBER & BATCH ID.
 - 5 THIS PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008
 - 6 THE HOUSING WILL WITHSTAND EXPOSURE TO 260DEGREE PEAK TEMPERATURE FOR 10 SECONDS IN A WAVE SOLDER APPLICATION.
 - 7 THE PRODUCT SPECIFICATION GS-12-453.

mat'l. code				tolerances unless otherwise specified			CUSTOMER COPY				www.fciconnect.com										
ltr	ecn no	dr	date	linear	0.X ±0.30			projection 	title RA FEMALE POWER STB 12MM VERSION												
G	V70769	DDB	1997-06-02		0.XX ±0.15																
H	V00578	LLA	2000-03-16		0.XXX ±0.05																
J	V00847	LLA	2000-05-30	angles	0° ±2'			 MM	product family				METRAL				code				
K	DG05-0107	CLU	2005-05-10	dr	R.TRLPPE	1990-09-18			scale 5:1	size		dwg no						sheet 1 of 2			
L	DG07-0458	CEN	2007-11-15	engr	BDUWKNEGT	1990-09-18				A2		70231									
M	N11-0131	AZH	2011-05-09	chr	VAN ZANTEN	1990-09-18															
N	ELX-N-004584	AZH	2011-07-20	appd	VAN ZANTEN	1990-09-18															
sheet index		revision		N																	
		sheet		1-2																	









Copyright FCI.

PLATING CONTACT AREA:	
DASH NR:	PERFORMANCE LEVEL
-1YY	TELCORDIA CO
-2YY	CUSTOMER SPECIAL
-3YY	CUSTOMER SPECIAL
-4YY	TELCORDIA CO
-5YYLF	CUSTOMER SPECIAL
-6YYLF	TELCORDIA CO
-7YYLF	TELCORDIA CO
-8YYLF	CUSTOMER SPECIAL
-9YYLF	TELCORDIA CO
-1YYLF	TELCORDIA CO
-3YYLF	CUSTOMER SPECIAL

OBSELETE
OBSELETE
OBSELETE
OBSELETE
OBSELETE
OBSELETE
OBSELETE

PC BOARD VERSIONS		
PRODUCTNR:	PCB THICKNESS	DIM"A"
70231-X02LF	1.6	2.90
70231-X12LF	2.4	3.53



- NOTES:
- 1 BODY MAT'L: LIQUID CRYSTAL POLYMER 30% GLASS FLAME RETARDANT ACC. UL 94-V0
 - 2 TERMINAL MATERIAL: PHOSPHOR BRONZE.
 - 3 INDICATED HOLES ARE UNPLATED.
 - 4 PRODUCT MARKING: PARTNUMBER & BATCH ID.
 - 5 SET BACK FOR PRESS BLOCK.
 - 6 TOP SURFACE OF PRESS BLOCK MAY EXTEND UP TO 0.4MM HIGHER THAN HOUSING. THIS MAY AFFECT THE TAIL LENGTH BEFORE APPLICATION TO A BOARD
 - 7 THIS PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008
 - 8 THE HOUSING WILL WITHSTAND EXPOSURE TO 260DEGREE PEAK TEMPERATURE FOR 10 SECONDS IN A WAVE SOLDER APPLICATION.
 - 9 THE PRODUCT SPECIFICATION GS-12-453.

mat'l. code				tolerances unless otherwise specified		CUSTOMER COPY		FCI			
ltr	ecn no	dr	date	linear	0.X ±0.30	projection	title	www.fciconnect.com			
N	ELX-N-004584	AZH	2011-07-20		0.XX ±0.15			RA FEMALE POWER STB 12MM VERSION			
					0.XXX ±0.05						
				angles	0° ±2'	MM	product family	METRAL			
				dr	R.TRLPPE			code			
				enrg	BOUWKNEGT			size			
				chr	VAN ZANTEN	scale	A2	dwg no			
				appd	VAN ZANTEN			70231			
sheet index	revision	N									
	sheet	1-2									

REV F - 2008-04-17