

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

**Part Number:** [1301040039](#)  
**Status:** **Active**  
**Overview:** [Stringlights](#)  
**Description:** Haztex Hazardous and Wet Location Stringlight 100W with 3 Lamps 12/3 SOOW  
13.72m (45.0') Length

**Documents:**

[Brochure \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

**Agency Certification**

CSA LR39801

**General**

Product Family Portable Lighting  
Series [130104](#)  
NEMA Configuration NEMA 5-15  
NEMA Rating NEMA 4X  
Outlet None  
Overview [Stringlights](#)  
Product Name Haztex  
Type String Lights  
UPC 78678834302

**Physical**

Cord Length - Primary 7.62m (25.0')  
Cord Length - Secondary N/A  
Depth N/A  
Duty Hazardous  
Guard Included Yes  
Guard Type Cast Aluminum  
Height N/A  
Length 13.72m (45.0')  
Material - Globe Tempered Glass  
Material - Guard Cast Aluminum  
Mounting Style Stringer  
Packaging Type Carton  
Socket Construction Rubber Molded

**Electrical**

Bulb Type Incandescent  
Cord Type - Primary 12/3 SOOW  
Lamp Type A21  
Lamp Wattage - Maximum 100W  
Lumens 1000  
On/Off Switch No  
Voltage (Fixture) - Maximum 120VAC 60 HZ

**Material Info**

Engineering Number 340310A



Series image - Reference only

**EU ELV**

**Not Reviewed**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

For more information, please visit [Contact US](#)

**China RoHS**

|                 |              |
|-----------------|--------------|
| China ROHS      | Not Reviewed |
| ELV             | Not Reviewed |
| RoHS Phthalates | Not Reviewed |

**Search Parts in this Series**

[130104](#) Series