

Precision ESD Safe Slotted/Phillips Drivers



273 Phillips Screwdriver, With Precision ESD Safe Dissipative

Handle. Blade high alloy chrome-vanadium-molybdenum steel. Hard chrome finished. Handle manufactured from impact resistant, dissipative material. ESD standard IEC 61340-5-1

Item									
No.	Size	mm	Inch	mm	Inch	mm	Inch	lbs.	pkg.
273 02	000	40	1.6	2.0	.08	120	4.7	.02	10
273 05	00	40	1.6	2.0	.08	120	4.7	.02	10
273 07	00	75	3.0	2.0	.08	155	6.1	.02	10
273 10	0	50	2.0	3.0	.12	145	5.7	.04	10
273 12	0	75	3.0	3.0	.12	170	6.7	.03	10
273 14	0	100	3.9	3.0	.12	195	7.6	.05	10
273 16	0	150	5.9	3.0	.12	245	9.6	.06	10
273 20	1	60	2.3	4.0	.16	170	6.7	.06	10
273 22	1	75	3.0	4.0	.16	155	6.1	.06	10
273 24	1	100	3.9	4.0	.16	210	8.2	.06	10
273 26	1	150	5.9	4.0	.16	260	10.2	.07	10

*Metric dimensions actual - Inch dimensions approximate



273 93 Set 7 Pcs. Extra Long Slotted/Phillips Precision ESD Safe

Dissipative Handle Blade CVM steel, hardened, hard chromed. Handle impact resistant, dissipative material. ESD standard IEC 61340-5-1

Item							
No.		mm	mm		Size	mm	lbs.
273 93	272 24	2.0	150	273 16	0	150	.48
	272 28	2.5	150	273 26	1	150	
	272 34	3.0	150				
	272 38	3.5	150				
	272 43	4.0	150				



273 99 Set 8 Pcs. Slotted & Phillips Precision ESD Safe

Dissipative Handle. Blade high alloy CVM steel, hardened, hard chromed. Handle manufactured from impact resistant, dissipative material. In storage pouch. ESD standard IEC 61340-5-1

Item							
No.		mm	mm		Size	mm	lbs.
273 99	272 15	1.5	40	273 02	000	40	.50
	272 20	2.0	40	273 05	00	40	
	272 25	2.5	50	273 10	0	50	
	272 30	3.0	50	273 20	1	60	



911 18 Rugged Polyester Canvas Storage Pouch

Holds 8 Precision Tools up to 170mm in length. Folding pouch.
Has security flaps and velcro closer.

Item			
No.	Size	lbs.	pkg.
911 18	14 1/2" W x 7 3/4" L	.13	1