




LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
GP	00		P2	REVISED PER ECO-07-008164	27JUL07	JDP	CWR



- 1 HOUSING FULLY LOADED WITH CONTACTS.
- 2 NUMBER ON CONTACT INDICATES WIRE RANGE.
- 3 CONTACT INSULATION RANGE: .060 MAXIMUM O.D.
- 4 CONTACTS PLATED .000030 GOLD ON MATING END FOR .100 MIN LENGTH. .000100-.000200 THICK BRIGHT TIN OR BRIGHT TIN-LEAD IN AREA SHOWN. .000050 THICK NICKEL UNDERPLATE ON ENTIRE CONTACT.
- 5 CONTACTS PLATED WITH GOLD FLASH ON MATING END FOR .100 MIN LENGTH. .000100-.000200 THICK BRIGHT TIN OR BRIGHT TIN-LEAD IN AREA SHOWN. .000030 THICK NICKEL UNDERPLATE ON ENTIRE CONTACT.
- 6 CONTACTS PLATED .000030 GOLD ON MATING END FOR .100 MIN LENGTH. .000100-.000200 THICK MATTE TIN IN AREA SHOWN. .000050 THICK NICKEL UNDERPLATE ON ENTIRE CONTACT.
- 7 CONTACTS PLATED WITH GOLD FLASH ON MATING END FOR .100 MIN LENGTH. .0001-.0002 THICK MATTE TIN PLATE IN AREA SHOWN. .000030 MIN NICKEL UNDERPLATE ON ENTIRE CONTACT.
- 8 HOUSING: BLACK THERMOPLASTIC 94V-0 RATED. CONTACTS: PHOSPHOR BRONZE.

SUPD BY 745209-3	OBSOLETE	7	2	#22-26	745209-8
		6	2	#22-26	745209-7
		5	3	#20-22	745209-6
			2	#22-26	745209-5
		4	1	#26-30	745209-4
			3	#20-22	745209-3
			2	#22-26	745209-2
		3	1	#26-30	745209-1
			2	#22-26	745209-0
		2	1	#26-30	745209-0
		1	1	#26-30	745209-0
		0	1	#26-30	745209-0

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN L. VARELA - 11-15-04	Tyco Electronics Corporation			
DIMENSIONS: INCHES		CHK J. GERACE 11-15-04	Harrisburg, PA 17105-3608			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD M. WALMSLEY 11-15-04	NAME			
0 PLC ± -		PRODUCT SPEC	RECEPTACLE ASSEMBLY, SIZE 3, 25 POSITION, AMPLITE			
1 PLC ± -		APPLICATION SPEC	SIZE CAGE CODE DRAWING NO RESTRICTED TO			
2 PLC ± -		114-40002	A2 00779 C=745209			
3 PLC ± .005		WEIGHT -	SCALE 4:1 SHEET 1 of 1 REV P2			
4 PLC ± -		CUSTOMER DRAWING				
ANGLES ± 2°						
FINISH						
SEE TABLE						