



main menue



- home
- test & measurement
- products
- skills
- download

online catalogue T&M

- clamp-type test probes
- crocodile clips
- test probes
- oscilloscope test probes
- measuring leads
- plugs
- sockets
 - 2 mm system
 - 2 mm safety system
 - 4 mm system
 - 4 mm safety system
- sets
- miscellaneous
- company
 - portrait
 - corporate association
 - location maps
 - fairs and exhibitions
 - jobs
 - imprint
 - terms and conditions

Home > sockets > sockets > SEB 2600 G M4

SEB 2600 G M4

datasheet for SEB 2600 G M4
article number: 972354101



[View Full-Size Image](#)



search online catalogue

Search

Messetermine

SPS/IPC/DRIVES
24. 11. 2015 - 26. 11. 2015

QR-Code



product description:	order number: 972 354-101
description:	Safety built-in socket, 4 mm diameter, touch-protected, M 4 thread and solder connection, gold-plated brass. For installation into switch panels and equipment chassis with wall thicknesses up to 6 mm. Installation hole: 12.2 mm diameter, Tightening torque: 50 Ncm Accessory: assembly tool MW SEB
typ:	SEB 2600 G M4 rot/red
system:	4mm safety system
order number:	972 354-101
color	
other color versions:	
technical data	
measurement category acc. to IEC 61010:	CAT III
type of contact:	4 mm socket (unsprung)
type of termination:	M4 thread, solder
rated voltage:	AC/DC 1000 V
rated current:	32 A
Please consider derating curve!	
contact resistance:	5 mOhm
mounting:	screw
material	
contact material:	brass
contact surface material:	gold
housing material:	PA
connecting nut material:	brass nickel - plated
environmental conditions:	
temperature range:	-40 °C to +80 °C
inflammable class:	
housing (basic material):	UL 94 V - 2
drawing	
	