

Product SKU: C1360.21.90

Product Description: Speaker Wire, UL Listed (Wires, Misc.) 120V max., No. of Conductors: 2, Gauge Size (AWG): 20, Conductor/Strands: 10/30, Jacket: Premium Grade PVC - Clear - 1000 Ft. Spool

Product Category: Electronics - Special Applications - Audio, Video, and Entertainment Cable - Speaker Wire - Clear



Product Construction:

- Conductor:
- 24 thru 12 AWG fully-annealed 1 bare, 1 tin stranded copper per ASTM B-174
- Insulation/Jacket:
- Premium grade PVC

Product Specification:

- No. of Conductors:
- 2
- Conductor Size (AWG):
- 20
- Conductor/Strands:
- 10/30
- Jacket Color:
- Clear
- Nominal Insulation Thickness (in):
- 0.020
- Nominal Insulation Thickness (mm):
- 0.51
- Nominal Outside Diameter (in):
- 0.085 x 0.160
- Nominal Outside Diameter (mm):
- 2.16 x 4.06
- Standard Packaging:
- 1000' Spool
- Standard Package Quantity:
- 2
- UPC #:
- 079407762385

Put-up:	• 1000
SCC-14:	• 50079407762388
Cube:	• 1330.89
Weight Per Unit of Measure:	• .01
ColorOption:	• Clear

Product Information:

Applications:	• Hi-fi and stereo speaker wire • Juke boxes • Lamps • Radios • Suggested voltage rating: 120 Volts • Not for in-wall use
Compliances:	• UL Wires Misc. (UL: 120V)
Packaging:	• 1000' (305 m) Spools • 500' (152 m) Spools • Other put-ups available- consult Customer Service

Technical Specifications

[Unit Conversion Factors](#)

[Cable Design Equations - Balanced Pair](#)

[Insulation and Jacket Properties](#)

[Temperature Conversion Chart](#)

[Decimal and Unit Conversion Factors](#)

[Cable Design Equations - Braid Shield](#)

[AWG Conductor Chart](#)

[Conduit Capacity Chart](#)

[Cable Design Equations - Coaxial Cable](#)

[Engineering Prefixes](#)

[Coax Connector Cross Reference](#)

[Glossary](#)



**CAROL
BRAND**