





HEAT SEALED



- 1.CABLE:NO UL,,28AWG(7/0.127),TINNED AND STRANDED COPPER WIRE  
INSULATOR:PVC,ID:0.85mm ,CABLING:7C+DRAIN WIRE  
SHIELD:AL/MY COVERAGE  
JACKET:PVC,COMPLIANCE ROHS,COLOR:BEIGE,D.D:5mm
- 2.2PCS CONNECTOR:D-SUB 9 WAYS FEMALE SOLDER TYPE CONNECTOR  
INSULATOR:P.B.T.+GLASS FIBER,COLOR:BLUE  
CONTACT:COPPER ALLOY,GOLD FLASH OVER NICKEL PLATED  
SHELL:NICKEL PLATED.  
CONNECTOR COMPLIANCE ROHS
- 3.HOOD:PVC MOLDED TYPE WITH FOIL SHIELDED ON INNER  
ON INNER MOLD AND INJECTION OUTER MOLD WITH  
THUMB SCREW#4-40 UNC  
COLOR:BEIGE,COMPLIANCE ROHS
- 4.Fulfil ROHS Guideline
- 5.ELECTRONIC TEST  
100% OPEN SHORT+MISS WIRE TEST

#### DRAWING

| DB9PIN JACK(J1) | WIRE       | DB9PIN JACK(J2) |
|-----------------|------------|-----------------|
| 2               |            | 3               |
| 3               |            | 2               |
| 4               |            | 6               |
| 5               |            | 5               |
| 6               |            | 4               |
| 7               |            | 8               |
| 8               |            | 7               |
| SHELL           | DRAIN WIRE | SHELL           |

|                                                      |         |          |   |                        |
|------------------------------------------------------|---------|----------|---|------------------------|
| PART NO                                              | 4070-XX | SHEET NO | 1 | THIRD ANGLE PROJECTION |
| TITLE: DB9 PIN FEMALE TO DB9 PIN MALE<br>BEIGE COLOR |         |          |   | SCALE N.T.S            |
|                                                      |         |          |   | SIZE A4                |
|                                                      |         |          |   | UNIT                   |
| DWN NO                                               |         |          |   | APPROVED BY & DATE     |
|                                                      |         |          |   | mm INCH                |