


REV. DE



PT-01--24-01--22



SEE NOTE 15

PACKAGING VIEW LEAD STYLE SD -22

TABLE 2: SOCKET SPECIFICATION

LEAD STYLE	SERIES					
	-1	F _I G	SL	SDL	'B'	PIN LENGTH
	SS HSS SD					NO OF FINGER CLIPS
-1A	SC-1W1-XX-2 (SL & SDL N/R)	1	N/A	.038 [.97]	.553 [14.05]	4
-1B	SC-1W1-XX-1 (SL & SDL N/R)	1	N/A	.038 [.97]	.703 [17.86]	4
-1C	SC-1W1-XX-3 (SL & SDL N/R)	1	N/A	.038 [.97]	.453 [11.51]	4
-2	SC-1P1-XX (SL & SDL N/R)	1	N/A	.038 [.97]	.300 [7.62]	4
-3	SC-1S1-XX (SL & SDL N/R)	1	N/A	.038 [.97]	.203 [5.16]	4
-5	SC-2P1-XX (SS & HSS ONLY)	3	N/A	.038 [.97]	.703 [17.86]	4
-5A	SC-2P1-XX (SL & SDL N/R)	1	N/A	N/A	.703 [17.86]	4
-7	SC-1P3-XX (SL & SDL N/R)	1	N/A	N/A	.600 [15.24]	4
-8	SC-2P3-XX (SL & SDL N/R)	1	N/A	N/A	.542 [13.77]	4
-10	N/A	2	SC-3P1-XX	.038 [.97]	.230 [5.84]	4
-11	N/A	2	SC-4P1-XX	.028 [.71]	.240 [6.10]	4
-12	N/A	2	SC-5P1-XX	.028 [.71]	.190 [4.83]	4
-13	SC-2P7-XX (SS ONLY)	2	N/A	.039 [.99]	.310 [7.87]	4
-14	SC-1M1-XX (N/A)	1	N/A	N/A	.205 [5.21]	4
-15	SC-1M2-XX (N/A)	1	N/A	.028 [.71]	.167 [4.24]	4
-17	SC-7P1-XX (N/A)	1	N/A	N/A	.443 [11.25]	4
-18	SC-6P1-XX (SL & SDL N/R)	1	N/A	.038 [.97]	.353 [8.97]	4
-19	N/A	2	SC-8P1-XX	.016 [.41]	.165 [4.19]	4
-20	SC-9P1-XX (N/A)	2	N/A	.028 [.71]	.190 [4.83]	4
-21A	EZ-1W1-XX-2 (SL & SDL N/R)	1	N/A	N/A	.553 [14.05]	6
-21B	EZ-1W1-XX-1 (SL & SDL N/R)	1	N/A	N/A	.703 [17.86]	6
-21C	EZ-1W1-XX-3 (SL & SDL N/R)	1	N/A	N/A	.453 [11.51]	6
-22	EZ-1P1-XX (SL & SDL N/R)	1	N/A	.038 [.96]	.300 [7.62]	6
-23	EZ-1S1-XX (SL & SDL N/R)	1	N/A	N/A	.203 [5.16]	6
-28	EZ-2P3-XX (SL & SDL N/R)	1	N/A	N/A	.542 [13.77]	6
-29	EZ-2P2-XX (SL & SDL N/R)	1	N/A	N/A	.703 [17.86]	6
-30	EZ-3P1-XX (SL & SDL ONLY)	2	N/A	.038 [.97]	.230 [5.84]	6
-31	EZ-4P1-XX (SL & SDL ONLY)	2	N/A	.028 [.71]	.240 [6.10]	6
-32	EZ-5P1-XX (SL & SDL ONLY)	2	N/A	.028 [.71]	.190 [4.83]	6
-34	EZ-1M1-XX (N/A)	1	N/A	N/A	.205 [5.21]	6
-37	EZ-7P1-XX (N/A)	1	N/A	N/A	.443 [11.25]	6
-38	EZ-6P1-XX (SL & SDL N/R)	1	N/A	.038 [.97]	.353 [8.97]	6
-39	EZ-8P1-XX (SL & SDL ONLY)	2	N/A	.016 [.41]	.165 [4.19]	6
-40	EZ-9P1-XX (N/A)	2	N/A	.028 [.71]	.190 [4.83]	6
-41	SC-6P1-XX (N/A)	9	N/A	.005 [.13]	.353 [8.97]	4

SEE NOTE 13
SEE NOTE 14NOT AVAILABLE
IN -TT PLATING

PROPRIETARY NOTE
THIS DOCUMENT CONTAINS INFORMATION
CONFIDENTIAL AND PROPRIETARY TO
SANTER INC. AND SHALL NOT BE
REPRODUCED OR TRANSMITTED IN
ANY FORM OR BY ANY MEANS
WITHOUT THE WRITTEN CONSENT OF SANTER INC.


DELETED
FIGURE 7

FIGURE 9

DIMENSIONS ARE IN INCHES
UNLESS OTHERWISE NOTED
TOLERANCES ARE:
ONE PLACE DECIMALS ±.1[2.5] THREE PLACE DECIMALS ±.005 [.13]
TWO PLACE DECIMALS ±.01[.25] FOUR PLACE DECIMALS ±.002[.05]
ANGLES
± 2°






TITLE: ASSEMBLY
SOCKET STRIPDWG NO: XSX-1XX-XX-XX-X-X
SHEET 2 OF 2FIGURE 1
(FOR -N OPTION, SEE NOTE 9 SHT.1)FIGURE 2
(SEE NOTE 9 SHT.1)

FIGURE 3

OPTION -L: REPLACE BOTH END
POS. (BOTH ROWS) AS SHOWN
FIGURE 4
(SEE NOTE 9 SHT.1)FIGURE 8
OPTION -N
(FOR -SD STYLE, SEE NOTE 9 SHT.1)
(FOR HSS AND SS STYLES, SEE NOTES 3 & 4)
'B' DIMENSION FOR OPTION -N = NON FLUSHMFG/ASST
XSX-10X-XX-XX-X-X-MKT-SHT2

santec

520 PARK EAST BLVD. NEW ALBANY, INDIANA 47151-1147
PHONE (812) 944-6733 P.O. BOX 1147
CODE 55322

MADE BY: MARK CHILTON 11-28-88

XSX-1XX-XX-XX-X-X
SHEET 2 OF 2