



Sample photo

Order symbol: AL 061505
Product nbr: 7011100
Description: Enclosure
Remarks: Aluminium

EAN: 6418074004109
El. number:
 Finland 3423607
 Denmark 8212004634
 Italy 7321025
 Sweden 2536309

Including: Base with screws for mounting plate/DIN-rail, cover with PUR gasket and stainless steel cover screws.

Dimensions:		L	W	H	Rating:
mm:		66	152	46	Ingress Protection (EN 60529): IP 66/67 Impact Resistance (EN 50102): IK 08 NEMA Class: NEMA 1, 4, 4X, 12, 13
inch:		2.6	6	1.8	
Materials:					Certificates: Underwriters Laboratories UL Canada
Material:		AL			
Base colour:		RAL 7001			
Cover colour:		RAL 7001			
Cover screws material:		Stainless steel			
Gasket material:		Polyurethane			
Temperatures:					
Short term:		-50 ... 140 °C			
Continuous:		-50 ... 80 °C			
Short term:		-60 ... 285 °F			
Continuous:		-60 ... 175 °F			
Accessories:					
ARM 0615		DIN-15 Mounting rail			
ARH 16		DIN-35 Mounting rail			
MR 75003		Tapite screw			
MRS 28540		Wall fastening lug set			

