



RBK HSS JOBBER DRILL 15/64"

DIN 338/BS 328

Flute Geometry Standard Helix, right hand spiral

Surface finish Blue

Point geometry Up to 2.9mm - 118° 3.0mm and above - 135° split point

Angle, drill point	118 °
Associated Products	023051
Diameter, drill bit Imperial	15/64 "
Diameter, External	15/64 "
Length, effective	57 mm
Length, overall	93 mm
Material	HSS
RoHS Compliant	NA