


Type	Size	Description	Part No.
Incandescent	T5 (T-1½)	Sub-Miniature Screw lamp (LES)	(see table)



Drawing not to scale
All dimensions in mm

PHOTOMETRY DATA

Farnell Part No.	SLI P/N	Lamp Rating	Test Volts	Current (mA)			Light Output (Lm)			Fil Shape	Life (Hrs)
				Min	Nom	Max	Min	Nom	Max		
328133	673	6V 0.36W	6.0	50	55	60	0.8	1.0	1.2	C-2R	10000
328145	674	6.5V 1W	6.5	135	150	165	3.0	4.0	5.0	C-2R	2500
328157	679	12V 1W	12	75	83	91	1.8	2.4	3.0	C-2V	10000
328169	280	12V 1.5W	12	114	127	140	4.0	5.3	6.6	C-2F	5000
328170	690	14V 0.56W	14	33	37	41	1.2	1.6	2.0	C-2F	5000
328182	5682	14V 0.7W	14	45	50	55	2.2	3.0	3.8	C-2F	1000
328194	687	24V 1W	24	36	40	44	2.2	3.0	3.8	C-2F	10000
265342	399	28V 1.12W	28	36	40	44	2.8	3.8	4.8	C-2F	7000
328200	688	28V 1.12W	28	36	40	44	3.4	4.5	5.6	C-2F	4000

NOTES:

- 1) E5 nickel-plated screw cap in accordance with IEC 61-1, (BS EN 60061-1), sheet 7004-25-x.
- 2) Metal base to be durably marked with rating and trademark.