

THIS DRAWING IS UNPUBLISHED.	RELEASED FOR PUBLICATION	- , - .
© COPYRIGHT - By - ALL RIGHTS RESERVED.		

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
H	—		A	INITIAL RELEASE	15NOV2013	YC	BvH
			A1	ECR-14-011671	16AUG2014	GSK	BvH

NOTES:

Tolerances cable lengths:

0m to 0.5m	+30mm
------------	-------

0.5m to 1.0m	+50mm
--------------	-------

1.0m to 3.0m	+100mm
--------------	--------


< 3.0m	+1.5%
--------	-------



TECHNICAL DATA	
Operating voltage	max. 30 V AC/DC
Operating current per contact	max. 2 A
Locking of ports	Screw thread M12 x 1 mm (recommended torque 0.6 Nm) self-securing
Protection	IP65 and IP67 when plugged and screwed down (EN 60529)

PUR CABLE	
No./diameter of wires	8 x 0.25 mm ²
Wire isolation	PP (br, wh, bl, bk, gr, pk, vi, or)
C-track properties	2 million
Jacket	PUR (UL/CSA)
Outer diameter	approx. 6.0 mm
Bend radius (moving)	10 x outer diameter
Temperature range (fixed)	−40...+80 °C
Temperature range (mobile)	−20...+80 °C

8 pos	10mtr	PUR	Grey	2273040-4	8x24AWG PUR 10.0m	4
	5mtr			2273040-3	8x24AWG PUR 5.0m	3
	3mtr			2273040-2	8x24AWG PUR 3.0m	2
	1.5mtr			2273040-1	8x24AWG PUR 1.5m	1
	LENGTH”L”	MATERIAL	JACKET COLOR	TE PN	DESCRIPTION	ITEM

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN YATHISH.C 15NOV2013		 TE Connectivity	
		CHK B.VELDHOVEN 15NOV2013			
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± -		NAME	
				M12 X 1.0 STRAIGHT PLUG PIGT A	
MATERIAL -		FINISH -		SIZE A3	
		WEIGHT -		CAGE CODE 00779	
		CUSTOMER DRAWING		DRAWING NO C-2273040	
				RESTRICTED TO -	
				SCALE NTS	
				SHEET 1 OF 1	
				REV A1	