


REV.	DATE	DESCRIPTION
NC	10/18/D2	INITIAL RELEASE
A	05/01/04	UPDATE DRAWING FORMAT



Amphenol Connex									
PART DESCRIPTION									
BNC MALE TO FEMALE R/A ADAPTOR									
PART NO. 112454									
DWG. NO. 112454.DWG									
REV. A SIZE A SCALE NA									
APPROVALS		DATE							
DRAWN G.R.S.		05/01/04							
CHECKED									
ISSUED									
SHEET 1 OF 1									
CAD FILE C:/112/112454.DWG									
DO NOT SCALE DRAWING									
UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN MILLIMETERS, DECIMALS IN () ARE IN INCHES AND FOR DISTANCE REFERENCE ONLY.									
UNLESS OTHERWISE SPECIFIED, TOLERANCES FOR MILLIMETERS ARE: 0.5 - 8mm ± 0.20mm 8 - 30mm ± 0.40mm 30 - 120mm ± 0.50mm									
UNLESS OTHERWISE SPECIFIED, TOLERANCES FOR INCHES ARE: .020 - .315 ± 0.007" .315 - 1.180 ± 0.015" 1.180 - 4.724 ± 0.020"									
QTY		FINISH		MATERIAL		DESCRIPTION			
1		NICKEL		BRASS		BODY			
2		NATURAL		DELTRIN		INSULATOR			
1		GOLD		PHOS. BRONZE		CONTACT PIN			
1		GOLD		BRASS		CONTACT PIN			
		</							