

FEATURES:

- Diffused Lens
- Directional Efficiency
- Low Profile
- Long Life
- Instant On
- Mercury Free
- Lead Free
- No UV

The Bayfront series features a sturdy aluminum housing for greater durability and a diffused lens to maximize output uniformity.

SPECIFICATIONS

Color Temperature	Lumen Output	Efficacy (lm/W)	Color Rendering Index (CRI)
Cool (C) - 6500K	180	45	80
Neutral (N) - 4500K	170	43	75
Warm (W) - 3000K	160	40	70
Soft (S) - 2700K	160	40	66


Rated Life:	50,000 hours
Beam Angle:	120°
Power Consumption:	4 Watts
Operating Temperature:	0° C ~+ 40° C
Voltage Input:	24VDC, Constant Voltage
Controls:	See Accessory SW-1001
Housing:	Extruded Aluminum, Black Polycarbonate Lens, Frosted
Weight (g):	136
Dimensions:	W .63" (15.69mm) H .89" (22.6mm) L 12.2" (308.9mm) ** **not including mounts

Compliance:



Restriction of Hazardous Substances Directive (RoHS) implements EU Directive 2002 / 95 which bans placing electrical and hazardous equipment that contains more than agreed levels of hazardous substances on the EU market. For a list of these substances, visit www.rohs.gov.uk.

DIMENSIONS



BAYFRONT SERIES

B7100 STANDARD (S)

ORDERING INFORMATION

Choose the option that best suits your needs and write in corresponding code on the appropriate line to form product code.

Model	Color	Type	Example
B7100	C - 6500K N - 4500K W - 3000K S - 2700K	S-Standard	B7100-C-S

All luminaires are easily customizable. Please contact us to inquire about customizing a luminaires to fill your needs.

Order power accessories as separate catalog numbers from the Accessories section below. (Note: 2 mounting screws and double sided tape included for mounting of Standard luminaires.)

ACCESSORIES

- Universal Regulated Quick Connect Power Supply (North American Plug)
- Universal Regulated Quick Connect Power Supply (Euro Plug)
- In-line On/Off Switch

- Califia Lighting Part #WA-UL-001
- Califia Lighting Part #WA-VDE-001
- Califia Lighting Part #SW-1001

PHOTOMETRY CHARACTERISTICS

