


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

Material	High Conductivity Seamless Copper Tube
Plating	Electro-Tin
Wire Size & Type	Stranded Copper Flex Cable; 2 AWG (150/24) Diesel Locomotive
Wire Strip Length	1-7/16 in.
Stud Size	1/2 in.
UL Listed Wire Connector	Yes, for applications up to 35kv. Consult cable manufacturer for voltage stress relief instructions with applications greater than 2000 volts.
UL Temperature Rating	90° C
C.S.A Certified Wire Connector	Yes
Panduit Color Code on Barrel	BROWN
Panduit Die Index No. on Barrel	P33
Alternate Industry Die Index No. () on Barrel	(10)



LISTED Wire Connector



						PANDUIT CORP. TINLEY PARK, ILLINOIS	
						LCCF2-12F-E	
01	11/03	DRL	DRL	TONGUE WIDTH WAS .79		11257	Copper Lug - Two-Hole, Flared Barrel, 90° Angle Tongue
REV	DATE	BY	CHK	DESCRIPTION		ECN	SCALE N/A
						DRAWING NO / CAD FILE LCCF2-12F-CUST	