

Hot Air Stations

100 W Hot Air Stations



Hot air nozzles: see page 336–141
Spare parts: see www.weller.eu

Order No.	Model	Description
005 33 756 99	WMD 1A	Desoldering station multi digital 310 W, 230 V, with internal pump • 3 channel • Hot air pencil • Digitally controlled electronic for soldering, desoldering and hot air tools up to 150 W • Temperature range 50°C–450°C (HAP 1+ WSP 150: 550°C) • Air volume hot air 1–10 l/min • Max. vacuum -0,7 bar • Temperature, vacuum and air volume control via buttons • 3-position digital display • Protection class 1 • Antistatic housing • Equipotential bonding (normal state hard grounded) • Automatic tool recognition • Dimensions: 240 x 270 x 150 mm (L x W x H)
consists of:		
005 33 026 99	WMD 3	Power unit 230 V
005 27 115 99	HAP 1	Hot air pencil 100 W/24 V with hot air nozzle round R 06 Ø 3,0 mm
005 15 027 99	KH 27	Safety rest
005 87 278 21	R 04	Hot air nozzle round Ø 1,2 mm
005 87 488 61		Tool for solder-pointed nozzle changes
Accessory:		
005 87 388 50		Adapter for foot switch
005 13 120 99		Foot switch 1-step



Hot air nozzles: see page 136 –141
Spare parts: see www.weller.eu

Order No.	Model	Description
005 32 666 99	WAD 101	Hot air station digital 105 W, 230 V, compressed air or inert gas operated • 1 channel • Digitally controlled electronic for soldering and hot air tools up to 100 W • Inlet pressure 400 KPA (58 psi) oil-free, dry compressed air or inert gas • Temperature range 50°C–550°C (HAP 1) • Temperature control via buttons • Air volume control via regulator • 3-position digital display • Calibration box WCB 2 (see page 174) may be connected for CALIBRATION, LOCK OUT or OFFSET function • Protection class 1 • Antistatic housing • Equipotential bonding (normal state hard grounded) • Automatic tool recognition • Dimensions: 166 x 134 x 101 mm (L x W x H) • For use with external compressed air
consists of:		
005 32 686 99	PU WAD101	Power unit 230 V
005 27 115 99	HAP 1	Hot air pencil 100 W/24 V with hot air nozzle round R 06 Ø 3,0 mm
005 15 027 99	KH 27	Safety rest
005 87 278 21	R 04	Hot air nozzle round Ø 1,2 mm
Accessory:		
005 87 388 50		Adapter for foot switch
005 13 120 99		Foot switch 1-step