

Defence Standard Part4

Screened Type C

pro-POWER

RoHS
Compliant



Construction:

Conductor	Tinned Copper
Construction	0.055mm ² (7/0.1mm)
Insulation	Type 2 PVC compound to BS 7655-3.2
Screen	0.1mm tinned annealed copper braid (91% coverage)
Sheath	Type 6 PVC compound to BS 7655-4-2
Sheath Colour	Black or Grey

Standards / Conformances:

Def Stan 61-12 (Part 4), where applicable

Electrical Characteristics:

Rated Voltage (V)	: 250V AC RMS
Max. Conductor DC Resistance at 20°C (Ω/Km)	: 384
Min. Insulation Resistance of one core at 20°C (MΩ/Km)	: 140
Operating Temperature (°C)	: 70

Physical Characteristics:

Cores	Insulation Diameter (mm)		Nominal Overall Diameter (mm)	
	Min.	Max.	Min.	Max.
2	0.65	0.75	2.5	3.0
3	0.65	0.75	2.7	3.2
4	0.65	0.75	2.9	3.4
6	0.65	0.75	3.3	3.8
9	0.65	0.75	3.9	4.4
12	0.65	0.75	4.1	4.6
15	0.65	0.75	4.9	5.4
18	0.65	0.75		
25	0.65	0.75	6.0	6.6
36	0.65	0.75	6.6	7.2
50	0.65	0.75	7.7	8.3

Defence Standard Part4

Screened Type C

pro-POWER

Core Colours:

No. of Cores	Identification Colours
2 3 4 6 9 12 15 18 25 36	1- red, 2-blue, 3- green, 4- yellow, 5- white, 6- black, 7- brown, 8- violet, 9- orange, 10- pink, 11- turquoise, 12- grey, 13- red/blue, 14- green/red, 15- yellow/red, 16- white/red, 17- red/black, 18- red/brown, 19- yellow/blue, 20- white/blue, 21- blue/black, 22- orange/blue, 23- green/blue, 24- grey/blue, 25- yellow/green, 26- white/green, 27- green/black, 28- orange/green, 29- grey/green, 30- yellow/brown, 31- white/brown, 32- brown/black, 33- grey/brown, 34- yellow/violet, 35- violet/black, 36- white/violet
50	Centre: 1 Red, 2 Blue, 3 White. First layer: 4 Red, 5 Blue, (6, 7, 8, 9, 10, 11, 12) White. Second layer: 13 Red, 14 Blue, (15, 16, 17, 18, 19, 20, 21, 22, 23, 24, 25, 26, 27, 28) White. Outer layer: 29 Red, 30 Blue, (31, 32, 33, 34, 35, 36, 37, 38, 39, 40, 41, 42, 43, 44, 45, 46, 47, 48, 49, 50) White.

Part Number Table

Description	Part Number
Cable, Scrn, 4Core, 7/0.1mm, 25m	860173 25M
Cable, Scrn, 4Core, 7/0.1mm, 100m	860173 100M
Cable, Scrn, 6Core, 7/0.1mm, 25m	860180 25M
Cable, Scrn, 6Core, 7/0.1mm, 100m	860180 100M
Cable, Scrn, 9Core, 7/0.1mm, 25m	860184 25M
Cable, Scrn, 9Core, 7/0.1mm, 100m	860184 100M
Cable, Scrn, 15Core, 7/0.1mm, 25m	860183-25M.
Cable, Scrn, 15Core, 7/0.1mm, 100m	860183-100M
Cable, Scrn, 25Core, 7/0.1mm, 25m	860128-25M

Important Notice : This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. pro-POWER is the registered trademark of the Group. © Premier Farnell plc 2012.