This document was generated on 10/13/2014

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: 98268-0188

Status: Active

Overview: Premo-Flex™ FFC and Etched Polyimide Jumpers

Description: 1.25mm Pitch Premo-Flex™ FFC Jumper, Opposite Side Contacts (Type D), 12 Circuits, 0.305m Cable Length, 0.22mm Cable Thickness, Tin(Sn) Plating

Series image - Reference only

Documents:

Drawing (PDF)
Product Specification PS-98268-001 (PDF)
Packaging Specification PK-98268-001 (PDF)
RoHS Certificate of Compliance (PDF)

General

Product Family	Cable
Series	98268
Comments	Contacts on opposite sides, Type D
Crimp Quality Equipment	Yes
Overview	Premo-Flex™ FFC and Etched Polyimide Jumpers
Product Name	Premo-Flex™FFC Jumper
UPC	756054776391

Physical

Cable Length	0.305m
Circuits (Loaded)	12
Net Weight	3.122/g
Packaging Type	Bag
Pitch - Termination Interface	1.25mm
Temperature Range - Operating	-40°C to +105°C
Wire Size AWG	N/A
Wire/Cable Type	Flat Flex Cable

Electrical

Current - Maximum per Contact	1.4A
Voltage - Maximum	60V AC

Material Info

Reference - Drawing Numbers

Packaging Specification	PK-98268-001
Product Specification	PS-98268-001
Sales Drawing	SD-98268-001

EU RoHS
ELV and RoHS Compliant
REACH SVHC
Not Reviewed
Low-Halogen Status
Not Reviewed

China RoHS

Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, click here

Please visit the Contact Us section for any non-product compliance questions.

Search Parts in this Series
98268Series

Use With
Molex FFC – FPC connector.
Be sure to match like plating

This document was generated on 10/13/2014

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION