

Earth terminals

Screw connection system



Insulating terminal housing PA 6.6 V2
Rail mount on TS 15 / TS 32 / TS 35

Connection diagram

Connection type

Dimension (L x W x H)

with TS 15 mm

with TS 32mm

with TS 35 x 7,5mm

Type

Type

Cat. no./Qty. p. pck.

Rating

Rated voltage V

Rated current A

Rated conductor cross-section mm²/ AWG

Rated surge voltage kv/Contamination degree

Gauge plug acc. to EN 60 947-1 / Flammability class UL 94

For certifications and approvals

Conductor data

Single wire (solid)/Stranded (flexible) mm²

Flexible/Flexible (with ADH acc. to DIN 46 228/1) mm²

Contact wire range mm²

Insulation stripping length mm

Features

Number of cross connection channels

Test pick-off feature

Accessories


End plate AP

Cat. no./Qty. p. pck. green


Screw driver

Cat. no./Qty. p. pck.

SL 4/15



M 3



Earth terminal
2 connectors

Screw connection technology

32 x 7 x 34

SL 4/15
1064.2/100

IEC UL CSA

4 | 22-10

8 | 3

A3 | V2

see page 302

0,2-4 | -

0,2-4 | -


0,2-4

9

SLN 2,5/32



M 2,5



Earth terminal
2 connectors

Screw connection technology

40 x 6 x 43,7

SLN 2,5/32
1057.2/100

IEC UL CSA

2,5 | 22-12

8 | 3

A3 | V2

see page 302

0,2-4 | -

0,2-4 | 0,2-2,5


0,2-4

10

SLN 2,5/35



M 2,5



Earth terminal
2 connectors

Screw connection technology

52 x 6 x 38,9

SLN 2,5/35
1058.2/100

IEC UL CSA

2,5 | 22-12

8 | 3

A3 | V2

see page 302


0,2-4 | -

0,2-4 | 0,2-2,5


0,2-4

10

SL 2,5/35 ZR



M 3



Earth terminal
3 connectors

Screw connection technology

62 x 6 x 47

SL 2,5/35 ZR
1060.2/100

IEC UL CSA

2,5 | 22-12

6 | 3

A3 | V2

see page 302

0,2-4 | -

0,2-4 | 0,2-2,5

0,2-4

9

AP 2,5 R
2574.1/20

SDB 0,5 x 3,0

1085.0/1

Further accessories

Further accessories like marking systems, test adapters, covers, end brackets etc. you can find on the pages for accessories specified below!

Page 126

Page 126

Page 126

Page 126

81

[illegible]