

SUMMARY

Wires

Low	67
High	0
Coax	0
Triax	0
Quad	0
Fiber	0
Fluidic	0



Image is for illustrative purpose only

Download

[Request a quote](#)

[Catalog](#)

Series	1R
Termination type	Female crimp
IP rating	50
Cable Ø	0.00 - 0.00 mm
Matching parts	FGG.1R.367.GLC92
Status	active
Alternative part	

TECHNICAL DETAILS

Mechanics

Shell Style/Model	EGG*: Fixed receptacle, key (G) or key (A)
Keying	3 keys (alpha=50,beta=30, plug: male contacts, receptacle: female contacts)
Housing Material	Crastin® PBT (Polybutylene terephthalate), gray
Cable Fixing	∅ 0 - 0 mm
Variant	

Performance

Configuration	1R.367 : 67 low voltage
Insulator	L: PEEK (UL 94 / V-0/3.2, depends on material thickness)
Rated Current	0.5 Amps


Specifications

Contact Type: Crimp
Test voltage (kV rms) Contact-contact: 0.6

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

DRAWINGS

Draws



Dimensions

	A	B	C	E	G	L
mm.	24.5	10.5	34.5	3.2	2.2	31.5
in.	0,96	0,41	1,36	0,13	0,09	1,24

RECOMMENDED BY LEMO

Tools

Crimp Tool: DPC.91.701.V
Positionner: DCE.91.051.BVM
Extractor: DCF.91.050.2LT

Cables

LEMO products and services are provided “as is”. LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.