

PART
NAME

GRABBER (STYLE D)

PART
No.


HH-3463 & HH-3464

MATERIAL: ABS THERMOPLASTIC, UL94V-0
FLAMMABILITY RATING (UL FILE #E121562),
SUGGESTED SERVICE TEMPERATURE -20° C
TO +70° C

FINISH: BLACK TEXTURED

FOUR (4) #4 x 0.500" LG. SCREWS (BLACK)
SUPPLIED FOR ASSEMBLING COVER TO BODY

NOTE: ALL DIMENSIONS HAVE ± 0.010
TOLERANCE UNLESS OTHERWISE
SPECIFIED



NOTES:

- 1.) PC BOARD CAN BE HELD IN PLACE BY BEING SANDWICHED BETWEEN TOP & BOTTOM CASE (0.063 NOM. BOARD THICKNESS)

PART NO.

HH-3463 .030 DEEP RECESSED COVER

HH-3464 FLUSH TEXTURED COVER

REV. 5-09-00