

Plastic Tip Tweezers

The largest and the most precise plastic tweezers range all over the world. 20 years of experience in high engineering plastic materials. Choose the right tweezers with the right material for your success in your application. Technical data are available on page 42 or on www.ideal-tek.com for more information and chemical data-charts. For A, B, C dimensions refer to scheme on page 31.



A 5" 130mm - B 0.04" 1.0mm - C 0.08" 2.0mm

00CF.SA
00CP.SA
00DG.SA
00DL.SA
00LC.SA
00LR.SA
00SV.SA



A 5" 130mm - B 0.07" 1.8mm - C 0.04" 1.0mm

2ABCF.SA
2ABCP.SA
2ABDG.SA
2ABDL.SA
2ABLC.SA
2ABLR.SA
2ABSV.SA



A 5" 130mm - B 0.07" 1.8mm - C 0.04" 1.0mm

2ACF.SA
2ACP.SA
2ADG.SA
2ADL.SA
2ALC.SA
2ALR.SA
2ASV.SA



A 5" 130mm - B 0.03" 0.8mm - C 0.04" 1.0mm

2CF.SA
2CP.SA
2DG.SA
2DL.SA
2LC.SA
2LR.SA
2SV.SA



A 4 1/4" 110mm - B 0.03" 0.8mm - C 0.05" 1.3mm

3CCF.SA
3CCP.SA
3CDG.SA
3CDL.SA
3CLC.SA
3CLR.SA
3CSV.SA



A 5" 130mm - B 0.03" 0.8mm - C 0.05" 1.3mm

3CF.SA
3CP.SA
3DG.SA
3DL.SA
3LC.SA
3LR.SA
3SV.SA



A 5" 130mm - B 0.02" 0.5mm - C 0.025" 0.6mm

5CF.SA
5CP.SA
5DG.SA
5DL.SA
5LC.SA
5LR.SA
5SV.SA



A 5" 130mm - B 0.02" 0.5mm - C 0.025" 0.6mm

5XCF.SA
5XCP.SA
5XDG.SA
5XDL.SA
5XLC.SA
5XLR.SA
5XSV.SA



A 5" 130mm - B 0.025" 0.6mm - C 0.025" 0.6mm

7CF.SA
7CP.SA
7DG.SA
7DL.SA
7LC.SA
7LR.SA
7SV.SA




A 5" 130mm - B 0.4" 10mm - C 0.07" 1.8mm

248CF.SA
248DL.SA
248LR.SA



A 5" 130mm - B 0.09" 2.2mm - C 0.09" 2.2mm

249CF.SA
249CP.SA
249DG.SA
249DL.SA
249LC.SA
249LR.SA
249SV.SA



A 5" 130mm - B 0.4" 10mm - C 0.07" 1.8mm

250CF.SA
250DL.SA



A 5" 130mm - B 0.025" 0.6mm - C 0.04" 1.0mm

259CF.SA
259CP.SA
259DG.SA
259DL.SA
259LC.SA
259LR.SA
259SV.SA





A 5" 130mm - B 0.12" 3.0mm - C 0.07" 1.8mm

269CF.SA
269CP.SA
269DG.SA
269DL.SA
269LC.SA
269LR.SA
269SV.SA

Plastic Replaceable Tip Tweezers

The largest and the most precise plastic tweezers range all over the world. 20 years of experience in high engineering plastic materials. Choose the right tweezers with the right material for your success in your application. Technical data are available on page 42 or on www.ideal-tek.com for more information and chemical data charts. Replaceable kits come with 2 tips and 3 screws. The easiest and most precise replacement system available into the tweezers market.



A 5" 130mm - B 0.04" 1.0mm - C 0.08" 2.0mm

000CFR.SA
000CPR.SA
000DGR.SA
000DLR.SA
000LCR.SA
000LRR.SA
000SVR.SA



A 5" 130mm - B 0.07" 1.8mm - C 0.04" 1.0mm

2ABCFR.SA
2ABCPR.SA
2ABDGR.SA
2ABDLR.SA
2ABLCR.SA
2ABLRR.SA
2ABSVR.SA



A 5" 130mm - B 0.07" 1.8mm - C 0.04" 1.0mm

2ACFR.SA
2ACPR.SA
2ADGR.SA
2ADLR.SA
2ALCR.SA
2ALRR.SA
2ASVR.SA



A 5" 130mm - B 0.07" 1.8mm - C 0.04" 1.0mm

2AXCFR.SA
2AXCPR.SA
2AXDGR.SA
2AXDLR.SA
2AXLCR.SA
2AXLRR.SA
2AXSVR.SA

A 0.25" 6.6mm - B 0.41" 10.5mm - C 0.08" 2.0mm
D 0.14" 3.5mm - E 0.18" 4.5mm

2WFCPR.SA
2WFCPR.SA
2WFDGR.SA
2WFDLR.SA
2WFLCR.SA
2WFLRR.SA
2WFSVR.SA

A 0.47" 12mm - B 0.41" 10.5mm - C 0.08" 2.0mm
D 0.14" 3.5mm - E 0.18" 4.5mm

4WFCPR.SA
4WFCPR.SA
4WFDGR.SA
4WFDLR.SA
4WFLCR.SA
4WFLRR.SA
4WFSVR.SA



A 5" 130mm - B 0.02" 0.5mm - C 0.025" 0.6mm

5CFR.SA
5CPR.SA
5DGR.SA
5DLR.SA
5LCR.SA
5LRR.SA
5SVR.SA



A 5" 130mm - B 0.02" 0.5mm - C 0.025" 0.6mm

5XCFR.SA
5XCPR.SA
5XDGR.SA
5XDLR.SA
5XLCR.SA
5XLRR.SA
5XSVR.SA



A 5" 130mm - B 0.025" 0.6mm - C 0.025" 0.6mm

7CFR.SA
7CPR.SA
7DGR.SA
7DLR.SA
7LCR.SA
7LRR.SA
7SVR.SA



A 5" 130mm - B 0.055" 1.4mm - C 0.045" 1.2mm

242CFR.SA
242CPR.SA
242DGR.SA
242DLR.SA
242LCR.SA
242LRR.SA
242SVR.SA

A 5" 130mm - B 0.025" 0.6mm
C 0.03" 0.8mm - D 0.35" 9.0mm - E 45°

246CFR.SA
246CPR.SA
246DGR.SA
246DLR.SA
246LCR.SA
246LRR.SA
246SVR.SA




A 5" 130mm - B 0.09" 2.2mm - C 0.09" 2.2mm

249CFR.SA
249CPR.SA
249DGR.SA
249DLR.SA
249LCR.SA
249LRR.SA
249SVR.SA



A 5" 130mm - B 0.025" 0.6mm - C 0.04" 1.0mm

259CFR.SA
259CPR.SA
259DGR.SA
259DLR.SA
259LCR.SA
259LRR.SA
259SVR.SA



KCFR


carbofib replaceable tip tweezers set
249CFR, A2ACF, A259CF, A5CF, A7CF
top quality hard/foam wallet with 6 screws

Replaceable Tip Sets Part Numbers

	00	2AB	2A	2WF	4WF	5	7	242	246	249	259
CF	A00CF	A2ABCF	A2ACF			A5CF	A7CF	A242CF	A246CF	A249CF	A259CF
CP	A00CP	A2ABCP	A2ACP	A2WFCP	A4WFCP	A5CP	A7CP	A242CP	A246CP	A249CP	A259CP
DG	A00DG	A2ABDG	A2ADG			A5DG	A7DG	A242DG	A246DG	A249DG	A259DG
DL	A00DL	A2ABDL	A2ADL			A5DL	A7DL	A242DL	A246DL	A249DL	A259DL
LC	A00LC	A2ABLC	A2ALC			A5LC	A7LR	A242LC	A246LC	A249LC	A259LC
LR	A00LR	A2ABLR	A2ALR			A5LR	A7LR	A242LR	A246LR	A249LR	A259LR
SV	A00SV	A2ABSV	A2ASV			A5SV	A7SV	A242SV	A246SV	A249SV	A259SV


Soft Tip Tweezers

Carbofib soft tweezers, scratched proof specifically designed to handle sensitive parts.




251.SA

4 1/4" 110mm




252.SA

4 1/4" 110mm




253.SA

4 1/4" 110mm




254.SA

4 1/4" 110mm




255.SA

4 1/4" 110mm




256.SA

4 1/4" 110mm



257.SA

4 1/4" 110mm




258.SA

4 1/4" 110mm

Plastic Tweezers

High precision plastic tweezers available in four different materials for various applications.




702A.CF
702A.DG
702A.LR
702A.SV

A 4 1/2" 115mm - B 0.08" 2.0mm - C 0.04" 1.0mm



705.CF
705.DG
705.LR
705.SV

A 4 1/2" 115mm - B 0.02" 0.5mm - C 0.025" 0.6mm



707.CF
707.DG
707.LR
707.SV

A 4 1/2" 115mm - B 0.02" 0.5mm - C 0.045" 1.2mm




707A.CF
707A.DG
707A.LR
707A.SV

A 4 1/2" 115mm - B 0.025" 0.6mm - C 0.04" 1.0mm



708.CF
708.DG
708.LR
708.SV

A 4 1/2" 115mm - B 0.02" 0.5mm
C 0.04" 1.0mm - D 0.35 9.0mm - E 45°




709.CF
709.DG
709.LR
709.SV

A 4 1/2" 115mm - B 0.013" 3.3mm - C 0.02" 0.5mm



710.CF
710.DG
710.LR
710.SV

A 4 1/2" 115mm - B 0.03" 7.7mm - C 0.02" 0.5mm



K6CF

carbofil plastic tweezers set 702ACF, 705CF, 707CF, 708CF, 709CF, 710CF plastic wallet