


## Two Post Mounting Cantilever Shelf *RAS Series*

### Features



- Allows easy rack mounting of narrow equipment or items that do not have rack mounting capabilities.
- Shelves feature formed 16-gauge steel construction.
- Front & back edge folded - acting as both stiffeners and equipment retainers.
- Mounts to rack rails either as an internal shelf or external shelf/work area
- Choice of two depths - 7" or 14.5"
- Available in either vented or unvented versions
- Shelves include tie down slots on each side & four tie down holes.
- Rugged textured - black powder paint finish

### 19 Inch Mounting Shelves

| Part No.       | Part No.       | Mounting Dimensions |        |       |       | Stiffener           | Suggested     |
|----------------|----------------|---------------------|--------|-------|-------|---------------------|---------------|
|                |                | Rack                | Height | Width | Depth | Lip(s)              |               |
| Vented         | Solid          | Units               |        |       |       | Folded              | Load Capacity |
| RASV190107UBK1 | RASU190107UBK1 | 1U                  | 1.75   | 19.00 | 7.00  | Up (Front & Back)   | 40            |
| RASV190107DBK1 | RASU190107DBK1 | 1U                  | 1.75   | 19.00 | 7.00  | Down (Front & Back) | 40            |
| RASV190115BK1  | RASU190115BK1  | 1U                  | 1.75   | 19.00 | 15.00 | Up (Back Only)      | 40            |
| RASV190120BK1  | RASU190120BK1  | 1U                  | 1.75   | 19.00 | 20.00 | Up (Back Only)      | 40            |
| RASVL190314BK1 | RASUL190314BK1 | 2U                  | 3.50   | 19.00 | 14.50 | Up (Back Only)      | 65            |
| RASVL190514BK1 | RASUL190514BK1 | 2U                  | 3.50   | 19.00 | 14.50 | Up (Back Only)      | 80            |
| RASV190315BK1  | RASU190315BK1  | 2U                  | 3.50   | 19.00 | 15.00 | Up (Back Only)      | 100           |
| RASV190320BK1  | RASU190320BK1  | 2U                  | 3.50   | 19.00 | 20.00 | Up (Back Only)      | 100           |
| RASV190515BK1  | RASU190515BK1  | 3U                  | 5.25   | 19.00 | 15.00 | Up (Back Only)      | 200           |
| RASV190520BK1  | RASU190520BK1  | 3U                  | 5.25   | 19.00 | 20.00 | Up (Back Only)      | 200           |
| RASV190715BK1  | RASU190715BK1  | 4U                  | 7.00   | 19.00 | 15.00 | Up (Back Only)      | 200           |
| RASV190720BK1  | RASU190720BK1  | 4U                  | 7.00   | 19.00 | 20.00 | Up (Back Only)      | 200           |

### 23 Inch Mounting Shelves

| Part No. | Part No. | Mounting Dimensions |  |  |  | Stiffener | Suggested |
|----------|----------|---------------------|--|--|--|-----------|-----------|
|          |          |                     |  |  |  | Lip(s)    |           |

| Vented               | Solid                | Rack<br>Units | Height | Width | Depth | Folded            | Load<br>Capacity |
|----------------------|----------------------|---------------|--------|-------|-------|-------------------|------------------|
| <b>RASV230515BK1</b> | <b>RASU230515BK1</b> | 3U            | 5.25   | 23.00 | 15.00 | Up (Back<br>Only) | 200              |
| <b>RASV230520BK1</b> | <b>RASU230520BK1</b> | 3U            | 5.25   | 23.00 | 20.00 | Up (Back<br>Only) | 200              |

## 24 Inch Mounting Shelves

| Part No.             | Part No.             | Mounting Dimensions |        |       |       | Stiffener<br>Lip(s) | Suggested<br>Load<br>Capacity |
|----------------------|----------------------|---------------------|--------|-------|-------|---------------------|-------------------------------|
| Vented               | Solid                | Rack<br>Units       | Height | Width | Depth | Folded              |                               |
| <b>RASV240520BK1</b> | <b>RASU240520BK1</b> | 3U                  | 5.25   | 24.00 | 20.00 | Up (Back<br>Only)   | 200                           |
| <b>RASV240515BK1</b> | <b>RASU240515BK1</b> | 3U                  | 5.25   | 24.00 | 15.00 | Up (Back<br>Only)   | 200                           |

*Data subject to change without notice.*