


LOC DF	DIST S0	P	F	REVISIONS						
				ZONE	LTR	DESCRIPTION				DATE
					C	REV PER 063D-0222-03	CT	1-04	DE	



OBSOLETE	13973-841416-3 REV --	42.00 ±.25 [1066.8 ± 6.4]	47.00 ±.50 [1193.8 ± 12.7]	447671-2
	-	26.00 ±.25 [660.4 ± 6.4]	31.00 ±.50 [787.4 ± 12.7]	447671-1
	CUST. PART NO.	B	A	PART NO.
DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN INCHES [mm] TOLERANCES ON: 2 PLC DEC ± .01 [0.25] 3 PLC DEC ± .005 [0.13] ANGLES ± -		DR W.LEUFERT 12-4-90	AMP AMP INCORPORATED Harrisburg, Pa. 17105	
		CHK D.EABY 2-27-91		
		APPD D.EABY 2-27-91	NAME LEAD ASSEMBLY, LGH-1 CRT BASE W/J1-21 CONTACT	
		MATERIAL SEE CALLOUTS		
FINISH SEE CALLOUTS		APPLICATION SPEC -	SIZE D	CAGE CODE 00779
		WEIGHT -	SCALE 2:1	DRAWING NO 447671
			SHEET -	1 of 1

- 1

TO MATE WITH AMP LGH-1 RCPT. WITH .88 [22.4] BARREL DEPTH.
- 2

TO MATE WITH J1-21 TYPE TERMINAL.
- 3

MARKED PER MIL-STD-130 INCLUDING CUSTOMER PART NO. (SEE TABLE).
4.

OPERATING CONDITIONS: 20KVDC, SEA LEVEL TO +70,000 FEET, [21.3 KM] -55°C TO +125°C.