






RoHS



K202XHT Series Right Angle Surface Mount

K202XHT Series Dimensions Dimensions in mm




Recommended PCB Layout

D-SUBMINIATURE CONNECTORS

K202XHT Series

Ordering Information



Series

K202XHT - D-Subminiature Connector, Right Angle,
Ultra Short Footprint, Surface Mount,
Reflow Compatible

Shell Size-Contact Option

E - 9 Contacts
B - 25 Contacts
E - 15 Contacts, High Density (Socket only)

Contact Type

P - Pin Contact (Plug)
S - Socket Contact (Receptacle)

Mounting Option

N - With Board Locks and (#4-40) Riveted Threaded Inserts
NJ - With Board Locks, Riveted Threaded Inserts, and
JSX-1055 Jack Screws Assembled to Connector

Plating Option

Blank - Gold Flash
15 - 15µ" Gold
30 - 30µ" Gold

Tape and Reel Available Contact Kycon

Shell Size	A In mm	A1 ±.010 ±.25	B ±.005 ±.013	C ±.015 ±.038	D ±.005 ±.013
9 (E)	.643 16.33	.666 16.92	.984 24.99	1.213 30.81	.626 15.90
15 (E)	.643 16.33	N/A	.984 24.99	1.213 30.81	.609 15.46
25 (B)	1.511 38.38	1.534 38.96	1.852 47.04	2.088 53.04	1.498 38.06

A = Exterior of Female Shell (S) A1 = Interior of Male Shell (P)