

APPLICATOR PARTS LIST				TYPE SIDEWISE STRAIN RELIEF HOOK & RING				AMP INCORPORATED HARRISBURG, PENNA.				NO. STAMPING DEVICE	
NO.	DESCRIPTION	REQ.	PART NO.	NO.	DESCRIPTION	REQ.	PART NO.	CRIMPING DATA			TERMINALS		
1	WIRE CRIMPER			42	SHEAR DEPRESSOR	1	810955-6	TO APPLY TERMINAL			180-240		
2	INS. CRIMPER	1	386993-7	43	SPRING SHEAR	1	386455				.660		
3	ANVIL	1	694325-2	44	SPRING SEAT	1	386443	WIRE SIZE CRIMP HEIGHT			RING		
4	ANVIL SPACER	1	453263-1	45	SHEAR BEARING PL. FRT.	1	386409-1				61520		
5	SHEAR FLOATING	1	473243-2	46	REAR OILITE BEARING PL.	1	386408				62245		
6	REAR SHEAR PLATE			47	LEFT OILITE BEARING PL.	1	386406						
7	SHEAR BLADE MT. BLK.	1	386442	48	RIGHT OILITE BEARING PL.	1	386407						
8	SHEAR PLATE	1	386414	49									
9	REAR ANVIL SPACER PLT.			50									
10	FRONT ANVIL SPACER PLT.			51	STRIP HOLD	1	692871-1	CRIMP SIZE TYPE FEED					
11	TOOL SPACER	1	376409	52				WIRE .250 .0" .660 OR			HOOK		
12	CRIMP SPACER			53				INSUL. .908			61522		
13	FRONT STRIP GUIDE	1	386444-3	54				SLEEVED					
14	REAR STRIP GUIDE	1	1-465350-0	55				INSULATION RANGE .180-.225			WIRE RANGE		
15	RAM	1	473699	56				EXPLODED VIEW					
16	TOOL HOLDER			57				A-6009-3					
17	ADJ. CRIMP MOUNT			58	NOTE :			REMARKS:			150-200		
18	ADJ. BLOCK			59	MUST ADJ. FEED STRIP GUIDE &			1. MT. ON ITEM 14			.908		
19	APPLICATOR MOUNT ASSY.			60	CRIMP HEIGHT FOR DIFFERENT			2. MT. ON TOP SCREW			J HOOK		
20	BASE PLATE	1	473228	61	TERMINALS.			OF ITEM 45			61828		
21	BASE BLOCK	1	473227	62				TOP TOOL MOUNTING			62269		
22	STRIP GUIDE PLATE	1	453689-1	63	BRACKET-AIR FEED MT.	1	452063-1	42,1142			62362		
23	ANVIL HOLDER			64	1" AIR FEED ASS'Y	1	690021-1						
24	AUX. ANVIL HOLDER			65	TENSION ADJ. PLATE	1	374999						
25	STRIPPER	1	694924-2	66	MISCELLANEOUS								
26	STRIPPER MOUNT			67	REEL SPREADER ASS'Y	1	453596-1				WING		
27	RETAINER PLATE			68	LUBRICATOR ASS'Y	REF	465184-8				61831		
28	STRIPPER MOUNT BRACKET			69	TERMINAL LUBRICANT		561230-3						
29	STRIPPER BUSHING			70									
30	STOCK DRAG	1	387650-4	71									
31	STOCK DRAG HANDLE	1	21018-5	72									
32	STOCK DRAG STUD	1	800849	REV.	REVISION RECORD		DATE	BY	ECN				
33	STOCK DRAG SPRING	1	370572	01	ADD TERM. 62362		12-11-81						
34	STOCK DRAG ADJ. SCREW	1	221006-9	A	ECN A-230090		1/25/90						
35	FEED FINGER HOLDER	1	386942										
36	FEED FINGER	1	473739-1										
37	FEED FINGER TIP	1	387251										
38	FEED FINGER GUIDE	1	693680-3										
39	BASE CASTING	1	570238										
40	GUARD	1	461343-1										
41													

FOR HARDWARE
SEE 607514-5