



© COPYRIGHT 1974 BY AMP INCORPORATED, HARRISBURG, PA.
ALL INTERNATIONAL RIGHTS RESERVED. AMP INCORPORATED PRODUCTS
COVERED BY U. S. AND FOREIGN PATENTS AND/OR PATENTS PENDING.

		REVISIONS					DATE	APPROVED
P	F	ZONE	LTR	DESCRIPTION			DATE	APPROVED
			L	OBS - 4; ECN AA-5371			1/4/89	TE
			M	REV; EC OUIE-0040-01			3-19-01	DD
								EB



1. THE CONTACT SURFACES OF THE TERMINALS ARE COATED WITH LUBRICANT.
2. ALL DIMENSIONS SHOWN ARE MAXIMUM UNLESS OTHERWISE SPECIFIED.
3. MATERIAL: HOUSING & COVERS - POLYPHENYLENE OXIDE.
TERMINALS - GOLD OVER NICKEL PLATED HIGH STRENGTH COPPER ALLOY.
HARDWARE - ZINC PLATED STEEL.
4. COVER AND HARDWARE SHIPPED UNASSEMBLED.
5. WIRE SIZE: 24 & 26 AWG SOLID & 24/7 STRAND COPPER CONDUCTORS.
MAX. INSULATION DIAMETER OF .045 IS ACCEPTABLE FOR MOST APPLICATIONS.
6. CABLE RANGE: .415 - .465 DIA.

△ CORING MAY OR MAY NOT APPEAR AND IS AT THE DISCRETION OF AMP INCORPORATED.



POLY BAGGED	BLACK	552259-1
PACKAGING	COLOR	PART NO

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES. TOLERANCES ON: DECIMALS ± ANGLES ±		CONTRACT NO DR A. Holt 5-27-81 CHK MD/mt 11-23-81		AMP INCORPORATED Harrisburg, Pa.	
MATERIAL △ 3		APPD S. H. 11/23/81 APPD R. M. 11/23/81		NAME PLUG KIT, 50 POSITION, B SLOT, SCREW LOCK W/90° COVER, CHAMP-LOK®	
FINISH △ 3		DSGN APPD OTHER APPD		SIZE CODE IDENT NO C 00779	DRAWING NO 552259
				SCALE 2/1	SHEET 1 OF 1