


# RUGGED RELIABLE MICRO SOCKETS

(1.00 mm) .0394" PITCH • CLM/MLE SERIES



## CLM

### Mates:

FTM, FTMH, MW

## MLE

### Mates:

FTM, FTMH, MW

## SPECIFICATIONS

**Insulator Material:** Black LCP  
**Contact Material:**

CLM: Phosphor Bronze

MLE: BeCu

### Plating:

CLM: Au or Sn over

50  $\mu$ " (1.27  $\mu$ m) Ni

MLE: Au over 10  $\mu$ " (0.25  $\mu$ m) Ni

### Operating Temp Range:

-55 °C to +125 °C

### Current Rating (CLM/FTMH):

3.1 A per pin

(2 pins powered)

### Current Rating (MLE/FTMH):

2.9 A per pin (2 pins powered)

### Max Cycles:

CLM: 100 with 10  $\mu$ " (0.25  $\mu$ m) Au

### Voltage Rating:

CLM: 270 VAC/382 VDC

MLE: 310 VAC/438 VDC

### Insertion Depth:

CLM:

Top Entry = (1.40 mm) .055" min.,

Bottom Entry =

(2.41 mm) .095" min.

(Add board thickness for

correct post OAL)

MLE:

(1.63 mm) .064" to



(3.18 mm) .125" with

(0.38 mm) .015" wiper,

pass-through, or (2.44 mm) .096"

minimum for bottom entry

**TIGER  
CLAW  
CONTACT**



| PIN/ROW | A           |
|---------|-------------|
| 04-15   | (3.56) .140 |
| 16-50   | (7.11) .280 |

-PA

-P

MLE

1

NO. PINS  
PER ROW

01

PLATING  
OPTION

DV

OPTIONS

02 thru 50

## PROCESSING

### Lead-Free Solderable:

Yes

### SMT Lead Coplanarity:

(0.10 mm) .004" max (02-25)



(0.15 mm) .006" max (26-50)\*

\*(.004" stencil solution

may be available; contact

ipg@samtec.com)

**TIGER  
BEAM  
CONTACT**



-P

-A

## ALSO AVAILABLE

Contact Samtec

Alignment pin

Other Gold plating options



### Note:

Some lengths, styles and options are non-standard, non-returnable.

CLM

1

NO. PINS  
PER ROW

02

PLATING  
OPTION

D

OPTIONS

02 thru 50

### -F

= Gold flash on contact,  
Matte Tin on tail

### -L

= 10  $\mu$ " (0.25  $\mu$ m)  
Gold on contact,  
Matte Tin on tail

### -BE

= Bottom Entry  
(Required for bottom entry)

### -K

= (3.50 mm) .138" DIA  
Polyimide film  
Pick & Place Pad  
(3 positions minimum)

### -P

= Pick & Place Pad  
(7 positions minimum)

### -PA

= Pick & Place Pad with  
integral Alignment Pin

### -TR

= Tape & Reel

### -FR

= Full Reel Tape & Reel  
(must order maximum  
quantity per reel;  
contact Samtec for  
quantity breaks)