

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

**Part Number:** [1301080088](#)  
**Status:** **Active**  
**Overview:** [Hand Lamps](#)  
**Description:** Super-Safeway 30W Fluorescent Hand Lamp with Cord Ballast Location and Switch, Cord Type 18/3 SJTW, Cord Length 15.24m (50.0')

**Documents:**  
[Brochure \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

|                             |                            |
|-----------------------------|----------------------------|
| <b>Agency Certification</b> |                            |
| CSA                         | LR85374                    |
| <b>General</b>              |                            |
| Product Family              | Portable Lighting          |
| Series                      | <a href="#">130108</a>     |
| NEMA Configuration          | NEMA 5-15                  |
| Outlet                      | None                       |
| Overview                    | <a href="#">Hand Lamps</a> |
| Product Name                | Super-Safeway              |
| Type                        | Hand Lamps                 |
| UPC                         | 78678861264                |
| <b>Physical</b>             |                            |
| Cord Length - Primary       | 15.24m (50.0')             |
| Cord Length - Secondary     | N/A                        |
| Depth                       | 58.40mm (2.300")           |
| Duty                        | Industrial                 |
| Guard Included              | No                         |
| Guard Type                  | N/A                        |
| Height                      | N/A                        |
| Length                      | 882.65mm (34.750")         |
| Material - Globe            | Butyrate                   |
| Material - Guard            | Nitrile Rubber 80 Shore A  |
| Mounting Style              | Hand Held                  |
| Packaging Type              | Carton                     |
| Socket Construction         | N/A                        |
| <b>Electrical</b>           |                            |
| Bulb Type                   | Fluorescent                |
| Cord Type - Primary         | 18/3 SJTW                  |
| Lamp Type                   | F30/T8                     |
| Lamp Wattage - Maximum      | 30W                        |
| Lumens                      | 2000                       |
| On/Off Switch               | Yes                        |
| Voltage (Fixture) - Maximum | 120VAC 60 HZ               |
| <b>Material Info</b>        |                            |
| Engineering Number          | 1015-3                     |



Series image - Reference only

|                                                               |                   |
|---------------------------------------------------------------|-------------------|
| <b>EU ELV</b><br><b>Not Relevant</b>                          |                   |
| <b>EU RoHS</b><br><b>Not Reviewed</b>                         | <b>China RoHS</b> |
| <b>REACH SVHC</b><br>Not Reviewed                             |                   |
| <b>Halogen-Free</b><br><b>Status</b><br><b>Not Reviewed</b>   |                   |
| For more information, please visit <a href="#">Contact US</a> |                   |
| China ROHS                                                    | Not Relevant      |
| ELV                                                           | Not Relevant      |
| RoHS Phthalates                                               | Not Reviewed      |

**Search Parts in this Series**  
[130108](#) Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION