






APPLICATION HOLE



TOTAL BOARD THICKNESS: 1.60 ± 0.05



NOTES:

1. MATERIAL:
BODY: HEAT STABILIZED NYLON 6/6
CONTACT: C88800 COPPER ALLOY
HARD TEMPER

LAMP VERSION			
LAMP TRADE NUMBER	SOCKET COLOR	CML (CANADA) PART NUMBER	FILTER COLOR
37	BLACK	55750603	
73	TAN	55750203	
74	BLUE	55750103	
74	BLUE	55750105	BLUE
74	GREY	55750405	BLUE
80	GREY	55750303	

NO LAMP VERSION	
SOCKET COLOR	CML (CANADA) PART NUMBER
GREY	55750302

DIST.
S

F	22470	CANADA UPDATE
REV	FOR NO.	REV DESCRIPTION/DATE
DWG NO.	B12794	REV. F
PART NO.	SEE TABLE	
CHK/APP	RHW/V	DIST. S
CHICAGO MINIATURE LAMP, INC.		

DO NOT SCALE

THIS DWG IS THE PROPERTY
OF CML (CANADA) INC.
AND IS PROPRIETARY IN
GENERAL AND IN DETAIL.
IT SHALL NOT BE COPIED
OR ITS CONTENTS REVEALED
TO OUTSIDE PARTIES WITH-
OUT THE WRITTEN CONSENT
OF CML (CANADA) INC.

PART NO.	5575 SERIES	TITLE	T1-3/4S LAMP & SOCKET ASSEMBLY
MODEL NO.			
FIELD NO.			
MATERIAL:	SEE NOTES		
FINISH:			
TOLERANCE UNLESS OTHERWISE SPECIFIED:			
MILLIMETERS	x.x ± 0.25 (0.010")		
ANGLE	± 1 deg.		
DRAWN	W.A. CAVEN	SCALE:	2:1
CHECKED			
ENG. APPROV			
		PB-0407	REV E

DWG NO. PB 0407

SHEET: 1 of 1