




Recommended Maximum Panel Thickness: .57" (15mm)

FEATURES:

- Banana Jack mates to all popular shrouded and unshrouded DMM plugs
- Meets IEC 1010-2-031 CAT III 1000V

MATERIALS:

Banana Jack: Brass, see ordering information for plating

Insulation: Nylon, see ordering information for color

Nut: Brass, Nickel Plated

RATINGS:

Operating Voltage: 1000 VRMS Max.

Current: 15 Amperes Max.

ORDERING INFORMATION: Model 6388-T-P-C

T = Terminal Type = SC=(Solder Cup), ST=(Solder Turret), BC=(Bifurcated Cup),

TS6= (Threaded Stud #6-32), TS8=(Threaded Stud #8-32)

P = Plating Options =T=(Tin), G=(Gold), N=(Nickel)

C = Color Options = 0=Black, 1=Brown, 2=Red, 3=Orange, 4=Yellow, 5=Green, 6=Blue, 7=Violet, 8=Gray, 9=White.

Sold in packs of ten.

All dimensions are in inches and metric. All specifications are to the latest revisions. Specifications are subject to change without notice.
Registered trademarks are the property of their respective companies. Made in USA

Sales: 800-490-2361 Fax: 888-403-3360
Technical Assistance: 800-241-2060

PomonaACCESS 90833 (800) 444-6785 or (425) 446-6010
More drawings available at www.pomonaelectronics.com

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Pomona:

[6388-BC-T-0](#) [6388-BC-T-8](#) [6388-BC-T-2](#) [6388-TS6-N-4](#) [6388-TS6-N-0](#) [6388-TS6-N-8](#) [6388-ST-T-8](#) [6388-ST-T-0](#)
[6388-ST-T-6](#) [6388-ST-T-2](#) [6388-ST-T-3](#) [6388-ST-T-4](#) [6388-ST-T-7](#) [6388-ST-T-5](#) [6388-ST-T-9](#) [6388-ST-T-1](#) [6388-](#)
[TS6-N-6](#) [6388-TS6-N-7](#) [6388-TS6-N-2](#) [6388-TS6-N-5](#) [6388-TS6-N-3](#) [6388-TS6-N-1](#) [6388-TS6-N-9](#) [6388-TS8-N-0](#)
[6388-TS8-N-4](#) [6388-TS8-N-6](#) [6388-TS8-N-7](#) [6388-TS8-N-9](#) [6388-TS8-N-5](#) [6388-TS8-N-8](#) [6388-TS8-N-2](#) [6388-TS8-](#)
[N-1](#) [6388-TS8-N-3](#) [6388-BC-G-4](#) [6388-BC-G-9](#) [6388-BC-G-7](#) [6388-BC-G-5](#) [6388-BC-G-2](#) [6388-BC-G-0](#) [6388-BC-](#)
[G-6](#) [6388-BC-G-3](#) [6388-BC-G-8](#) [6388-BC-G-1](#) [6388-SC-G-7](#) [6388-SC-G-8](#) [6388-SC-G-6](#) [6388-SC-G-4](#) [6388-SC-](#)
[G-5](#) [6388-SC-G-1](#) [6388-SC-G-9](#) [6388-SC-G-3](#) [6388-SC-T-0](#) [6388-SC-T-2](#) [6388-BC-T-1](#) [6388-BC-T-3](#) [6388-BC-T-4](#)
[6388-BC-T-5](#) [6388-BC-T-6](#) [6388-BC-T-7](#) [6388-BC-T-9](#) [6388-SC-T-1](#) [6388-SC-T-3](#) [6388-SC-T-4](#) [6388-SC-T-5](#)
[6388-SC-T-6](#) [6388-SC-T-7](#) [6388-SC-T-8](#) [6388-SC-T-9](#)