

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION




© COPYRIGHT BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC
JDIST
—

REVISIONS

変更

P	LTR	DESCRIPTION	DATE	DWN	APVD
	U	REVISED ECR-08-002576	30JAN'08	J.S	S.M
	V	REVISED ECR-08-010483	23MAY'08	J.S	S.M
	W	REVISED ECR-08-014271	16JUN'08	J.S	S.M

表 1
(TABLE 1)

No	名称 (NAME)	材料 (MATERIAL)
①	ヘッダーハウジング (HEADER HOUSING)	PBT ガラス強化 UL94V-0 (PBT GLASS FILLED UL94V-0)
②	ポスト コンタクト (POST CONTACT)	黄銅錫めっき仕上げ (POST TIN-BRASS)

注記:

1. 嵌合相手側製品型番: □-1123722-□
2. 取付け基板穴寸法: FIG.1参照
3. 適用基板厚: 1.6t
4. 7.92mmピッチタイプ (FIG.2参照)

NOTES:

1. MATING CONN P/N: □-1123722-□
2. APPLICABLE P.C.B LAY OUT: SEE FIG.1
3. APPLICABLE P.C.B THICKNESS: 1.6t
4. TYPE OF 7.92mm PITCH (SEE FIG.2)





FIG. 1

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
単位: 概
mmMATERIAL
材料
SEE TABLE1TOLERANCES UNLESS
OTHERWISE SPECIFIED:
一般公差5±0.3
5<±0.4
±
±
±FINISH
仕上

—//—

DWN N.YAMASAKI 13MAR'01

CHK M.SHINDO 13MAR'01

APVD Y.KASHIWA 13MAR'01

PRODUCT SPEC

製品規格

108-5609

APPLICATION SPEC

取付適用規格

WEIGHT

—//—

CUSTOMER DRAWING

Tyco Electronics Corporation
Kawasaki, JapanNAME
名称 3.96(7.92)MM PITCH ECONOMY POWER(EP) CONN
HEADER ASSY

3.96(7.92)mmピッチ エコノミパワー(EP)コネクタ ヘッダーアッセンブリ

SIZE CAGE CODE DRAWING NO
番号

A3 00779 C-1123723

RESTRICTED TO

SCALE —//— SHEET 1 OF 2 REV W

[illegible]

SCALE	SHEET	REV
-------	-------	-----