



Black Box Products

Cables > Computer & Data Cables

Extended-Distance Data Cable, Office Environment, PVC Jacket, 25 Conductors (12 1/2 Pairs), 1000-ft. (304.8-m)



Send RS-232 data up to 500 feet in your office environment.
EDN25A-1000
Extended Double Diamond™ Warranty Available
(Lifetime)

Product Highlights

- For use with RS-232, V.35, RS-422, and RS-485 interfaces.
- Distances up to 500 feet (152.4 m).
- Low capacitance, foil shielded. Ideal choice for office environments.
- 24 AWG stranded construction.
- Guaranteed for life!



Description

Extended-Distance Data Cable, Office Environment, PVC Jacket, 25 Conductors (12 1/2 Pairs), 1000-ft. (304.8-m)

Quick Facts

- For use with RS-232, V.35, RS-422, and RS-485 interfaces.
- Distances up to 500 feet (152.4 m).
- Low capacitance, foil shielded. Ideal choice for office environments.
- 24 AWG stranded construction.
- Guaranteed for life!

Technical Specifications for Extended-Distance Data Cable, Office Environment, PVC Jacket, 25 Conductors (12 1/2 Pairs), 1000-ft. (304.8-m):

"

| | |
|-----------------|------------------------------|
| Cable Type | Twisted pair, PVC jacket |
| Capacitance | 12 pF/ft. ± 2 pF/ft. |
| Conductor Gauge | 24 AWG (7 x 32 AWG) stranded |
| Resistance | 25 ohms/1000 ft. |
| Shield | Foil wrap with drain wire |

