





REV. U

DIMENSIONS ARE IN INCHES ONE PLACE DECIMALS $\pm .1$ [.3] TWO PLACE DECIMALS $\pm .01$ [.3]		UNLESS OTHERWISE NOTED TOLERANCES ARE: THREE PLACE DECIMALS $\pm .005$ [.13] FOUR PLACE DECIMALS $\pm .0020$ [.051]		ANGLES $\pm 2^\circ$	TITLE: LOW PROFILE SOCKET STRIP	DWG NO: SLW-1XX-01-X-X SHEET 1 OF 1
---	--	--	--	-------------------------	---------------------------------------	---



- NOTES:
1. MIN PUSHOUT FORCE: 1 lb.
 2. MAX BOW: .005 in/in [mm/mm], .025 [.64]
 3. CUT END WALLS TO BE .012 [.30] MIN.
 4. (C) REPRESENTS CRITICAL DIM.
- FOR STATISTICAL PROCESS CONTROL
5. .010 [.25] MAX CUT FLASH
 6. NO TUBE PACKAGING REQUIRED

Do not scale
from this print

PROPRIETARY NOTE
THIS DOCUMENT CONTAINS INFORMATION
CONFIDENTIAL AND PROPRIETARY TO
SAMTEC INC. AND SHALL NOT BE
REPRODUCED OR TRANSMITTED IN
ANY FORM OR BY ANY MEANS
ELECTRONIC OR MECHANICAL,
INCLUDING PHOTOCOPYING,
RECORDING, OR BY ANY
INFORMATION STORAGE AND
RETRIEVAL SYSTEM, WITHOUT
WRITTEN PERMISSION OF SAMTEC INC.

PLOT SCALE: 1=1

samtec

520 PARK EAST BLVD. NEW ALBANY, INDIANA 47150
PHONE (812) 944-6733 P.O. BOX 1147
CODE 55322

MADE BY: PURVIS 9-4-87
CHECKED BY: McCARTIN

ENG. APPROVAL: DEM

SLW-1XX-01-X-X
SHEET 1 OF 1