

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0681290611](#)
Status: **Obsolete**
Description: 2.50mm (.098") Pitch Board-to-Board Header, One-Piece, Right-Angle, 3.20/5.30mm (.126/.209") Length PC Tail, 6 Circuits
Replacement Part Number: 681290661

Documents:
[Drawing \(PDF\)](#)

General

Product Family	PCB Headers
Series	68129
Application	Signal, Wire-to-Board
Obsolete Date	2005/01/01
Product Name	N/A
Replacement Part Number	681290661

Physical

Breakaway	No
Circuits (Loaded)	6
Circuits (maximum)	6
Durability (mating cycles max)	30
Glow-Wire Compliant	No
Lock to Mating Part	None
Number of Rows	1
Orientation	Right Angle
PC Tail Length	3.20mm (.126")
PCB Locator	No
PCB Retention	None
PCB Thickness - Recommended	1.60mm (.063")
Packaging Type	Bag
Pitch - Mating Interface	2.50mm (.098")
Polarized to Mating Part	No
Shrouded	No
Stackable	No
Surface Mount Compatible (SMC)	No
Temperature Range - Operating	-20°C to +85°C


Electrical

Current - Maximum per Contact	1A
Voltage - Maximum	250V

Material Info

Reference - Drawing Numbers

Product Specification	PS-68129-001
Sales Drawing	SD-68129-001



Series

image - Reference only

EU RoHS	China RoHS
Compliance Status	
Not Reviewed	
REACH SVHC	
Not Reviewed	
Low-Halogen Status	
Not Reviewed	

Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series
[68129Series](#)