

6.02135.50 BS 14.4 Li

## 14.4 Volt Cordless Drill/Screwdriver BS 14.4

- Variospeed (V) electronics for infinitely variable speed change
- 20-level adjustable torque, plus drilling level
- Motor with high output and compact size
- Clockwise and anticlockwise rotation
- Quick stop for rapid fastening of screws
- Quick-action keyless chuck and spindle stop gear for convenient one-hand tool change: Metabo "Quick"
- Fatigue-free operation due to perfect ergonomics
- Rubber-coated handle provides a comfortable non-slip grip for the user
- High service life due to 3-level planetary metal gears
- Individual cell monitoring prevents over-discharging the battery pack
- Electronic overload protection with integrated temperature monitoring protects both the machine and the battery pack
- AIR COOLED technology for speedy charging and long service life
- Robust battery packs with capacity display for checking the charge status

### Comparative technical values

|                                 |                          |
|---------------------------------|--------------------------|
| Type of battery pack            | Li-Ion                   |
| Battery pack voltage            | 14,4 V                   |
| Capacity of battery pack        | 1,3 Ah                   |
| Max. torque, soft               | 20 Nm                    |
| Max. torque, hard               | 40 Nm                    |
| Drill diameter in               |                          |
| - Steel                         | 10 mm/5 mm               |
| - Wood                          | 20 mm/16 mm              |
| No-load speeds                  | 0 - 450 / 0 - 1.600 /min |
| Drill spindle thread            | 1/2" -20 UNF             |
| Chuck capacity                  | 1 - 10 mm                |
| Weight (including battery pack) | 1,35 kg                  |

### Scope of delivery

2 Li-Power Compact battery packs (14.4 V/1.3 Ah), AIR COOLED quick charger ASC 30