

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT - BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.


LOC	DIST	REVISIONS			
		P	LTR	DATE	DWN APVD
GP	00		B	REVISED PER ECO-08-007327	02OCT08 BM WM

D

C

B

A



- THE CONTACT SURFACES OF THE TERMINALS ARE COATED WITH LUBRICANT.
- ALL DIMENSIONS ARE MAXIMUM UNLESS OTHERWISE SPECIFIED.
- MATERIAL:
HOUSING, COVER, AND CABLE CLAMP: POLYPHENYLENE OXIDE GRAY.
TERMINAL: HIGH STRENGTH COPPER ALLOY PLATED WITH .000030 MIN GOLD OR GOLD FLASH OVER PALLADIUM NICKEL PLATE, .000030 MIN TOTAL ON MATING SURFACES. .000050 MIN NICKEL UNDERPLATE ON ENTIRE TERMINAL.
- COVER, SCREW & CABLE CLAMP SHIPPED UNASSEMBLED.
- WIRE SIZE: 24-26 AWG SOLID 7 OR 24 AWG STRANDED COPPER CONDUCTORS, MAXIMUM INSULATION DIAMETER OF .045 IS ACCEPTABLE FOR MOST APPLICATIONS.
- CABLE RANGE: .425 DIAMETER MAX.
- 500 KITS BULK PACKAGED.
- CORING IS AN OPTIONAL CONFIGURATION AND IS AT THE DISCRETION OF AMP.

D

C

B

A

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN B. MCMASTER	27OCT05	 Tyco Electronics Corporation Harrisburg, PA 17105-3608					
		CHK W. MILLHIMES	27OCT05						
DIMENSIONS: INCHES		APVD W. MILLHIMES	27OCT05	NAME RECEPTACLE KIT, 50 POSITION, B-SLOT, WITH 90 DEGREE COVER AND SCREW, CHAMP-LOK					
		PRODUCT SPEC						SIZE	
		—		A2		00779	C=5556006	—	
		APPLICATION SPEC							
		—							
MATERIAL		WEIGHT							
		—							
		FINISH							
		CUSTOMER DRAWING							
		SCALE 2:1 SHEET 1 of 1 REV B							

5556006