


Sockets

PKI 100



Product	PKI 100
description	Pole terminal with captive insulated head, which is held under constant pressure against the insulated rings by a spring. 4 mm diameter nickel-plated, brass threaded bolt with 2 mm diameter transverse hole. For non-rotating installation in switchpanels and equipment chassis with wall thickness up to 3.5 mm.
operating instruction	BA402
article-no. / *colour	9307571xx  00 black  01 red  02 blue  03 yellow  04 green  88 yellow green Ni
drawing	
	
technical data	
connection	M4 thread
rated voltage ⁽¹⁾	30 VAC / 60 VDC
measurement cat. acc. to IEC 61010	O ⁽³⁾
rated current ⁽¹⁾ (consider derating curve)	35 A
material socket	brass, nickel plated
housing material	PA
temperature range acc. To IEC61010 ⁽²⁾	-25 °C to +100 °C
inflammability class acc. to UL 94 (only valid for basic material of housing)	V-2

4 mm system

standard	IEC 61010
----------	-----------

⁽¹⁾ for normal environmental conditions -5°C to +40°C

⁽²⁾ contact the manufacturer for applications at deviating temperature ranges

⁽³⁾ without rated measurement category, for other circuits that are not directly connected to mains

stand: 03.09.2018