



Plotter MCP Basic and MCP Plus



MCP Basic



MCP Plus

Plotter **MCP Basic** and **MCP Plus** complement the Weidmüller MultiCard concept. They are suitable for smaller quantities of markers and when only part of a MultiCard is to be printed on. The special positioning frame for five MultiCards with MCP Plus increases productivity by 25 % over comparable systems. The MCP Basic plotter with a positioning frame for 3 MultiCard is a flexible and portable solution that allows you to print your labels on-site quickly and easily. With the positioning frame for SlimFix markers sizes 4 to 6 (optional), printing on more than 160 MultiCard types for terminals, cables, wires and equipment is possible. Labels are printed with the MCP-Label positioning frame (optional).

Suitable for use with the Weidmüller software **M-Print® PRO**.

- 2 positioning frames for more than 160 MultiCard types
- MultiCards easily fitted into the frame
- Easy to use with partly used MultiCards
- Automatic pen activation function
- Safe storage of the plotter pens

United Kingdom

Weidmüller Ltd.
1 Abbey Wood Road
West Malling, Kings Hill
ME19 4YT
Phone +44 1732 877000
Fax +44 1732 874296


USA

W-Interconnections, Inc.
821 Southlake Boulevard,
Virginia - Richmond 23236
Phone +1 804 7942877
Fax +1 804 3792593
info@weidmuller.com
www.weidmuller.com


Other countries

Weidmüller Interface GmbH & Co. KG
Postfach 3030
32720 Detmold
Klingenbergstraße 16
32758 Detmold
Phone +49 5231 14-0
Fax +49 5231 14-20 83
info@weidmueller.de
www.weidmueller.com

MCP Basic



MCP Plus



Technical data

Type	MCP Basic	MCP Plus
Application	Printing MultiCard markers and labels	Printing MultiCard markers and labels
Technology	plotting technique	plotting technique
Plotting speed	max. 40 mm/s	max. 40 mm/s
Pen-Depot	max. 2 Plotter-Pens (not used by Plotter)	max. 4 Plotter-Pens with double sealed
Print software	M-Print® PRO	M-Print® PRO
System requirements	Windows® 2000/XP/VISTA/7	Windows® 2000/XP/VISTA/7
Interface	USB	Parallel Centronics / USB
Feed	manual	manual
Voltage supply	Via external power supply unit with interchangeable adapters	Via external power supply unit with interchangeable adapters
Power supply input voltage	100-240V AC 50-60Hz	100-240V AC 50-60Hz
Power supply input current	0.7 A max.	0.7 A max.
Power supply output voltage	24 V DC	24 V DC
Power supply output current	1.25 A max.	1.25 A max.
Ambient temperature	10 °C – 35 °C	10 °C – 35 °C
Location	office conditions	office conditions
Safety certificate	EN 60950-1	EN 60950-1
Interference safety compliance	EN 55022 B EN 61000-4-2 to 6 EN 61000-4-2 to 11	EN 55022 B EN 61000-4-2 to 6 EN 61000-4-2 to 11
Dimensions: (L x W x H) mm	440 x 440 x 125	660 x 440 x 125
Weight:	approx. 6 kg	approx. 8 kg
Scope of supply	MCP Basic with USB cable, power pack (AC 110 V / 240 V, 50-60 Hz), Euro, UK and US plugs, MultiCard positioning frame, 0,25 plotter pen, software CD with M-Print PRO and manuals, trolley	MCP Plus with Centronics cable, power pack (AC 110 V / 240 V, 50-60 Hz), Euro, UK and US plugs, MultiCard positioning frame, 0,25 plotter pen, software CD with M-Print PRO and manuals

Ordering data

Type	Order No.	Type	Order No.
MCP Basic	1139400000	MCP Plus	1925000000



MCP positioning frames

Ordering data

Type	for	Qty.	Order No.
MCP AP PLUS	MultiCards	1	1924360000
MCP AP BASIC	MultiCards	1	1139880000
MCP AP SF 4-6	SlimFix sizes 4 to 6	1	1924310000
MCP AP Labels	Labels	1	1924370000

MCP plotter pens

Type	for	Qty.	Order No.
Plotter Pen 0.18	Reusable pen	1	1768570000
Plotter Pen 0.25	Reusable pen	1	1768540000
Plotter Pen 0.25 P-Ink	Disposable pen 8 ml Not for CLI T sleeves	1	1920640000
Plotter Pen 0.35	Reusable pen	1	1768550000
Plotter Pen 0.35 P-Ink	Disposable pen 8 ml Not for CLI T sleeves	1	1920650000
Plotter Pen 0.50	Reusable pen	1	1768560000
Plotter Pen 0.50 P-Ink	Disposable pen 8 ml Not for CLI T sleeves	1	1005710000
Plotter Pen 0.70	Reusable pen	1	1011440000
Plotter Pen 0.70 P-Ink	Disposable pen 8 ml Not for CLI T sleeves	1	1011450000

MCP ink

Type	Contents	Qty.	Order No.
P- Ink	30 ml Not for CLI T sleeves	1	1924340000
Ink 2000	25 ml	1	1772120000

MCP miscellaneous

Type	Contents	Qty.	Order No.
P cleaner	30 ml	1	1924330000
Cleaner Clean 2000	25 ml	1	1772130000
Inlay for MCP		1	1935130000
Inlay SFC 3		1	1058090000
MCP adhesive strips		5	1924320000
MCP Plus cover		1	1924350000
MCP TP-KOF Basic	Trolley MCP Basic	1	1139890000



Accessories - STI pen

Ordering data

Type	Qty.	Order No.
Adapter aluminium STI pen	1	1762440000
STI pen SW	10	0508401694

The STI-S felt tip pen is suitable for labelling blank Weidmüller marking products. It can be used for handwritten labels or, in conjunction with the STI-S adapter, for a plotter printout. A black, waterproof ink is used.

