


HANDLES

FOLDING HANDLES BRASS, NICKEL PLATED


30-1000-1-1 2 POSITIONS- 90°
30-1000-2-1 3 POSITIONS- 180°



SUPPLIED WITH NUTS AND LOCKWASHERS


ADJUSTABLE HANDLE BRASS, NICKEL PLATED

30-1300-1



FOLDING HANDLE BRASS, NICKEL PLATED


30-1100-1 FOLDS 90°



OFFSET HANDLES


ROUND BRASS, NICKEL PLATED

30-3405-1 L 4-1/2"
30-3410-1 L 6-1/2"




FOLDING HANDLES ALUMINUM

30-1200 FOLDS 180°




OFFSET HANDLES ROUND ALUMINUM

SEMI-FROST ANODIZE 30-3505-12 L 4-1/2"
BLACK ANODIZE 30-3510-12 L 6-1/2"




FOLDING HANDLES OVAL • BRASS, NICKEL PLATED

30-1400-1-1 2 POSITIONS- 90°
30-1400-2-1 3 POSITIONS- 180°




MTG. HARDWARE: 2 HEX NUTS, BRASS/NICKEL & 2 LOCKWASHERS, STEEL/ZINC

OVAL HANDLES



FOLDING HANDLE STAINLESS STEEL

30-1600-2 3 POSITIONS- 180°



MTG. HARDWARE: 2 HEX NUTS & 2 LOCKWASHERS, STAINLESS STEEL

BRASS NICKEL PLATE	ALUMINUM		L	D	THREAD
	SEMI-FROST ANODIZE	BLACK ANODIZE			
30-3005-1	30-3105-12	30-3105-11	3	1-9/32	10-32
-	30-3106-12	30-3106-11	3	1-9/32	10-24
30-3010-1	30-3110-12	30-3110-11	3	1-3/4	10-32
30-3015-1	30-3115-12	30-3115-11	4	1-3/4	10-32
30-3020-1	30-3120-12	30-3120-11	4-9/16	1-1/2	10-32
-	30-3121-12	30-3121-11	4-9/16	1-1/2	10-24
30-3025-1	30-3125-12	30-3125-11	4-9/16	1-3/4	10-32
30-3030-1	30-3130-12	30-3130-11	6-7/16	1-3/4	10-32
-	30-3131-12	30-3131-11	6-7/16	1-3/4	10-24
30-3035-1	30-3135-12	30-3135-11	9	1-3/4	10-32
-	30-3136-12	30-3136-11	9	1-3/4	10-24

FOR ADDITIONAL SIZES AND MATERIAL, CONTACT FACTORY

CONCORD