

U.I. Lapp GmbH	<b>DATASHEET</b>	 <b>LAPP GROUP</b>
	<b>DKK double clamp</b>	52026010 14.11.2013

DKK double clamp for fastening cables and conductors

### Application range

Simple and reliable mounting clamps for lift control cables

### Benefits

Secure protection without restricting the mobility of the cable cores

Wide clamping range



### Note

Installation guidelines for ÖLFLEX® -LIFT RH and RS lift control cables can be found in the appendix T5

Maximum load for each clamp: 800 N (80 kg)

Only for vertical assembly

### Included

Impact anchor, screws and safety discs are supplied as installation accessories

### Remark

Photographs are not to scale and do not represent detailed images of the respective products.

### Technical Data

Article designation:	DKK 18
For cable Ø (mm):	15-18
Length x width x height (mm):	125 x 85 x 120
Weight (kg/piece):	1.9
Pieces / PU:	1
Temperature range:	high mechanical load: +65°C low mechanical load: +100°C

Product Management	Document: DKK double clamp	1 / 1
--------------------	----------------------------	-------