




















SxV Soldering Tips



Compatible with: PS-900, MFR-1120, MFR-2220, MFR-2222 Systems,
PS-HC3 and MFR-H2-ST hand-pieces, PS-CA3 and MFR-CA2 Coil Assemblies

SxV SOLDERING TIPS		Compatible with: PS-900, MFR-1120, MFR-2220 Systems, PS-HC3 and MFR-H2-ST hand-pieces, PS-CA3 and MFR-CA2 Coil Assemblies				
CHISEL	NEW 	SFV-CH10A STV-CH10A SCV-CH10A	CHISEL		SFV-CH25 STV-CH25 SCV-CH25	
		SFV-CH10AR STV-CH10AR SCV-CH10AR			SFV-CH30AR STV-CH30AR SCV-CH30AR	
		SFV-CH10 STV-CH10 SCV-CH10		NEW 	SFV-CH50A STV-CH50A SCV-CH50A	
	NEW 	SFV-CH15A STV-CH15A SCV-CH15A			SFV-CH50AR STV-CH50AR SCV-CH50AR	
		SFV-CH15AR STV-CH15AR SCV-CH15AR			SFV-CH50 STV-CH50 SCV-CH50	
		SFV-CHB15 STV-CHB15 SCV-CHB15		CONICAL		SFV-CNL03AR STV-CNL03AR SCV-CNL03AR
		SFV-CH18AR STV-CH18AR SCV-CH18AR			NEW 	SFV-CNB04A STV-CNB04A SCV-CNB04A
		SFV-CH20 STV-CH20 SCV-CH20			NEW 	SFV-CN05A STV-CN05A SCV-CN05A
	NEW 	SFV-CH24A STV-CH24A SCV-CH24A				SFV-CNB04AR STV-CNB04AR SCV-CNB04AR
		SFV-CH25AR STV-CH25AR SCV-CH25AR				SFV-CNL04 STV-CNL04 SCV-CNL04

F = FR4 / Fiber Glass, for most standard applications T = Temperature Sensitive C = Ceramic for high thermal demand applications.

SxV Soldering Tips

CxV Blade Tips



Compatible with: PS-900, MFR-1120, MFR-2220, MFR-2222 Systems,
PS-HC3 and MFR-H2-ST hand-pieces, PS-CA3 and MFR-CA2 Coil Assemblies



CONICAL

SxV SOLDERING TIPS	
	SFV-CN05AR STV-CN05AR SCV-CN05AR
	SFV-CN05 STV-CN05 SCV-CN05
	SFV-CNB05 STV-CNB05 SCV-CNB05
	SFV-CNL10A STV-CNL10A SCV-CNL10A
	SFV-CNL10AR STV-CNL10AR SCV-CNL10AR
	SFV-CNL10 STV-CNL10 SCV-CNL10
	SFV-CNL14 STV-CNL14 SCV-CNL14
	SFV-DRH20 STV-DRH20 SCV-DRH20
	SFV-CNL20 STV-CNL20 SCV-CNL20
	SFV-WV20 STV-WV20 SCV-WV20
	SFV-DRK45A STV-DRK45A SCV-DRK45A
	SFV-DRK50 STV-DRK50 SCV-DRK50

KNIFE

HOOF

	SFV-DRH420AR STV-DRH420AR SCV-DRH420AR
	SFV-DRH20CP STV-DRH20CP SCV-DRH20CP
	SFV-DRH430AR STV-DRH430AR SCV-DRH430AR
	SFV-DRH630AR STV-DRH630AR SCV-DRH630AR
	SFV-DRH420A STV-DRH420A SCV-DRH420A
	SFV-DRH30CP STV-DRH30CP SCV-DRH30CP
	SFV-DRH440R STV-DRH440R SCV-DRH440R
	SFV-DRH640AR STV-DRH640AR SCV-DRH640AR
	SFV-DRH40CP STV-DRH40CP SCV-DRH40CP
	SFV-DRH440A STV-DRH440A SCV-DRH440A
	SFV-DRK30AR STV-DRK30AR SCV-DRK30AR
	SFV-DRK45AR STV-DRK45AR SCV-DRK45AR

CxV BLADE TIPS			A
NEW  	CFV-BL100	CCV-BL100	10mm (.40")
	CFV-BL250	CCV-BL250	25mm (1")
	CFV-BL350	CCV-BL350	35mm (1.4")
	CFV-BL400	CCV-BL400	40mm (1.6")
	CFV-BL500	CCV-BL500	50mm (2")

F = FR4 / Fiber Glass, for most standard applications T = Temperature Sensitive C = Ceramic for high thermal demand applications.