

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

130094-0478

Status:

Active

Overview:

Support Grips

Description:

Heavy Duty Support Grip, Double Eye, Double Weave, Split Lace, Cable Diameter 88.90-101.35m (3.500-3.990"), Approximate Break Strength 5,951.13kg (13,120 lbs)

Documents:

RoHS Certificate of Compliance (PDF)

Product Literature (PDF)

Agency Certification

CSA

LR32159

General

Product Family

Series

Eye Type

O-Ring

Overview

Product Literature Order No

Product Name

Type

UPC

Woodhead

Cable Grips

130094

Double

N/A

Support Grips

987650-8065

Heavy Duty

Support Grip

78678835447

Yes

Physical

Approximate Break Strength

Bale Length

Body Style

Cable Diameter

Color - Grommet

Gender

Material - Body

Material - Grip

Mesh Length

Net Weight

Number of Holes

Thread Size

5,951.13kg (13,120 lbs)

0.254m (10.00")

Straight

88.90-101.35mm (3.500-3.990")

N/A

N/A

N/A

Non-magnetic Tin Bronze Wire

1.143m (45.00")

131.540/kg


N/A

N/A

Material Info

Old Part Number

35447



EU RoHS

ELV and RoHS

Compliant

REACH SVHC

Not Reviewed

Low-Halogen Status

Not Reviewed

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com

For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

130094Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION