


CONTACT PLATING : gold 0.40 μ over nickel 1 μ .



8630-3099NLF	Power contact (AWG 8)	4.40	5.00	3.90	8.98
8630-3057NLF	Power contact (AWG 12)	2.80	3.65	2.40	3.18
8630-3061NLF	Power contact (AWG 14)	2.10	3.00	1.70	1.91
8630-3065NLF	Power contact (AWG 16)	1.70	2.60	1.50	1.34
PART NUMBER	Designation	$\phi A^{+0.10}_0$	$\phi B^{+0.10}_0$	ϕ ame mm	Section mm ²
WIRE					

NOTE:RoHS INFORMATIONS

- The "LF" product meets European union Directives and other country regulations as described in GS-22-008.
- The product is not intended to be exposed to a manufacturing solder process.
- Packaging spec: see GS-14-920.

rev	ecn no	dr	date
A	LS06-0022	MPE	2006/06/11
B	LS06-0095	LGO	2006/06/23
-	-	-	-
-	-	-	-
-	-	-	-
-	-	-	-

www.fciconnect.com		surface ISO 1302	tolerance std ISO 406 ISO 1101	projection mm
TOLERANCES UNLESS OTHERWISE SPECIFIED		ANGULAR	LINEAR	size A3
Dr M. PESSON 2006/06/11		0.X	±0.1	Scale 5
Eng M. PESSON 2006/06/11		0.XX	±0.1	ECN LS06-0095
Chr LEGARRE 2006/06/11		0.XX' ±2'	0.XXX	±0.1
Appr LEGARRE 2006/06/11		Product family D-SUB Spec ref -		
FCI		POWER CONTACT (taille 8)		Rev. B
removable contact		C01-8639-2159		
catalog no		CUSTOMER		sheet 1 of 1