

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [130023-0067](#)
Status: **Active**
Description: M16 Single-Ended Cordset, 14 Poles, Female (90°) to Pigtail, 22/14 AWG, PUR Cable, 5.0m (16.40') Length

Documents:
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)


General	
Product Family	Industrial Cordsets
Series	130023
Connector End A	M16
Connector End B	Pigtail
IP Rating	IP67
Product Name	M16
Protocol	N/A
Region	America, Asia, Europe
Type	Single Ended
UPC	78678834288

Physical	
Cable Diameter	9.40mm (.370")
Cable Length	5.0m (16.40')
Color - Cable Jacket	Black
Coupling Style	Threaded
Gender	Female-Pigtail
Keyway	Single
LED Indicator	No
Material - Cable Jacket	PUR
Material - Connector Body	PUR
Material - Contact	Copper Alloy
Material - Coupling Nut	Anodized Aluminum
Material - Plating Mating	Gold
Net Weight	583.500/g
Orientation	90° to Straight
Poles	14
Temperature Range - Operating	-40°C to +85°C
Wire Size AWG	22
Wire/Cable Type	Shielded-Stranded

Electrical	
Current - Maximum per Contact	3A
Voltage - Maximum	60V

Material Info	
Old Part Number	L04A01M78M050

Reference - Drawing Numbers	
Sales Drawing	SD-130023-004



EU RoHS
ELV and RoHS
Compliant
REACH SVHC
Not Reviewed
Low-Halogen Status
Not Reviewed



Need more information on product environmental compliance?
Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)
Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series
[130023Series](#)