



✓ Active

 Add to Part List

 Always EU RoHS/ELV Compliant (Statement of Compliance)

- Contactor Type = Sealed
- LEV200 Series
- DC Actuating System
- Number of Poles = 1
- Contact Arrangement = 1 Form X, SPST-NO-DM

[View all Features](#) | [Find Similar Products](#)

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

- None Available

- None Available



- None Available

- None Available

- None Available

- None Available

- Product Line Information

- Tooling

- Contactor Type = Sealed
- Terminal Type = 10-32 Stud

- Actuating System = DC
- Contact Rating = 500A
- Coil Voltage (VDC) = 24
- Coil Voltage, Max. (VDC) = 24

- Coil Termination = Wire

- Series = LEV200
- Torque = 80-100 in-lbs
- Mount Type = Bottom Mount

- Number of Poles = 1

- Contact Arrangement = 1 Form X, SPST-NO-DM
- Auxiliary Switch Contact Arrangement = None
- Coil Wire Length (mm [in]) = 390 [15.3]

- RoHS/ELV Compliance = RoHS compliant, ELV compliant
- Lead Free Solder Processes = Not relevant for lead free process
- RoHS/ELV Compliance History = Always was RoHS compliant

- Packaging Method = Individual

- Brand = Kilovac