


Chassis mounted filter



DFHF

High performance multistage chassis mounted filter for demanding industrial applications

Extra high performance multi purpose filter with two-stage circuitry. Enhanced common and differential mode attenuation.

Applications: Vary sensitive systems and installations, SMPS, environments with very high level of interference.


- 1 – 10 A current ratings
- UL, CSA, VDE, S, FI

Operating voltage: 250 VAC
Operating frequency: 0 – 400 Hz
Temperature range: -25°C - +85°C


Type	Rated current [A] (40°C)	Max. Leakage current [mA] (250 V, 50 Hz)	L [mH]	Cx [μF]	Cy [pF]	R [MΩ]	Weight [g]
DFHF-1	1	0,2	2 x 10	2 x 0,1	2 x 2200	1	85
DFHF-3	3	0,2	2 x 2	2 x 0,1	2 x 2200	1	85
DFHF-6	6	0,2	2 x 0,8	2 x 0,1	2 x 2200	1	85
DFHF-10	10	0,2	2 x 0,3	2 x 0,1	2 x 2200	1	85

Connectors: Faston 6,3 x 0,8mm


DFHF-1




DFHF-3



DFHF-6



DFHF-10



— asym.,

— symm.

