

## Laser Printable Labels - Introduction

### General Information:

Panduit Laser Labels are designed to function in most desk-top laser printers.

Polyester materials are provided on a clear liner to assure clear movement throughout your printer's paper path. Most Panduit Labels are intended for flat application labeling, with the exception of Self-Laminating Polyester Labels (GMY3) and Permanent Polyolefin Labels (GMPO).

All labels can also be used in a wide variety of copiers. If you need to make many of the same label, a copier might be the quickest solution. Note: Some copiers do reduce the legend slightly so we suggest you print your legend on paper and then test transferring it to your laser label sheet with your copier.

### Sheet Formats:

Panduit Laser Labels are provided in two sheet formats:

- PLL labels are provided on U.S. Letter Sheets which are 8.5" x 11.0" (215.9 mm x 279.4 mm).
- PEL labels are provided on DIN A4 Sheets which are 8.27" x 11.69" (210 mm x 297 mm).

### Test Labels on Your Printer:

The rapid advances in laser printing technology make it increasingly difficult to test all laser materials on the ever increasing number of individual printer models.

The suitability of a specific material in a particular printer and for a particular application depends greatly on the printer model and operating conditions. We recommend that each user test the suggested material on their printer and in each unique application.

To order sample sheets of a specific label call your local Panduit distributor or sales office.

**Choose from three types of Panduit Laser Printable Labels for excellent print quality using your own printer:**



### Self-Laminating Laser Printable Labels

- Panduit Blank Self-Laminating Laser Labels provide excellent print quality and clear, crisp legends. These labels are available in a thin polyester film for indoor/outdoor applications. Print on the white print-on area, then protect the legend using the clear over-laminate.



### Blank Laser Printable Labels

- Panduit Blank Laser Labels are available in specific sizes for different flat labeling applications.



### Litho Paper Laser Printable Labels

- These labels are made from standard litho paper and are available in common sizes. These labels can be used for a wide variety of general labeling applications.

## Suggested Applications for Laser Labels



Wire and Cable Labeling

### Recommended Materials

| Material        | Color         | Usage            | Part Number Listing on Page |
|-----------------|---------------|------------------|-----------------------------|
| GMPO Polyolefin | White         | Indoor           | 61                          |
| GMY3 Polyester  | White / Clear | Indoor / Outdoor | 60-61                       |



Flat Ribbon Cable Labeling

### Recommended Materials

| Material        | Color         | Usage            | Part Number Listing on Page |
|-----------------|---------------|------------------|-----------------------------|
| GMPO Polyolefin | White         | Indoor           | 61                          |
| GMY3 Polyester  | White / Clear | Indoor / Outdoor | 60-61                       |



Electronic Labeling

### Recommended Materials

| Material                          | Color  | Usage            | Part Number Listing on Page |
|-----------------------------------|--------|------------------|-----------------------------|
| GMPO Polyolefin                   | White  | Indoor           | 61                          |
| GMPOR Removable Polyolefin        | White  | Indoor           | 61                          |
| GMY3-C Polyester                  | Clear  | Indoor / Outdoor | 62                          |
| GMY2-W Polyester                  | White  | Indoor / Outdoor | 63-64                       |
| GMY2-Y Polyester                  | Yellow | Indoor / Outdoor | 64-65                       |
| GMY2-S Polyester                  | Silver | Indoor / Outdoor | 65                          |
| GMY2-STE Tamper Evident Polyester | Silver | Indoor / Outdoor | 66                          |



Name and Rating Plates

### Recommended Materials

| Material                          | Color  | Usage            | Part Number Listing on Page |
|-----------------------------------|--------|------------------|-----------------------------|
| GMPO Polyolefin                   | White  | Indoor           | 61                          |
| GMY3-C Polyester                  | Clear  | Indoor / Outdoor | 62                          |
| GMY2-W Polyester                  | White  | Indoor / Outdoor | 63-64                       |
| GMY2-Y Polyester                  | Yellow | Indoor / Outdoor | 64-65                       |
| GMY2-S Polyester                  | Silver | Indoor / Outdoor | 65                          |
| GMY2-STE Tamper Evident Polyester | Silver | Indoor / Outdoor | 66                          |

## Suggested Applications for Laser Labels (cont.)



Network Systems Labeling

### Recommended Materials

| Material         | Color | Usage            | Part Number Listing on Page |
|------------------|-------|------------------|-----------------------------|
| GMPO Polyolefin  | White | Indoor           | 67-69                       |
| GMY3-C Polyester | Clear | Indoor / Outdoor | 67-69                       |
| GMY2-W Polyester | White | Indoor / Outdoor | 67-69                       |



Asset Labeling

### Recommended Materials

| Material         | Color  | Usage            | Part Number Listing on Page |
|------------------|--------|------------------|-----------------------------|
| GMY3-C Polyester | Clear  | Indoor / Outdoor | 62                          |
| GMY2-W Polyester | White  | Indoor / Outdoor | 63-64                       |
| GMY2-Y Polyester | Yellow | Indoor / Outdoor | 64-65                       |



Bar Code Labeling

### Recommended Materials

| Material         | Color | Usage            | Part Number Listing on Page |
|------------------|-------|------------------|-----------------------------|
| GMPO Polyolefin  | White | Indoor           | 61                          |
| GMY2-W Polyester | White | Indoor / Outdoor | 63-64                       |



General Labeling

### Recommended Materials

| Material    | Color | Usage  | Part Number Listing on Page |
|-------------|-------|--------|-----------------------------|
| Litho Paper | White | Indoor | 62                          |

## Laser Label Material Selection Guide

Choose the material that best suits your application:

| Material Code | Material Type            | Temperature Range                  | Key Features                                                                                                 | Color       | Outdoor Rated | Hazardous Environment | UL Rec. | CSA |
|---------------|--------------------------|------------------------------------|--------------------------------------------------------------------------------------------------------------|-------------|---------------|-----------------------|---------|-----|
| —             | Litho Paper              | -65°F to 200°F<br>(-54°C to 93°C)  | Standard litho paper for general indoor labeling                                                             | White       | No            | No                    | No      | No  |
| GMPO          | Polyolefin               | -50°F to 120°F<br>(-46°C to 49°C)  | For general identification and wire marking; excellent print quality                                         | White       | No            | No                    | No      | No  |
| GMPOR         | Removable Polyolefin     | -40°F to 200°F<br>(-40°C to 93°C)  | Removable adhesive for temporary indoor applications; excellent print quality                                | White       | No            | No                    | No      | No  |
| GMY3          | Polyester                | 0°F to 275°F<br>(-18°C to 135°C)   | Used for high quality indoor/outdoor self-laminating labels                                                  | Clear       | Yes           | Yes                   | No      | No  |
| GMY3-C        | Polyester                | 0°F to 275°F<br>(-18°C to 135°C)   | Provides durability, high temperature resistance, and dimensional stability; Use on colored or clear surface | Clear       | Yes           | Yes                   | No      | No  |
| GMY3M         | Polyester                | 0°F to 275°F<br>(-18°C to 135°C)   | Provides durability, high temperature resistance, and dimensional stability; Use on colored or clear surface | Matte Clear | Yes           | Yes                   | No      | No  |
| GMY2-W        | Polyester                | 0°F to 275°F<br>(-18°C to 135°C)   | Provides durability, high temperature resistance, and dimensional stability                                  | White       | Yes           | Yes                   | Yes     | Yes |
| GMY2-Y        | Polyester                | 0°F to 275°F<br>(-18°C to 135°C)   | Provides durability, high temperature resistance, and dimensional stability                                  | Yellow      | Yes           | Yes                   | Yes     | Yes |
| GMY2-S        | Polyester                | 0°F to 275°F<br>(-18°C to 135°C)   | Metallized polyester provides opacity, durability, high temperature resistance, and dimensional stability    | Silver      | Yes           | Yes                   | No      | No  |
| GMY2-STE      | Tamper Evident Polyester | -40°F to 302°F<br>(-40°C to 150°C) | Destructible material; label cannot be completely removed; for tamper evident applications                   | Silver      | Yes           | No                    | No      | No  |



## Self-Laminating Labels

- Print on the white print-on area and over-laminate with clear portion for permanent, clean identification
- Preferred material chosen for most OEM applications
- Thin film with permanent adhesive

## Clear Polyester – Indoor/Outdoor Applications

U.S. Letter Sheet Format (8.5" x 11" / 215.9 mm x 279.4 mm)

| Part Number    | Material                         | Print-On Area Color | Label Size Width x Length In. (mm) | Print-On Area Width x Length In. (mm) | Nominal Cable Outside Diameter * In. (mm) | Dwg. Page No. | Std. Pkg. Qty.* |
|----------------|----------------------------------|---------------------|------------------------------------|---------------------------------------|-------------------------------------------|---------------|-----------------|
| PLL-3-Y3-5     | GMY3-C Self-Laminating Polyester | White               | 0.50 x 0.75 (12.7 x 19.1)          | 0.50 x 0.34 (12.7 x 8.64)             | 0.11 - 0.13 (2.7 - 3.3)                   | 70            | 5000            |
| PLL-33-Y3-5    |                                  | White               | 0.50 x 1.50 (12.7 x 38.1)          | 0.50 x 0.50 (12.7 x 12.7)             | 0.16 - 0.32 (4.0 - 8.1)                   | 70            | 5000            |
| PLL-10-Y3-2.5  |                                  | White               | 1.00 x 0.75 (25.4 x 19.1)          | 1.00 x 0.34 (25.4 x 8.64)             | 0.11 - 0.13 (2.7 - 3.3)                   | 70            | 2500            |
| PLL-10-Y3-5    |                                  | White               | 1.00 x 0.75 (25.4 x 19.1)          | 1.00 x 0.34 (25.4 x 8.64)             |                                           | 70            | 5000            |
| PLL-11-Y3-2.5† |                                  | White               | 1.00 x 1.00 (25.4 x 25.4)          | 1.00 x 0.34 (25.4 x 8.64)             | 0.11 - 0.21 (2.7 x 5.3)                   | 70            | 2500            |
| PLL-12-Y3-1    |                                  | White               | 1.00 x 1.33 (25.4 x 33.8)          | 1.00 x 0.50 (25.4 x 12.7)             | 0.16 - 0.26 (4.0 - 6.7)                   | 70            | 1000            |
| PLL-12-Y3-2.5† |                                  | White               | 1.00 x 1.33 (25.4 x 33.8)          | 1.00 x 0.50 (25.4 x 12.7)             |                                           | 70            | 2500            |
| PLL-39-Y3-1    |                                  | White               | 1.00 x 1.33 (25.4 x 33.8)          | 1.00 x 0.50 (25.4 x 12.7)             |                                           | 70            | 1000            |
| PLL-13-Y3-D    |                                  | White               | 1.00 x 3.17 (25.4 x 80.5)          | 1.00 x 0.97 (25.4 x 24.6)             | 0.31 - 0.70 (7.8 - 17.8)                  | 70            | 500             |
| PLL-13-Y3-1    |                                  | White               | 1.00 x 3.17 (25.4 x 80.5)          | 1.00 x 0.97 (25.4 x 24.6)             |                                           | 70            | 1000            |
| PLL-38-Y3-1    |                                  | White               | 1.00 x 5.45 (25.4 x 138.4)         | 1.00 x 1.00 (25.4 x 25.4)             | 0.32 - 1.42 (8.1 - 36.1)                  | 70            | 1000            |
| PLL-37-Y3-1    |                                  | White               | 1.88 x 3.17 (47.6 x 80.5)          | 1.88 x 0.97 (47.6 x 24.6)             | 0.31 - 0.70 (7.8 - 17.8)                  | 70            | 1000            |
| PLL-40-Y3-1    |                                  | White               | 2.00 x 1.50 (50.8 x 38.1)          | 2.00 x 0.50 (50.8 x 12.7)             | 0.16 - 0.32 (4.0 - 8.1)                   | 70            | 1000            |
| PLL-21-Y3-1    |                                  | White               | 2.00 x 3.17 (50.8 x 80.5)          | 2.00 x 1.00 (50.8 x 25.4)             | 0.32 - 0.69 (8.1 - 17.5)                  | 70            | 1000            |

\*Refer to Wire Size Selection Guide on [page 196](#) to review diameters of commonly used cables

†Labels available with TIA Specified Colored Print-On Area; to order, add the following letters after-Y3 in the part number: B for Blue, BR for Brown, G for Green, IG for Gray, OR for Orange, PR for Purple, RD for Red and Y for Yellow. i.e. PLL-11-Y3B-2.5 has a Blue Print-On Area.

## Self-Laminating Labels by Material (cont.)

### Clear Polyester – Indoor/Outdoor Applications (cont.)

DIN A4 Sheet Format (8.26" x 11.69" / 210 mm x 297 mm)

| Part Number    | Material                         | Print-On Area Color | Label Size Width x Length In. (mm) | Print-On Area Width x Length In. (mm) | Nominal Cable Outside Diameter* In. (mm) | Dwg. Page No. | Std. Pkg. Qty.* |
|----------------|----------------------------------|---------------------|------------------------------------|---------------------------------------|------------------------------------------|---------------|-----------------|
| PEL-17-Y3-2.5† | GMY3-C Self-Laminating Polyester | White               | 0.70 x 1.33 (17.8 x 33.9)          | 0.70 x 0.33 (17.8 x 8.5)              | 0.11 - 0.32 (2.8 - 8.1)                  | 71            | 2500            |
| PEL-18-Y3-1†   |                                  | White               | 0.90 x 2.17 (22.9 x 55.0)          | 0.90 x 0.50 (22.9 x 12.7)             | 0.16 - 0.53 (4.1 - 13.5)                 | 71            | 1000            |
| PEL-19-Y3-1†   |                                  | White               | 1.00 x 2.67 (25.4 x 67.7)          | 1.00 x 0.67 (25.4 x 16.9)             | 0.21 - 0.64 (5.3 - 16.2)                 | 71            | 1000            |
| PEL-20-Y3-1    |                                  | White               | 1.20 x 2.67 (30.5 x 67.7)          | 1.20 x 0.83 (30.5 x 21.1)             | 0.26 - 0.58 (6.6 - 14.7)                 | 71            | 1000            |
| PEL-21-Y3-0.5† |                                  | White               | 1.40 x 3.67 (35.6 x 93.1)          | 1.40 x 1.00 (35.6 x 25.4)             | 0.32 - 0.85 (8.1 - 21.6)                 | 71            | 500             |
| PEL-22-Y3-0.5  |                                  | White               | 1.40 x 5.50 (35.6 x 140.0)         | 1.40 x 1.00 (35.6 x 25.4)             | 0.32 - 1.40 (8.1 - 35.6)                 | 71            | 500             |
| PEL-23-Y3-0.5  |                                  | White               | 1.80 x 5.50 (45.7 x 140.0)         | 1.80 x 1.167 (45.7 x 29.6)            | 0.37 - 1.38 (9.4 - 35.0)                 | 71            | 500             |

\*Refer to Wire Size Selection Guide on [page 196](#) to review diameters of commonly used cables

†Labels available with TIA Specified Colored Print-On Areas; to order replace -Y3 with -BLU for Blue, -BRN for Brown, -GRN for Green, -GRY for Gray, -ORN for Orange, -PUR for Purple, -RED for Red, and -YEL for Yellow. i.e. PEL-17-BLU-2.5 has a Blue Print-On Area.

### Clear Polyolefin – Indoor Applications

DIN A4 Sheet Format (8.26" x 11.69" / 210 mm x 297 mm)

| Part Number  | Material        | Print-On Area Color | Label Size Width x Length In. (mm) | Print-On Area Width x Length In. (mm) | Nominal Cable Outside Diameter* In. (mm) | Dwg. Page No. | Std. Pkg. Qty.* |
|--------------|-----------------|---------------------|------------------------------------|---------------------------------------|------------------------------------------|---------------|-----------------|
| PEL-18-PO3-1 | GMPO Polyolefin | White               | 0.90 x 2.17 (22.9 x 55.0)          | 0.90 x 0.50 (22.9 x 12.7)             | 0.16 - 0.53 (4.1 - 13.5)                 | 71            | 1000            |

\*Refer to Wire Size Selection Guide on [page 196](#) to review diameters of commonly used cables

## Blank Labels by Material



- Non-laminated material used in indoor applications
- Permanent adhesive
- Excellent print quality, limited resistance to solvents and oil

### Polyolefin - Indoor Applications

U.S. Letter Sheet Format (8.5" x 11" / 215.9 mm x 279.4 mm)

| Part Number   | Material        | Color | Label Size Width x Length In. (mm) | Dwg. Page No. | Std. Pkg. Qty.* |
|---------------|-----------------|-------|------------------------------------|---------------|-----------------|
| PLL-33-PO-5   | GMPO Polyolefin | White | 0.50 x 1.50 (12.7 x 38.1)          | 72            | 5000            |
| PLL-8-PO-10   |                 |       | 1.00 x 0.38 (25.4 x 9.5)           | 72            | 10,000          |
| PLL-10-PO-5   |                 |       | 1.00 x 0.75 (25.4 x 19.1)          | 73            | 5000            |
| PLL-14-PO-5   |                 |       | 1.50 x 0.25 (38.1 x 6.4)           | 73            | 5000            |
| PLL-35-PO-2.5 |                 |       | 1.50 x 0.75 (38.1 x 19.1)          | 73            | 2500            |
| PLL-16-PO-2.5 |                 |       | 1.88 x 0.38 (47.6 x 9.5)           | 73            | 2500            |
| PLL-17-PO-2.5 |                 |       | 1.88 x 0.83 (47.6 x 21.1)          | 74            | 2500            |
| PLL-36-PO-1   |                 |       | 2.50 x 1.00 (63.5 x 25.4)          | 74            | 1000            |
| PLL-22-PO-1†  |                 |       | 7.88 x 0.50 (200.0 x 12.7)         | 74            | 1000            |
| PLL-25-PO-SH  |                 |       | 8.50 x 11.00 (215.9 x 279.4)       | 74            | 25              |

†Labels available in colors; to order add the following suffix to part number: -Y for Yellow, -R for Red, -B for Blue, -G for Green, -GR for Gray, -PR for Purple and -BR for Brown



- Used for temporary identification

### Removable Polyolefin - Indoor Applications

U.S. Letter Sheet Format (8.5" x 11" / 215.9 mm x 279.4 mm)

| Part Number    | Material                   | Color | Label Size Width x Length In. (mm) | Dwg. Page No. | Std. Pkg. Qty.* |
|----------------|----------------------------|-------|------------------------------------|---------------|-----------------|
| PLL-31-POR-10  | GMPOR Removable Polyolefin | White | 0.50 x 0.44 (12.7 x 11.1)          | 72            | 10,000          |
| PLL-9-POR-10   |                            |       | 1.00 x 0.50 (25.4 x 12.7)          | 73            | 10,000          |
| PLL-34-POR-10  |                            |       | 1.25 x 0.38 (31.8 x 9.5)           | 73            | 10,000          |
| PLL-14-POR-5   |                            |       | 1.50 x 0.25 (38.1 x 6.4)           | 73            | 5000            |
| PLL-35-POR-2.5 |                            |       | 1.50 x 0.75 (38.1 x 19.1)          | 73            | 2500            |
| PLL-36-POR-1   |                            |       | 2.50 x 1.00 (63.5 x 25.4)          | 74            | 1000            |
| PLL-19-POR-2.5 |                            |       | 3.00 x 0.38 (76.2 x 9.5)           | 74            | 2500            |
| PLL-25-POR-SH  |                            |       | 8.50 x 11.00 (215.9 x 279.4)       | 74            | 25              |

\*Order number of labels required in multiples of Std. Pkg. Qty.

## Blank Labels by Material (cont.)



- Used for shipping or labeling
- Excellent black/white contrast for bar code applications
- Most economical labeling solution

### Litho Paper - Indoor/Temporary Applications

U.S. Letter Sheet Format (8.5" x 11" / 215.9 mm x 279.4 mm)

| Part Number  | Material    | Color | Label Size Width x Length In. (mm) | Dwg. Page No. | Sheets Per Pkg. | Std. Pkg. Qty.* |
|--------------|-------------|-------|------------------------------------|---------------|-----------------|-----------------|
| LL2561-100G  | Litho Paper | White | 2.83 x 1.00 (72.0 x 25.4)          | 75            | 100             | 1 Pkg.          |
| LL2561-100   |             |       | 2.83 x 1.00 (72.0 x 25.4)          | 75            | 100             | 1 Pkg.          |
| LL2561-250   |             |       | 2.83 x 1.00 (72.0 x 25.4)          | 75            | 250             | 1 Pkg.          |
| LL2561-500   |             |       | 2.83 x 1.00 (72.0 x 25.4)          | 75            | 500             | 1 Pkg.          |
| LL256138-100 |             |       | 2.83 x 1.38 (72.0 x 34.9)          | 75            | 100             | 1 Pkg.          |
| LL25615-100G |             |       | 2.83 x 1.50 (72.0 x 38.1)          | 75            | 100             | 1 Pkg.          |
| LL4252-100G  |             |       | 4.25 x 2.00 (108.0 x 50.8)         | 75            | 100             | 1 Pkg.          |
| LL425275-250 |             |       | 4.25 x 2.00 (108.0 x 50.8)         | 75            | 250             | 1 Pkg.          |
| LL42513-100G |             |       | 4.25 x 13.00 (108.0 x 330.2)       | 75            | 100             | 1 Pkg.          |
| LL8511-100   |             |       | 8.50 x 11.00 (215.9 x 279.4)       | 75            | 100             | 1 Pkg.          |

\*Order number of packages required in multiples of Std. Pkg. Qty.

- Use on colored or clear surfaces
- Durable polyester material is UV and temperature resistant
- Apply to flat, clean surfaces only

### Clear Polyester - Indoor/Outdoor Applications

U.S. Letter Sheet Format (8.5" x 11" / 215.9 mm x 279.4 mm)

| Part Number    | Material       | Color | Label Size Width x Length In. (mm) | Dwg. Page No. | Std. Pkg. Qty.* |
|----------------|----------------|-------|------------------------------------|---------------|-----------------|
| PLL-24-Y3-1    | GMY3 Polyester | Clear | 0.56 x 0.19 (14.3 x 4.8)           | 72            | 1000            |
| PLL-24-Y3-5    |                |       | 0.56 x 0.19 (14.3 x 4.8)           | 72            | 5000            |
| PLL-23-Y3-1    |                |       | 0.56 x 0.56 (14.3 x 14.3)          | 72            | 1000            |
| PLL-23-Y3-5    |                |       | 0.56 x 0.56 (14.3 x 14.3)          | 72            | 5000            |
| PLL-9-Y3C-5    |                |       | 1.00 x 0.50 (25.4 x 12.7)          | 73            | 5000            |
| PLL-10-Y3C-2.5 |                |       | 1.00 x 0.75 (25.4 x 19.1)          | 73            | 2500            |
| PLL-11-Y3C-2.5 |                |       | 1.00 x 1.00 (25.4 x 25.4)          | 73            | 2500            |
| PLL-22-Y3-1    |                |       | 7.88 x 0.50 (200.0 x 12.7)         | 74            | 1000            |
| PLL-25-Y3C-SH  |                |       | 8.50 x 11.00 (215.9 x 279.4)       | 74            | 25              |

\*Order number of labels required in multiples of Std. Pkg. Qty.

DIN A4 Sheet Format (8.26" x 11.69" / 210 mm x 297 mm)

| Part Number  | Material       | Color | Label Size Width x Length In. (mm) | Dwg. Page No. | Std. Pkg. Qty.* |
|--------------|----------------|-------|------------------------------------|---------------|-----------------|
| PEL-A4-Y3-25 | GMY3 Polyester | Clear | 8.27 x 11.69 (210.0 x 297.0)       | 77            | 25              |

\*Order number of labels required in multiples of Std. Pkg. Qty.

- Matte clear finish
- Use on colored or clear surfaces
- Durable polyester material is UV and temperature resistant
- Apply to flat, clean surfaces only

### Matte Clear Polyester - Indoor/Outdoor Applications

DIN A4 Sheet Format (8.26" x 11.69" / 210 mm x 297 mm)

| Part Number   | Material        | Color       | Label Size Width x Length In. (mm) | Dwg. Page No. | Std. Pkg. Qty.* |
|---------------|-----------------|-------------|------------------------------------|---------------|-----------------|
| PEL-29-Y3M-10 | GMY3M Polyester | Matte Clear | 0.56 x 0.25 (14.3 x 6.4)           | 76            | 10,000          |
| PEL-28-Y3M-5  |                 |             | 0.56 x 0.56 (14.3 x 14.3)          | 76            | 5000            |
| PEL-10-Y3M-5  |                 |             | 0.70 x 0.50 (17.8 x 12.7)          | 76            | 5000            |
| PEL-2-Y3M-10  |                 |             | 1.00 x 0.25 (25.4 x 6.4)           | 76            | 10,000          |
| PEL-7-Y3M-5   |                 |             | 1.50 x 0.33 (38.1 x 8.5)           | 77            | 5000            |
| PEL-A4-Y3M-25 |                 |             | 8.27 x 11.69 (210.0 x 297.0)       | 77            | 25              |

\*Order number of labels required in multiples of Std. Pkg. Qty.

## Blank Labels by Material (cont.)



- Adhesive becomes permanent after 24 hours
- Durable polyester, ideal for the top of circuit boards
- Can be used (on top) before wave solder process
- UV resistant for outdoor applications
- Apply to flat, clean surfaces only

### White Polyester - Indoor/Outdoor Applications

U.S. Letter Sheet Format (8.5" x 11" / 215.9 mm x 279.4 mm)

| Part Number   | Material            | Color | Label Size<br>Width x Length<br>In. (mm) | Dwg.<br>Page<br>No. | Std.<br>Pkg.<br>Qty.* |
|---------------|---------------------|-------|------------------------------------------|---------------------|-----------------------|
| PLL-30-Y2-10  | GMY2-W<br>Polyester | White | 0.25 x 0.25 (6.4 x 6.4)                  | 75                  | 10,000                |
| PLL-1-Y2-10   |                     |       | 0.30 x 0.25 (7.6 x 6.4)                  | 75                  | 10,000                |
| PLL-2-Y2-10   |                     |       | 0.38 x 0.38 (9.5 x 9.5)                  | 72                  | 10,000                |
| PLL-31-Y2-10  |                     |       | 0.50 x 0.44 (12.7 x 11.1)                | 72                  | 10,000                |
| PLL-24-Y2-1   |                     |       | 0.56 x 0.19 (14.3 x 4.8)                 | 72                  | 1000                  |
| PLL-24-Y2-5   |                     |       | 0.56 x 0.19 (14.3 x 4.8)                 | 72                  | 5000                  |
| PLL-23-Y2-1   |                     |       | 0.56 x 0.56 (14.3 x 14.3)                | 72                  | 1000                  |
| PLL-23-Y2-5   |                     |       | 0.56 x 0.56 (14.3 x 14.3)                | 72                  | 5000                  |
| PLL-32-Y2-10  |                     |       | 0.65 x 0.20 (16.5 x 5.1)                 | 72                  | 10,000                |
| PLL-4-Y2-10   |                     |       | 0.65 x 0.25 (16.5 x 6.4)                 | 72                  | 10,000                |
| PLL-20-Y2-10  |                     |       | 0.80 x 0.20 (20.3 x 5.1)                 | 72                  | 10,000                |
| PLL-5-Y2-10   |                     |       | 0.80 x 0.25 (20.3 x 6.4)                 | 72                  | 10,000                |
| PLL-6-Y2-5    |                     |       | 0.80 x 0.50 (20.3 x 12.7)                | 72                  | 5000                  |
| PLL-6-Y2-10   |                     |       | 0.80 x 0.50 (20.3 x 12.7)                | 72                  | 10,000                |
| PLL-7-Y2-10   |                     |       | 1.00 x 0.25 (25.4 x 6.4)                 | 72                  | 10,000                |
| PLL-8-Y2-5    |                     |       | 1.00 x 0.38 (25.4 x 9.5)                 | 72                  | 5000                  |
| PLL-8-Y2-10   |                     |       | 1.00 x 0.38 (25.4 x 9.5)                 | 72                  | 10,000                |
| PLL-9-Y2-5    |                     |       | 1.00 x 0.50 (25.4 x 12.7)                | 73                  | 5000                  |
| PLL-9-Y2-10   |                     |       | 1.00 x 0.50 (25.4 x 12.7)                | 72                  | 10,000                |
| PLL-10-Y2-2.5 |                     |       | 1.00 x 0.75 (25.4 x 19.1)                | 73                  | 2500                  |
| PLL-11-Y2-2.5 |                     |       | 1.00 x 1.00 (25.4 x 25.4)                | 73                  | 2500                  |
| PLL-12-Y2-1   |                     |       | 1.00 x 1.33 (25.4 x 33.8)                | 73                  | 1000                  |
| PLL-12-Y2-2.5 |                     |       | 1.00 x 1.33 (25.4 x 33.8)                | 73                  | 2500                  |
| PLL-34-Y2-10  |                     |       | 1.25 x 0.38 (31.8 x 9.5)                 | 73                  | 10,000                |
| PLL-14-Y2-5   |                     |       | 1.50 x 0.25 (38.1 x 6.4)                 | 73                  | 5000                  |
| PLL-14-Y2-10  |                     |       | 1.50 x 0.25 (38.1 x 6.4)                 | 73                  | 10,000                |
| PLL-15-Y2-5   |                     |       | 1.88 x 0.25 (47.6 x 6.4)                 | 73                  | 5000                  |
| PLL-15-Y2-10  |                     |       | 1.88 x 0.25 (47.6 x 6.4)                 | 73                  | 10,000                |
| PLL-16-Y2-2.5 |                     |       | 1.88 x 0.38 (47.6 x 9.5)                 | 73                  | 2500                  |
| PLL-16-Y2-5   |                     |       | 1.88 x 0.38 (47.6 x 9.5)                 | 73                  | 5000                  |
| PLL-17-Y2-1   |                     |       | 1.88 x 0.83 (47.6 x 21.1)                | 73                  | 1000                  |
| PLL-17-Y2-2.5 |                     |       | 1.88 x 0.83 (47.6 x 21.1)                | 73                  | 2500                  |
| PLL-18-Y2-1   |                     |       | 1.88 x 1.33 (47.6 x 33.8)                | 74                  | 1000                  |
| PLL-18-Y2-1.5 |                     |       | 1.88 x 1.33 (47.6 x 33.8)                | 74                  | 1500                  |
| PLL-36-Y2-1   |                     |       | 2.50 x 1.00 (63.5 x 25.4)                | 74                  | 1000                  |
| PLL-26-Y2-1   |                     |       | 2.83 x 1.00 (72.0 x 25.4)                | 74                  | 1000                  |
| PLL-27-Y2-1   |                     |       | 2.83 x 1.38 (72.0 x 34.9)                | 74                  | 1000                  |
| PLL-28-Y2-1   |                     |       | 2.83 x 1.50 (72.0 x 38.1)                | 74                  | 1000                  |
| PLL-19-Y2-1   |                     |       | 3.00 x 0.38 (76.2 x 9.5)                 | 74                  | 1000                  |
| PLL-19-Y2-2.5 |                     |       | 3.00 x 0.38 (76.2 x 9.5)                 | 74                  | 2500                  |
| PLL-29-Y2-1   |                     |       | 4.25 x 2.00 (108.0 x 50.8)               | 74                  | 1000                  |
| PLL-22-Y2-1   |                     |       | 7.88 x 0.50 (200.0 x 12.7)               | 74                  | 1000                  |
| PLL-25-Y2-SH  |                     |       | 8.50 x 11.00 (215.9 x 279.4)             | 74                  | 25                    |

\*Order number of labels required in multiples of Std. Pkg. Qty.

## Blank Labels by Material (cont.)



- Adhesive becomes permanent after 24 hours
- Durable polyester, ideal for the top of circuit boards
- Can be used (on top) before wave solder process
- UV resistant for outdoor applications
- Apply to flat, clean surfaces only

### White Polyester - Indoor/Outdoor Applications (cont.)

DIN A4 Sheet Format (8.26" x 11.69" / 210 mm x 297 mm)

| Part Number   | Material            | Color | Label Size<br>Width x Length<br>In. (mm) | Dwg.<br>Page<br>No. | Std.<br>Pkg.<br>Qty.* |
|---------------|---------------------|-------|------------------------------------------|---------------------|-----------------------|
| PEL-9-Y2-10   | GMY2-W<br>Polyester | White | 0.50 x 0.50 (12.7 x 12.7)                | 76                  | 10,000                |
| PEL-29-Y2-10  |                     |       | 0.56 x 0.25 (14.3 x 6.4)                 | 76                  | 10,000                |
| PEL-28-Y2-5   |                     |       | 0.56 x 0.56 (14.3 x 14.3)                | 76                  | 5000                  |
| PEL-1-Y2-10   |                     |       | 0.70 x 0.25 (17.8 x 6.4)                 | 76                  | 10,000                |
| PEL-4-Y2-10   |                     |       | 0.70 x 0.33 (17.8 x 8.5)                 | 76                  | 10,000                |
| PEL-10-Y2-5   |                     |       | 0.70 x 0.50 (17.8 x 12.7)                | 76                  | 5000                  |
| PEL-5-Y2-10   |                     |       | 0.80 x 0.33 (20.3 x 8.5)                 | 76                  | 10,000                |
| PEL-2-Y2-10   |                     |       | 1.00 x 0.25 (25.4 x 6.4)                 | 76                  | 10,000                |
| PEL-6-Y2-5    |                     |       | 1.00 x 0.33 (25.4 x 8.5)                 | 76                  | 5000                  |
| PEL-11-Y2-5   |                     |       | 1.00 x 0.50 (25.4 x 12.7)                | 76                  | 5000                  |
| PEL-3-Y2-5    |                     |       | 1.44 x 0.25 (36.5 x 6.4)                 | 77                  | 5000                  |
| PEL-7-Y2-5    |                     |       | 1.50 x 0.33 (38.1 x 8.5)                 | 77                  | 5000                  |
| PEL-12-Y2-2.5 |                     |       | 1.50 x 0.50 (38.1 x 12.7)                | 77                  | 2500                  |
| PEL-8-Y2-2.5  |                     |       | 2.00 x 0.33 (50.8 x 8.5)                 | 77                  | 2500                  |
| PEL-13-Y2-2.5 |                     |       | 2.00 x 0.50 (50.8 x 12.7)                | 77                  | 2500                  |
| PEL-14-Y2-1   |                     |       | 2.00 x 0.83 (50.8 x 21.1)                | 77                  | 1000                  |
| PEL-15-Y2-1   |                     |       | 2.00 x 1.00 (50.8 x 25.4)                | 77                  | 1000                  |
| PEL-16-Y2-0.5 |                     |       | 2.50 x 1.33 (63.5 x 33.9)                | 77                  | 500                   |
| PEL-A4-Y2-25  |                     |       | 8.27 x 11.69 (210.0 x 297.0)             | 77                  | 25                    |



- Adhesive becomes permanent after 24 hours
- Durable polyester, ideal for the top of circuit boards
- Can be used (on top) before wave solder process
- UV resistant for outdoor applications
- Apply to flat, clean surfaces only

### Yellow Polyester - Indoor/Outdoor Applications

U.S. Letter Sheet Format (8.5" x 11" / 215.9 mm x 279.4 mm)

| Part Number    | Material            | Color  | Label Size<br>Width x Length<br>In. (mm) | Dwg.<br>Page<br>No. | Std.<br>Pkg.<br>Qty.* |
|----------------|---------------------|--------|------------------------------------------|---------------------|-----------------------|
| PLL-1-Y2Y-10   | GMY2-Y<br>Polyester | Yellow | 0.30 x 0.25 (7.6 x 6.4)                  | 75                  | 10,000                |
| PLL-2-Y2Y-10   |                     |        | 0.38 x 0.38 (9.5 x 9.5)                  | 72                  | 10,000                |
| PLL-32-Y2Y-10  |                     |        | 0.65 x 0.20 (16.5 x 5.1)                 | 72                  | 10,000                |
| PLL-4-Y2Y-10   |                     |        | 0.65 x 0.25 (16.5 x 6.4)                 | 72                  | 10,000                |
| PLL-20-Y2Y-10  |                     |        | 0.80 x 0.20 (20.3 x 5.1)                 | 72                  | 10,000                |
| PLL-5-Y2Y-10   |                     |        | 0.80 x 0.25 (20.3 x 6.4)                 | 72                  | 10,000                |
| PLL-6-Y2Y-5    |                     |        | 0.80 x 0.50 (20.3 x 12.7)                | 72                  | 5000                  |
| PLL-6-Y2Y-10   |                     |        | 0.80 x 0.50 (20.3 x 12.7)                | 72                  | 10,000                |
| PLL-7-Y2Y-10   |                     |        | 1.00 x 0.25 (25.4 x 6.4)                 | 72                  | 10,000                |
| PLL-8-Y2Y-5    |                     |        | 1.00 x 0.38 (25.4 x 9.5)                 | 72                  | 5000                  |
| PLL-8-Y2Y-10   |                     |        | 1.00 x 0.38 (25.4 x 9.5)                 | 72                  | 10,000                |
| PLL-9-Y2Y-5    |                     |        | 1.00 x 0.50 (25.4 x 12.7)                | 73                  | 5000                  |
| PLL-9-Y2Y-10   |                     |        | 1.00 x 0.50 (25.4 x 12.7)                | 73                  | 10,000                |
| PLL-34-Y2Y-10  |                     |        | 1.25 x 0.38 (31.8 x 9.5)                 | 73                  | 10,000                |
| PLL-14-Y2Y-5   |                     |        | 1.50 x 0.25 (38.1 x 6.4)                 | 73                  | 5000                  |
| PLL-15-Y2Y-5   |                     |        | 1.88 x 0.25 (47.6 x 6.4)                 | 73                  | 5000                  |
| PLL-16-Y2Y-2.5 |                     |        | 1.88 x 0.38 (47.6 x 9.5)                 | 73                  | 2500                  |
| PLL-16-Y2Y-5   |                     |        | 1.88 x 0.38 (47.6 x 9.5)                 | 73                  | 5000                  |
| PLL-17-Y2Y-2.5 |                     |        | 1.88 x 0.83 (47.6 x 21.1)                | 73                  | 2500                  |
| PLL-18-Y2Y-1   |                     |        | 1.88 x 1.33 (47.6 x 33.8)                | 74                  | 1000                  |
| PLL-18-Y2Y-1.5 |                     |        | 1.88 x 1.33 (47.6 x 33.8)                | 74                  | 1500                  |
| PLL-19-Y2Y-1   |                     |        | 3.00 x 0.38 (76.2 x 9.5)                 | 74                  | 1000                  |
| PLL-19-Y2Y-2.5 |                     |        | 3.00 x 0.38 (76.2 x 9.5)                 | 74                  | 2500                  |
| PLL-25-Y2Y-SH  |                     |        | 8.50 x 11.00 (215.9 x 279.4)             | 74                  | 25                    |

## Blank Labels by Material (cont.)



- Adhesive becomes permanent after 24 hours
- Durable polyester, ideal for the top of circuit boards
- UV resistant for outdoor applications
- Apply to flat, clean surfaces only



- Warning sign, reference EIA (Electronic Industries Assoc) Standard RS-471 and MIL Standard 129J



- UV opaque material used to cover EPROM windows
- Adhesive becomes permanent after 24 hours
- Durable polyester, ideal for the top of circuit boards
- Can be used (on top) before wave solder process
- UV resistant for outdoor applications
- Apply to flat, clean surfaces only

### Yellow Polyester - Indoor/Outdoor Applications (cont.)

DIN A4 Sheet Format (8.26" x 11.69" / 210 mm x 297 mm)

| Part Number    | Material         | Color  | Label Size Width x Length In. (mm) | Dwg. Page No. | Std. Pkg. Qty.* |
|----------------|------------------|--------|------------------------------------|---------------|-----------------|
| PEL-25-Y2Y-10  | GMY2-Y Polyester | Yellow | 0.35 x 0.59 (9.0 x 15.0)           | 76            | 10,000          |
| PEL-26-Y2Y-5   |                  |        | 0.43 x 0.75 (11.0 x 19.1)          | 76            | 5000            |
| PEL-27-Y2Y-5   |                  |        | 0.43 x 1.50 (11.0 x 38.1)          | 76            | 5000            |
| PEL-4-Y2Y-10   |                  |        | 0.70 x 0.33 (17.8 x 8.5)           | 76            | 10,000          |
| PEL-10-Y2Y-5   |                  |        | 0.70 x 0.50 (17.8 x 12.7)          | 76            | 5000            |
| PEL-24-Y2Y-10  |                  |        | 0.79 x 0.31 (20.0 x 8.0)           | 76            | 10,000          |
| PEL-5-Y2Y-10   |                  |        | 0.80 x 0.33 (20.3 x 8.5)           | 76            | 10,000          |
| PEL-2-Y2Y-10   |                  |        | 1.00 x 0.25 (25.4 x 6.4)           | 76            | 10,000          |
| PEL-11-Y2Y-5   |                  |        | 1.00 x 0.50 (25.4 x 12.7)          | 76            | 5000            |
| PEL-7-Y2Y-5    |                  |        | 1.50 x 0.33 (38.1 x 8.5)           | 77            | 5000            |
| PEL-12-Y2Y-2.5 |                  |        | 1.50 x 0.50 (38.1 x 12.7)          | 77            | 2500            |
| PEL-15-Y2Y-1   |                  |        | 2.00 x 1.00 (50.8 x 25.4)          | 77            | 1000            |
| PEL-A4-Y2Y-25  |                  |        | 8.27 x 11.69 (210.0 x 297.0)       | 77            | 25              |

### Static Sensitive Label

DIN A4 Sheet Format (8.26" x 11.69" / 210 mm x 297 mm)

| Part Number | Material         | Color  | Label Size Width x Length In. (mm) | Printable Area Width x Length In. (mm) | Dwg. Page No. | Std. Pkg. Qty.* |
|-------------|------------------|--------|------------------------------------|----------------------------------------|---------------|-----------------|
| PESS-SEL    | GMY2-Y Polyester | Yellow | 1.00 x 0.50 (25.4 x 12.7)          | 1.00 x 0.25 (25.4 x 6.4)               | 76            | 2500            |

### Silver Polyester - Indoor/Outdoor Applications

U.S. Letter Sheet Format (8.5" x 11" / 215.9 mm x 279.4 mm)

| Part Number    | Material         | Color  | Label Size Width x Length In. (mm) | Dwg. Page No. | Std. Pkg. Qty.* |
|----------------|------------------|--------|------------------------------------|---------------|-----------------|
| PLL-9-Y2S-10   | GMY2-S Polyester | Silver | 1.00 x 0.50 (25.4 x 12.7)          | 73            | 10,000          |
| PLL-35-Y2S-2.5 |                  |        | 1.50 x 0.75 (38.1 x 19.1)          | 73            | 2500            |
| PLL-36-Y2S-1   |                  |        | 2.50 x 1.00 (63.5 x 25.4)          | 74            | 1000            |
| PLL-25-Y2S-SH  |                  |        | 8.50 x 11.00 (215.9 x 279.4)       | 74            | 25              |

DIN A4 Sheet Format (8.26" x 11.69" / 210 mm x 297 mm)

| Part Number   | Material         | Color  | Label Size Width x Length In. (mm) | Dwg. Page No. | Std. Pkg. Qty.* |
|---------------|------------------|--------|------------------------------------|---------------|-----------------|
| PEL-9-Y1-10   | GMY2-S Polyester | Silver | 0.50 x 0.50 (12.7 x 12.7)          | 76            | 10,000          |
| PEL-1-Y1-10   |                  |        | 0.70 x 0.25 (17.8 x 6.4)           | 76            | 10,000          |
| PEL-4-Y1-10   |                  |        | 0.70 x 0.33 (17.8 x 8.5)           | 76            | 10,000          |
| PEL-10-Y1-5   |                  |        | 0.70 x 0.50 (17.8 x 12.7)          | 76            | 5000            |
| PEL-5-Y1-10   |                  |        | 0.80 x 0.33 (20.3 x 8.5)           | 76            | 10,000          |
| PEL-2-Y1-10   |                  |        | 1.00 x 0.25 (25.4 x 6.4)           | 76            | 10,000          |
| PEL-6-Y1-5    |                  |        | 1.00 x 0.33 (25.4 x 8.5)           | 76            | 5000            |
| PEL-11-Y1-5   |                  |        | 1.00 x 0.50 (25.4 x 12.7)          | 76            | 5000            |
| PEL-3-Y1-5    |                  |        | 1.44 x 0.25 (36.5 x 6.4)           | 77            | 5000            |
| PEL-7-Y1-5    |                  |        | 1.50 x 0.33 (38.1 x 8.5)           | 77            | 5000            |
| PEL-12-Y1-2.5 |                  |        | 1.50 x 0.50 (38.1 x 12.7)          | 77            | 2500            |
| PEL-8-Y1-2.5  |                  |        | 2.00 x 0.33 (50.8 x 8.5)           | 77            | 2500            |
| PEL-13-Y1-2.5 |                  |        | 2.00 x 0.50 (50.8 x 12.7)          | 77            | 2500            |
| PEL-14-Y1-1   |                  |        | 2.00 x 0.83 (50.8 x 21.1)          | 77            | 1000            |
| PEL-15-Y1-1   |                  |        | 2.00 x 1.00 (50.8 x 25.4)          | 77            | 1000            |
| PEL-16-Y1-0.5 |                  |        | 2.50 x 1.33 (63.5 x 33.9)          | 77            | 500             |
| PEL-A4-Y1-25  |                  |        | 8.27 x 11.69 (210.0 x 297.0)       | 77            | 25              |

\*Order number of labels required in multiples of Std. Pkg. Qty.

## Blank Labels by Material (cont.)



- For tamper evident applications

### Tamper Evident Polyester - Indoor/Outdoor Applications

DIN A4 Sheet Format (8.26" x 11.69" / 210 mm x 297 mm)

| Part Number    | Material                                   | Color  | Label Size<br>Width x Length<br>In. (mm) | Dwg.<br>Page<br>No. | Std.<br>Pkg.<br>Qty.* |
|----------------|--------------------------------------------|--------|------------------------------------------|---------------------|-----------------------|
| PEL-9-Y1C-10   | GMY2-STE<br>Tamper<br>Evident<br>Polyester | Silver | 0.50 x 0.50 (12.7 x 12.7)                | 76                  | 10,000                |
| PEL-4-Y1C-10   |                                            |        | 0.70 x 0.33 (17.8 x 8.5)                 | 76                  | 10,000                |
| PEL-6-Y1C-5    |                                            |        | 1.00 x 0.33 (25.4 x 8.5)                 | 76                  | 5000                  |
| PEL-11-Y1C-5   |                                            |        | 1.00 x 0.50 (25.4 x 12.7)                | 76                  | 5000                  |
| PEL-3-Y1C-5    |                                            |        | 1.40 x 0.25 (36.5 x 6.4)                 | 77                  | 5000                  |
| PEL-8-Y1C-2.5  |                                            |        | 2.00 x 0.33 (50.8 x 8.5)                 | 77                  | 2500                  |
| PEL-15-Y1C-1   |                                            |        | 2.00 x 1.00 (50.8 x 25.4)                | 77                  | 1000                  |
| PEL-16-Y1C-0.5 |                                            |        | 2.50 x 1.33 (63.5 x 33.9)                | 77                  | 500                   |
| PEL-A4-Y1C-25  |                                            |        | 8.27 x 11.69 (210.0 x 297.0)             | 77                  | 25                    |



### Full Sheets

- Used for a wide variety of applications
- Full size sheets are available in 7 materials suitable for laser printing
- Ideal for prototyping and low volume custom labeling
- Custom large or irregular label sizes

### U.S. Letter Sheet Format (8.5" x 11" / 215.9 mm x 279.4 mm)

| Part Number   | Material              | Color  | Label Size<br>Width x Length<br>In. (mm) | Dwg.<br>Page<br>No. | Std.<br>Pkg.<br>Qty.* |
|---------------|-----------------------|--------|------------------------------------------|---------------------|-----------------------|
| PLL-25-PO-SH  | GMPO Polyolefin       | White  | 8.50 x 11.00 (215.9 x 279.4)             | 74                  | 25                    |
| PLL-25-Y2S-SH | GMY2-S Polyester      | Silver | 8.50 x 11.00 (215.9 x 279.4)             | 74                  | 25                    |
| PLL-25-Y3C-SH | GMY3-C Polyester      | Clear  | 8.50 x 11.00 (215.9 x 279.4)             | 74                  | 25                    |
| PLL-25-Y2-SH  | GMY2-W Polyester      | White  | 8.50 x 11.00 (215.9 x 279.4)             | 74                  | 25                    |
| PLL-25-POR-SH | GMPOR Rem. Polyolefin | White  | 8.50 x 11.00 (215.9 x 279.4)             | 74                  | 25                    |
| PLL-25-Y2Y-SH | GMY2-Y Polyester      | Yellow | 8.50 x 11.00 (215.9 x 279.4)             | 74                  | 25                    |

### DIN A4 Sheet Format (8.26" x 11.69" / 210 mm x 297 mm)

| Part Number   | Material                             | Color       | Label Size<br>Width x Length<br>In. (mm) | Dwg.<br>Page<br>No. | Std.<br>Pkg.<br>Qty.* |
|---------------|--------------------------------------|-------------|------------------------------------------|---------------------|-----------------------|
| PEL-A4-Y3-25  | GMY3-C Polyester                     | Clear       | 8.27 x 11.69 (210.0 x 297.0)             | 77                  | 25                    |
| PEL-A4-Y3M-25 | GMY3M Polyester                      | Matte Clear | 8.27 x 11.69 (210.0 x 297.0)             | 77                  | 25                    |
| PEL-A4-Y1-25  | GMY2-S Polyester                     | Silver      | 8.27 x 11.69 (210.0 x 297.0)             | 77                  | 25                    |
| PEL-A4-Y2-25  | GMY2-W Polyester                     | White       | 8.27 x 11.69 (210.0 x 297.0)             | 77                  | 25                    |
| PEL-A4-Y2Y-25 | GMY2-Y Polyester                     | Yellow      | 8.27 x 11.69 (210.0 x 297.0)             | 77                  | 25                    |
| PEL-A4-Y1C-25 | GMY2-STE<br>Tamper Evident Polyester | Silver      | 8.27 x 11.69 (210.0 x 297.0)             | 77                  | 25                    |

## TIA/EIA-606 Compliant Network Systems Labeling



### What is TIA/EIA-606?

TIA/EIA-606 is a standard from the Telecommunications Industry Association which requires labeling and administration of the telecommunication infrastructure in commercial buildings. TIA-606 applies to Cables, Connectors, Hub Facilities, Termination Facilities (Patch Panels), Conduits and Pathways.

**Panduit manufactures a broad range of labeling products to help you conform to TIA/EIA-606.**

Along with the labels already shown in this section, the following pages feature labels designed specifically for Network Systems Labeling. Many of these labels can be used with Dot-Matrix and Laser Printers.

*For more information on the complete line of **PAN-NET™** Network Cabling System Products, ask for the Communication Products Catalog.*

## Termination Hardware Labeling



### Adhesive 110 Block Labels

Designed to work in Laser Printers Only

| Part Number   | Material        | TIA Color | Label Width In. (mm) | Label Length In. (mm) | Vertical Repeat In. (mm) | No. of Col. | No. of Rows | Labels Per Sheet | Std. Pkg. Qty.* |
|---------------|-----------------|-----------|----------------------|-----------------------|--------------------------|-------------|-------------|------------------|-----------------|
| PLL-22-Y3-1   | GMYP3 Polyester | Clear     | 7.88 (200.0)         | 0.50 (12.7)           | 0.50 (12.7)              | 1           | 20          | 20               | 1000            |
| PLL-22-P0-1   | GMPO Polyolefin | White     | 7.88 (200.0)         | 0.50 (12.7)           | 0.50 (12.7)              | 1           | 20          | 20               | 1000            |
| PLL-22-P0-1B  |                 | Blue      | 7.88 (200.0)         | 0.50 (12.7)           | 0.50 (12.7)              | 1           | 20          | 20               | 1000            |
| PLL-22-P0-1BR |                 | Brown     | 7.88 (200.0)         | 0.50 (12.7)           | 0.50 (12.7)              | 1           | 20          | 20               | 1000            |
| PLL-22-P0-1G  |                 | Green     | 7.88 (200.0)         | 0.50 (12.7)           | 0.50 (12.7)              | 1           | 20          | 20               | 1000            |
| PLL-22-P0-1GR |                 | Gray      | 7.88 (200.0)         | 0.50 (12.7)           | 0.50 (12.7)              | 1           | 20          | 20               | 1000            |
| PLL-22-P0-1OR |                 | Orange    | 7.88 (200.0)         | 0.50 (12.7)           | 0.50 (12.7)              | 1           | 20          | 20               | 1000            |
| PLL-22-P0-1PR |                 | Purple    | 7.88 (200.0)         | 0.50 (12.7)           | 0.50 (12.7)              | 1           | 20          | 20               | 1000            |
| PLL-22-P0-1R  |                 | Red       | 7.88 (200.0)         | 0.50 (12.7)           | 0.50 (12.7)              | 1           | 20          | 20               | 1000            |
| PLL-22-P0-1Y  |                 | Yellow    | 7.88 (200.0)         | 0.50 (12.7)           | 0.50 (12.7)              | 1           | 20          | 20               | 1000            |

### Adhesive Labels

- Eliminate the need for standard paper designation strips
- Labels are placed on top of label holders



### Non-Adhesive 110 Punch Down Block Labels

Designed to work in Laser and Dot-Matrix Printers

| Part Number | Material         | Color  | Label Width In. (mm) | Label Length In. (mm) | Vertical Repeat In. (mm) | Labels Per Row | Rows Per Fanfold | Web Width In. (mm) | Std. Pkg. Qty.* |
|-------------|------------------|--------|----------------------|-----------------------|--------------------------|----------------|------------------|--------------------|-----------------|
| DS110       | Semi-Rigid Paper | White  | 7.88 (200.0)         | 0.50 (12.7)           | 0.50 (12.7)              | 1              | 15               | 8.50 (215.9)       | 150             |
| DS110-BR    |                  | Brown  | 7.88 (200.0)         | 0.50 (12.7)           | 0.50 (12.7)              | 1              | 15               | 8.50 (215.9)       | 150             |
| DS110-BU    |                  | Blue   | 7.88 (200.0)         | 0.50 (12.7)           | 0.50 (12.7)              | 1              | 15               | 8.50 (215.9)       | 150             |
| DS110-GR    |                  | Green  | 7.88 (200.0)         | 0.50 (12.7)           | 0.50 (12.7)              | 1              | 15               | 8.50 (215.9)       | 150             |
| DS110-IG    |                  | Gray   | 7.88 (200.0)         | 0.50 (12.7)           | 0.50 (12.7)              | 1              | 15               | 8.50 (215.9)       | 150             |
| DS110-OR    |                  | Orange | 7.88 (200.0)         | 0.50 (12.7)           | 0.50 (12.7)              | 1              | 15               | 8.50 (215.9)       | 150             |
| DS110-RD    |                  | Red    | 7.88 (200.0)         | 0.50 (12.7)           | 0.50 (12.7)              | 1              | 15               | 8.50 (215.9)       | 150             |
| DS110-VL    |                  | Violet | 7.88 (200.0)         | 0.50 (12.7)           | 0.50 (12.7)              | 1              | 15               | 8.50 (215.9)       | 150             |
| DS110-YL    |                  | Yellow | 7.88 (200.0)         | 0.50 (12.7)           | 0.50 (12.7)              | 1              | 15               | 8.50 (215.9)       | 150             |

### Non-Adhesive Labels

- To use with Laser Printer, simply tear sheets apart at fanfold perforation and use manual feed supply on printer

## Network Systems Labeling — Termination Hardware (cont.)



### Adhesive Label for Patch Panels and Modular Furniture Faceplates

- Label is perforated on black lines to be used in 2 position, 4 position, or 6 position applications

### Designed to work in Laser and Dot-Matrix Printers

| Part Number | Material        | Color  | Label Width In. (mm) | Label Length In. (mm) | Horizontal Repeat In. (mm) | Vertical Repeat In. (mm) | No. of Col. | No. of Rows | Labels Per Sheet | Std. Pkg. Qty.* |
|-------------|-----------------|--------|----------------------|-----------------------|----------------------------|--------------------------|-------------|-------------|------------------|-----------------|
| CPPLF-5     | GMPO Polyolefin | White  | 0.61 (15.5)          | 0.33 (8.4)            | 0.61 (15.5)                | 0.33 (8.4)               | 12          | 25          | 300              | 5000            |
| CPPLF-5BU   |                 | Blue   | 0.61 (15.5)          | 0.33 (8.4)            | 0.61 (15.5)                | 0.33 (8.4)               | 12          | 25          | 300              | 5000            |
| CPPLF-5EI   |                 | Ivory  | 0.61 (15.5)          | 0.33 (8.4)            | 0.61 (15.5)                | 0.33 (8.4)               | 12          | 25          | 300              | 5000            |
| CPPLF-5GR   |                 | Green  | 0.61 (15.5)          | 0.33 (8.4)            | 0.61 (15.5)                | 0.33 (8.4)               | 12          | 25          | 300              | 5000            |
| CPPLF-5IG   |                 | Gray   | 0.61 (15.5)          | 0.33 (8.4)            | 0.61 (15.5)                | 0.33 (8.4)               | 12          | 25          | 300              | 5000            |
| CPPLF-5OR   |                 | Orange | 0.61 (15.5)          | 0.33 (8.4)            | 0.61 (15.5)                | 0.33 (8.4)               | 12          | 25          | 300              | 5000            |
| CPPLF-5VL   |                 | Violet | 0.61 (15.5)          | 0.33 (8.4)            | 0.61 (15.5)                | 0.33 (8.4)               | 12          | 25          | 300              | 5000            |
| CPPLF-5RD   |                 | Red    | 0.61 (15.5)          | 0.33 (8.4)            | 0.61 (15.5)                | 0.33 (8.4)               | 12          | 25          | 300              | 5000            |
| CPPLF-5YL   |                 | Yellow | 0.61 (15.5)          | 0.33 (8.4)            | 0.61 (15.5)                | 0.33 (8.4)               | 12          | 25          | 300              | 5000            |

## Termination Position Labeling



### MINI-JACK™ Modular Jack and OPTI-JACK™ Fiber Optic Connector Labels



- Identify individual jacks and connectors
- Wrap around design allows for quick and secure installation
- Labels attach directly to jacks

| Part Number  | Material        | Color | Label Width In. (mm) | Label Length In. (mm) | Horizontal Repeat In. (mm) | Vertical Repeat In. (mm) | No. of Col. | No. of Rows | Labels Per Sheet | Std. Pkg. Qty.* |
|--------------|-----------------|-------|----------------------|-----------------------|----------------------------|--------------------------|-------------|-------------|------------------|-----------------|
| PLL-46-Y3C-1 | GMYP3 Polyester | Clear | 1.38 (34.9)          | 0.19 (4.8)            | 1.53 (38.9)                | 0.19 (4.8)               | 5           | 53          | 265              | 1000            |
| PLL-46-Y2-1  | GMYP2 Polyester | White | 1.38 (34.9)          | 0.19 (4.8)            | 1.53 (38.9)                | 0.19 (4.8)               | 5           | 53          | 265              | 1000            |



### Surface Mount Box Labels

U.S. Letter Sheet Format (8.5" x 11" / 215.9 mm x 279.4 mm)

| Part Number | Material        | Color | Label Size Width x Length In. (mm) | Dwg. Page No. | Std. Pkg. Qty.* |
|-------------|-----------------|-------|------------------------------------|---------------|-----------------|
| PLL-23-Y3-1 | GMYP3 Polyester | Clear | 0.56 x 0.56 (14.3 x 14.3)          | 72            | 1000            |
| PLL-23-Y3-5 |                 | Clear |                                    | 72            | 5000            |
| PLL-23-Y2-1 | GMYP2 Polyester | White | 0.56 x 0.56 (14.3 x 14.3)          | 72            | 1000            |
| PLL-23-Y2-5 |                 | White |                                    | 72            | 5000            |

## Network Systems Labeling — Termination Position Labeling (cont.)



### Faceplates Labels



- For use with **MINI-COM®** Executive and Designer Series Faceplates
- Adhesive label designed to fit on vinyl insert provided with faceplate
- Single and Double Gang versions available
- Can also be used to identify **MINI-COM** Surface Mount Boxes

### Adhesive Faceplate Labels

Designed to work in Laser and Ink Jet Printers

| Part Number | Faceplate Type | Material           | Color | Label Width In. (mm) | Label Length In. (mm) | Horizontal Repeat In. (mm) | Vertical Repeat In. (mm) | No. of Col. | No. of Rows | Labels Per Sheet | Std. Pkg. Qty.* |
|-------------|----------------|--------------------|-------|----------------------|-----------------------|----------------------------|--------------------------|-------------|-------------|------------------|-----------------|
| JLEFPS-1    | Single Gang    | GMPO5-W Polyolefin | White | 1.80 (45.7)          | 0.38 (9.5)            | 2.01(51.1)                 | 0.45 (11.6)              | 4           | 21          | 84               | 1000            |
| JLEFPD-1    | Double Gang    |                    | White | 0.30 (7.6)           | 2.90 (73.7)           | 0.38 (9.5)                 | 3.30 (83.8)              | 21          | 3           | 63               | 1000            |


### Non-Adhesive Faceplate Labels

Designed to work in Laser and Dot-Matrix Printers

| Part Number | Faceplate Type | Material         | Color | Label Width In. (mm) | Label Length In. (mm) | Horizontal Repeat In. (mm) | Vertical Repeat In. (mm) | No. of Col. | No. of Rows | Labels Per Sheet | Std. Pkg. Qty.* |
|-------------|----------------|------------------|-------|----------------------|-----------------------|----------------------------|--------------------------|-------------|-------------|------------------|-----------------|
| EFPT-1      | Single Gang    | Semi-Rigid Paper | White | 1.80 (45.7)          | 0.38 (9.5)            | 1.80 (45.7)                | 0.38 (9.5)               | 4           | 19          | 76               | 1000            |
| EFPT10-1    | Double Gang    |                  | White | 2.90 (73.7)          | 0.30 (7.6)            | 2.90 (73.7)                | 0.30 (7.6)               | 2           | 24          | 48               | 1000            |

*For more information on the complete line of **PAN-NET™** Network Cabling System Products, ask for the Communication Products Catalog.*


## Self-Laminating Labels by Size



### U.S. Letter Sheet Format (8.5" x 11" / 215.9 mm x 279.4 mm)

| Part Number     | Material  | Print-On Area Color | Label Width A In. (mm) | Label Length B In. (mm) | Print-On Area Length C In. (mm) | Horizontal Repeat D In. (mm) | Vertical Repeat E In. (mm) | No. of Col. | No. of Rows | Labels Per Sheet | Sheets Per Pkg. | Std. Pkg. Qty.* |
|-----------------|-----------|---------------------|------------------------|-------------------------|---------------------------------|------------------------------|----------------------------|-------------|-------------|------------------|-----------------|-----------------|
| PLL-3-Y3-5      | Polyester | White               | 0.50 (12.7)            | 0.75 (19.1)             | 0.34 (8.64)                     | 0.60 (15.2)                  | 0.75 (19.1)                | 13          | 12          | 156              | 33              | 5000            |
| PLL-33-Y3-5     | Polyester | White               | 0.50 (12.7)            | 1.50 (38.1)             | 0.50 (12.7)                     | 0.60 (15.2)                  | 1.50 (38.1)                | 13          | 6           | 78               | 65              | 5000            |
| PLL-10-Y3-2.5   | Polyester | White               | 1.00 (25.4)            | 0.75 (19.1)             | 0.34 (8.64)                     | 1.10 (27.9)                  | 0.75 (19.1)                | 7           | 12          | 84               | 30              | 2500            |
| PLL-10-Y3-5     | Polyester | White               | 1.00 (25.4)            | 0.75 (19.1)             | 0.34 (8.64)                     | 1.10 (27.9)                  | 0.75 (19.1)                | 7           | 12          | 84               | 60              | 5000            |
| PLL-11-Y3-2.5   | Polyester | White               | 1.00 (25.4)            | 1.00 (25.4)             | 0.34 (8.64)                     | 1.10 (27.9)                  | 1.00 (25.4)                | 7           | 10          | 70               | 36              | 2500            |
| PLL-11-Y3B-2.5  | Polyester | TIA Blue            | 1.00 (25.4)            | 1.00 (25.4)             | 0.34 (8.64)                     | 1.10 (27.9)                  | 1.00 (25.4)                | 7           | 10          | 70               | 36              | 2500            |
| PLL-11-Y3BR-2.5 | Polyester | TIA Brown           | 1.00 (25.4)            | 1.00 (25.4)             | 0.34 (8.64)                     | 1.10 (27.9)                  | 1.00 (25.4)                | 7           | 10          | 70               | 36              | 2500            |
| PLL-11-Y3G-2.5  | Polyester | TIA Green           | 1.00 (25.4)            | 1.00 (25.4)             | 0.34 (8.64)                     | 1.10 (27.9)                  | 1.00 (25.4)                | 7           | 10          | 70               | 36              | 2500            |
| PLL-11-Y3IG-2.5 | Polyester | TIA Gray            | 1.00 (25.4)            | 1.00 (25.4)             | 0.34 (8.64)                     | 1.10 (27.9)                  | 1.00 (25.4)                | 7           | 10          | 70               | 36              | 2500            |
| PLL-11-Y3OR-2.5 | Polyester | TIA Orange          | 1.00 (25.4)            | 1.00 (25.4)             | 0.34 (8.64)                     | 1.10 (27.9)                  | 1.00 (25.4)                | 7           | 10          | 70               | 36              | 2500            |
| PLL-11-Y3PR-2.5 | Polyester | TIA Purple          | 1.00 (25.4)            | 1.00 (25.4)             | 0.34 (8.64)                     | 1.10 (27.9)                  | 1.00 (25.4)                | 7           | 10          | 70               | 36              | 2500            |
| PLL-11-Y3RD-2.5 | Polyester | TIA Red             | 1.00 (25.4)            | 1.00 (25.4)             | 0.34 (8.64)                     | 1.10 (27.9)                  | 1.00 (25.4)                | 7           | 10          | 70               | 36              | 2500            |
| PLL-11-Y3Y-2.5  | Polyester | TIA Yellow          | 1.00 (25.4)            | 1.00 (25.4)             | 0.34 (8.64)                     | 1.10 (27.9)                  | 1.00 (25.4)                | 7           | 10          | 70               | 36              | 2500            |
| PLL-12-Y3-1     | Polyester | White               | 1.00 (25.4)            | 1.33 (33.8)             | 0.47 (11.9)                     | 1.10 (27.9)                  | 1.33 (33.8)                | 7           | 7           | 49               | 21              | 1000            |
| PLL-12-Y3-2.5   | Polyester | White               | 1.00 (25.4)            | 1.33 (33.8)             | 0.47 (11.9)                     | 1.10 (27.9)                  | 1.33 (33.8)                | 7           | 7           | 49               | 52              | 2500            |
| PLL-12-Y3B-2.5  | Polyester | TIA Blue            | 1.00 (25.4)            | 1.33 (33.8)             | 0.47 (11.9)                     | 1.10 (27.9)                  | 1.33 (33.8)                | 7           | 7           | 49               | 52              | 2500            |
| PLL-12-Y3BR-2.5 | Polyester | TIA Brown           | 1.00 (25.4)            | 1.33 (33.8)             | 0.47 (11.9)                     | 1.10 (27.9)                  | 1.33 (33.8)                | 7           | 7           | 49               | 52              | 2500            |
| PLL-12-Y3G-2.5  | Polyester | TIA Green           | 1.00 (25.4)            | 1.33 (33.8)             | 0.47 (11.9)                     | 1.10 (27.9)                  | 1.33 (33.8)                | 7           | 7           | 49               | 52              | 2500            |
| PLL-12-Y3IG-2.5 | Polyester | TIA Gray            | 1.00 (25.4)            | 1.33 (33.8)             | 0.47 (11.9)                     | 1.10 (27.9)                  | 1.33 (33.8)                | 7           | 7           | 49               | 52              | 2500            |
| PLL-12-Y3OR-2.5 | Polyester | TIA Orange          | 1.00 (25.4)            | 1.33 (33.8)             | 0.47 (11.9)                     | 1.10 (27.9)                  | 1.33 (33.8)                | 7           | 7           | 49               | 52              | 2500            |
| PLL-12-Y3PR-2.5 | Polyester | TIA Purple          | 1.00 (25.4)            | 1.33 (33.8)             | 0.47 (11.9)                     | 1.10 (27.9)                  | 1.33 (33.8)                | 7           | 7           | 49               | 52              | 2500            |
| PLL-12-Y3RD-2.5 | Polyester | TIA Red             | 1.00 (25.4)            | 1.33 (33.8)             | 0.47 (11.9)                     | 1.10 (27.9)                  | 1.33 (33.8)                | 7           | 7           | 49               | 52              | 2500            |
| PLL-12-Y3Y-2.5  | Polyester | TIA Yellow          | 1.00 (25.4)            | 1.33 (33.8)             | 0.47 (11.9)                     | 1.10 (27.9)                  | 1.33 (33.8)                | 7           | 7           | 49               | 52              | 2500            |
| PLL-39-Y3-1     | Polyester | White               | 1.00 (25.4)            | 1.33 (33.8)             | 0.47 (11.9)                     | 1.10 (27.9)                  | 1.33 (33.8)                | 8           | 8           | 64               | 16              | 1000            |
| PLL-13-Y3-D     | Polyester | White               | 1.00 (25.4)            | 3.17 (80.5)             | 0.97 (24.6)                     | 1.10 (27.9)                  | 3.17 (80.5)                | 7           | 3           | 21               | 24              | 500             |
| PLL-13-Y3-1     | Polyester | White               | 1.00 (25.4)            | 3.17 (80.5)             | 0.97 (24.6)                     | 1.10 (27.9)                  | 3.17 (80.5)                | 7           | 3           | 21               | 48              | 1000            |
| PLL-38-Y3-1     | Polyester | White               | 1.00 (25.4)            | 5.45 (138.4)            | 1.00 (25.4)                     | 1.10 (27.9)                  | 5.45 (138.4)               | 7           | 2           | 14               | 72              | 1000            |
| PLL-37-Y3-1     | Polyester | White               | 1.88 (47.6)            | 3.17 (80.5)             | 0.97 (24.6)                     | 2.00 (50.8)                  | 3.17 (80.5)                | 4           | 3           | 12               | 84              | 1000            |
| PLL-40-Y3-1     | Polyester | White               | 2.00 (50.8)            | 1.50 (38.1)             | 0.50 (12.7)                     | 2.00 (50.8)                  | 1.50 (38.1)                | 4           | 6           | 24               | 42              | 1000            |
| PLL-21-Y3-1     | Polyester | White               | 2.00 (50.8)            | 3.17 (80.5)             | 1.00 (25.4)                     | 2.50 (63.5)                  | 3.17 (80.5)                | 3           | 3           | 9                | 111             | 1000            |

## Self-Laminating Labels by Size (cont.)




### DIN A4 Sheet Format (8.26" x 11.69" / 210 mm x 297 mm)

| Part Number    | Material   | Print-On Area Color | Label Width A<br>In. (mm) | Label Length B<br>In. (mm) | Print-On Area Length C<br>In. (mm) | Horizontal Repeat D<br>In. (mm) | Vertical Repeat E<br>In. (mm) | No. of Col. | No. of Rows | Labels Per Sheet | Sheets Per Pkg. | Std. Pkg. Qty.* |
|----------------|------------|---------------------|---------------------------|----------------------------|------------------------------------|---------------------------------|-------------------------------|-------------|-------------|------------------|-----------------|-----------------|
| PEL-17-Y3-2.5  | Polyester  | White               | 0.70 (17.8)               | 1.33 (33.8)                | 0.33 (8.5)                         | 0.70 (17.8)                     | 1.33 (33.8)                   | 10          | 8           | 80               | 32              | 2500            |
| PEL-17-BLU-2.5 | Polyester  | TIA Blue            | 0.70 (17.8)               | 1.33 (33.8)                | 0.33 (8.5)                         | 0.70 (17.8)                     | 1.33 (33.8)                   | 10          | 8           | 80               | 32              | 2500            |
| PEL-17-BRN-2.5 | Polyester  | TIA Brown           | 0.70 (17.8)               | 1.33 (33.8)                | 0.33 (8.5)                         | 0.70 (17.8)                     | 1.33 (33.8)                   | 10          | 8           | 80               | 32              | 2500            |
| PEL-17-GRN-2.5 | Polyester  | TIA Green           | 0.70 (17.8)               | 1.33 (33.8)                | 0.33 (8.5)                         | 0.70 (17.8)                     | 1.33 (33.8)                   | 10          | 8           | 80               | 32              | 2500            |
| PEL-17-GRY-2.5 | Polyester  | TIA Gray            | 0.70 (17.8)               | 1.33 (33.8)                | 0.33 (8.5)                         | 0.70 (17.8)                     | 1.33 (33.8)                   | 10          | 8           | 80               | 32              | 2500            |
| PEL-17-ORN-2.5 | Polyester  | TIA Orange          | 0.70 (17.8)               | 1.33 (33.8)                | 0.33 (8.5)                         | 0.70 (17.8)                     | 1.33 (33.8)                   | 10          | 8           | 80               | 32              | 2500            |
| PEL-17-PUR-2.5 | Polyester  | TIA Purple          | 0.70 (17.8)               | 1.33 (33.8)                | 0.33 (8.5)                         | 0.70 (17.8)                     | 1.33 (33.8)                   | 10          | 8           | 80               | 32              | 2500            |
| PEL-17-RED-2.5 | Polyester  | TIA Red             | 0.70 (17.8)               | 1.33 (33.8)                | 0.33 (8.5)                         | 0.70 (17.8)                     | 1.33 (33.8)                   | 10          | 8           | 80               | 32              | 2500            |
| PEL-17-YEL-2.5 | Polyester  | TIA Yellow          | 0.70 (17.8)               | 1.33 (33.8)                | 0.33 (8.5)                         | 0.70 (17.8)                     | 1.33 (33.8)                   | 10          | 8           | 80               | 32              | 2500            |
| PEL-18-P03-1   | Polyolefin | White               | 0.90 (22.9)               | 2.17 (55.0)                | 0.50 (12.7)                        | 0.90 (22.9)                     | 2.17 (55.0)                   | 8           | 5           | 40               | 25              | 1000            |
| PEL-18-Y3-1    | Polyester  | White               | 0.90 (22.9)               | 2.17 (55.0)                | 0.50 (12.7)                        | 0.90 (22.9)                     | 2.17 (55.0)                   | 8           | 5           | 40               | 25              | 1000            |
| PEL-18-BLU-1   | Polyester  | TIA Blue            | 0.90 (22.9)               | 2.17 (55.0)                | 0.50 (12.7)                        | 0.90 (22.9)                     | 2.17 (55.0)                   | 8           | 5           | 40               | 25              | 1000            |
| PEL-18-BRN-1   | Polyester  | TIA Brown           | 0.90 (22.9)               | 2.17 (55.0)                | 0.50 (12.7)                        | 0.90 (22.9)                     | 2.17 (55.0)                   | 8           | 5           | 40               | 25              | 1000            |
| PEL-18-GRN-1   | Polyester  | TIA Green           | 0.90 (22.9)               | 2.17 (55.0)                | 0.50 (12.7)                        | 0.90 (22.9)                     | 2.17 (55.0)                   | 8           | 5           | 40               | 25              | 1000            |
| PEL-18-GRY-1   | Polyester  | TIA Gray            | 0.90 (22.9)               | 2.17 (55.0)                | 0.50 (12.7)                        | 0.90 (22.9)                     | 2.17 (55.0)                   | 8           | 5           | 40               | 25              | 1000            |
| PEL-18-ORN-1   | Polyester  | TIA Orange          | 0.90 (22.9)               | 2.17 (55.0)                | 0.50 (12.7)                        | 0.90 (22.9)                     | 2.17 (55.0)                   | 8           | 5           | 40               | 25              | 1000            |
| PEL-18-PUR-1   | Polyester  | TIA Purple          | 0.90 (22.9)               | 2.17 (55.0)                | 0.50 (12.7)                        | 0.90 (22.9)                     | 2.17 (55.0)                   | 8           | 5           | 40               | 25              | 1000            |
| PEL-18-RED-1   | Polyester  | TIA Red             | 0.90 (22.9)               | 2.17 (55.0)                | 0.50 (12.7)                        | 0.90 (22.9)                     | 2.17 (55.0)                   | 8           | 5           | 40               | 25              | 1000            |
| PEL-18-YEL-1   | Polyester  | TIA Yellow          | 0.90 (22.9)               | 2.17 (55.0)                | 0.50 (12.7)                        | 0.90 (22.9)                     | 2.17 (55.0)                   | 8           | 5           | 40               | 25              | 1000            |
| PEL-19-Y3-1    | Polyester  | White               | 1.00 (25.4)               | 2.67 (67.7)                | 0.67 (16.9)                        | 1.00 (25.4)                     | 2.67 (67.7)                   | 7           | 4           | 28               | 36              | 1000            |
| PEL-19-BLU-1   | Polyester  | TIA Blue            | 1.00 (25.4)               | 2.67 (67.7)                | 0.67 (16.9)                        | 1.00 (25.4)                     | 2.67 (67.7)                   | 7           | 4           | 28               | 36              | 1000            |
| PEL-19-BRN-1   | Polyester  | TIA Brown           | 1.00 (25.4)               | 2.67 (67.7)                | 0.67 (16.9)                        | 1.00 (25.4)                     | 2.67 (67.7)                   | 7           | 4           | 28               | 36              | 1000            |
| PEL-19-GRN-1   | Polyester  | TIA Green           | 1.00 (25.4)               | 2.67 (67.7)                | 0.67 (16.9)                        | 1.00 (25.4)                     | 2.67 (67.7)                   | 7           | 4           | 28               | 36              | 1000            |
| PEL-19-GRY-1   | Polyester  | TIA Gray            | 1.00 (25.4)               | 2.67 (67.7)                | 0.67 (16.9)                        | 1.00 (25.4)                     | 2.67 (67.7)                   | 7           | 4           | 28               | 36              | 1000            |
| PEL-19-ORN-1   | Polyester  | TIA Orange          | 1.00 (25.4)               | 2.67 (67.7)                | 0.67 (16.9)                        | 1.00 (25.4)                     | 2.67 (67.7)                   | 7           | 4           | 28               | 36              | 1000            |
| PEL-19-PUR-1   | Polyester  | TIA Purple          | 1.00 (25.4)               | 2.67 (67.7)                | 0.67 (16.9)                        | 1.00 (25.4)                     | 2.67 (67.7)                   | 7           | 4           | 28               | 36              | 1000            |
| PEL-19-RED-1   | Polyester  | TIA Red             | 1.00 (25.4)               | 2.67 (67.7)                | 0.67 (16.9)                        | 1.00 (25.4)                     | 2.67 (67.7)                   | 7           | 4           | 28               | 36              | 1000            |
| PEL-19-YEL-1   | Polyester  | TIA Yellow          | 1.00 (25.4)               | 2.67 (67.7)                | 0.67 (16.9)                        | 1.00 (25.4)                     | 2.67 (67.7)                   | 7           | 4           | 28               | 36              | 1000            |
| PEL-20-Y3-1    | Polyester  | White               | 1.20 (30.5)               | 2.67 (67.7)                | 0.83 (21.1)                        | 1.20 (30.5)                     | 2.67 (67.7)                   | 6           | 4           | 24               | 42              | 1000            |
| PEL-21-Y3-0.5  | Polyester  | White               | 1.40 (35.6)               | 3.67 (93.1)                | 1.00 (25.4)                        | 1.40 (35.6)                     | 3.67 (93.1)                   | 5           | 3           | 15               | 34              | 500             |
| PEL-21-BLU-0.5 | Polyester  | TIA Blue            | 1.40 (35.6)               | 3.67 (93.1)                | 1.00 (25.4)                        | 1.40 (35.6)                     | 3.67 (93.1)                   | 5           | 3           | 15               | 34              | 500             |
| PEL-21-BRN-0.5 | Polyester  | TIA Brown           | 1.40 (35.6)               | 3.67 (93.1)                | 1.00 (25.4)                        | 1.40 (35.6)                     | 3.67 (93.1)                   | 5           | 3           | 15               | 34              | 500             |
| PEL-21-GRN-0.5 | Polyester  | TIA Green           | 1.40 (35.6)               | 3.67 (93.1)                | 1.00 (25.4)                        | 1.40 (35.6)                     | 3.67 (93.1)                   | 5           | 3           | 15               | 34              | 500             |
| PEL-21-GRY-0.5 | Polyester  | TIA Gray            | 1.40 (35.6)               | 3.67 (93.1)                | 1.00 (25.4)                        | 1.40 (35.6)                     | 3.67 (93.1)                   | 5           | 3           | 15               | 34              | 500             |
| PEL-21-ORN-0.5 | Polyester  | TIA Orange          | 1.40 (35.6)               | 3.67 (93.1)                | 1.00 (25.4)                        | 1.40 (35.6)                     | 3.67 (93.1)                   | 5           | 3           | 15               | 34              | 500             |
| PEL-21-PUR-0.5 | Polyester  | TIA Purple          | 1.40 (35.6)               | 3.67 (93.1)                | 1.00 (25.4)                        | 1.40 (35.6)                     | 3.67 (93.1)                   | 5           | 3           | 15               | 34              | 500             |
| PEL-21-RED-0.5 | Polyester  | TIA Red             | 1.40 (35.6)               | 3.67 (93.1)                | 1.00 (25.4)                        | 1.40 (35.6)                     | 3.67 (93.1)                   | 5           | 3           | 15               | 34              | 500             |
| PEL-21-YEL-0.5 | Polyester  | TIA Yellow          | 1.40 (35.6)               | 3.67 (93.1)                | 1.00 (25.4)                        | 1.40 (35.6)                     | 3.67 (93.1)                   | 5           | 3           | 15               | 34              | 500             |
| PEL-22-Y3-0.5  | Polyester  | White               | 1.40 (35.6)               | 5.50 (140.0)               | 1.00 (25.4)                        | 1.40 (35.6)                     | 5.50 (140.0)                  | 5           | 2           | 10               | 50              | 500             |
| PEL-23-Y3-0.5  | Polyester  | White               | 1.80 (45.7)               | 5.50 (140.0)               | 1.167 (29.6)                       | 1.80 (45.7)                     | 5.50 (140.0)                  | 4           | 2           | 8                | 63              | 500             |

\*Order number of labels required in multiples of Std. Pkg. Qty.


## Blank Labels by Size



### U.S. Letter Sheet Format (8.5" x 11" / 215.9 mm x 279.4 mm)

| Part Number   | Material          | Color  | Label Width A<br>In. (mm) | Label Length B<br>In. (mm) | Horizontal Repeat D<br>In. (mm) | Vertical Repeat E<br>In. (mm) | No. of Col. | No. of Rows | Labels Per Sheet | Sheets Per Pkg | Std. Pkg. Qty* |
|---------------|-------------------|--------|---------------------------|----------------------------|---------------------------------|-------------------------------|-------------|-------------|------------------|----------------|----------------|
| PLL-2-Y2-10   | Polyester         | White  | 0.38 (9.5)                | 0.38 (9.5)                 | 0.50 (12.7)                     | 0.38 (9.5)                    | 16          | 25          | 400              | 25             | 10,000         |
| PLL-2-Y2Y-10  | Polyester         | Yellow | 0.38 (9.5)                | 0.38 (9.5)                 | 0.50 (12.7)                     | 0.38 (9.5)                    | 16          | 25          | 400              | 25             | 10,000         |
| PLL-31-Y2-10  | Polyester         | White  | 0.50 (12.7)               | 0.44 (11.1)                | 0.60 (15.2)                     | 0.44 (11.1)                   | 13          | 22          | 286              | 35             | 10,000         |
| PLL-31-POR-10 | Remov. Polyolefin | White  | 0.50 (12.7)               | 0.44 (11.1)                | 0.60 (15.2)                     | 0.44 (11.1)                   | 13          | 22          | 286              | 35             | 10,000         |
| PLL-33-P0-5   | Polyolefin        | White  | 0.50 (12.7)               | 1.50 (38.1)                | 0.60 (15.2)                     | 1.50 (38.1)                   | 13          | 6           | 78               | 65             | 5000           |
| PLL-24-Y2-1   | Polyester         | White  | 0.56 (14.3)               | 0.19 (4.8)                 | 0.80 (20.3)                     | 0.40 (10.2)                   | 10          | 24          | 240              | 5              | 1000           |
| PLL-24-Y2-5   | Polyester         | White  | 0.56 (14.3)               | 0.19 (4.8)                 | 0.80 (20.3)                     | 0.40 (10.2)                   | 10          | 24          | 240              | 21             | 5000           |
| PLL-24-Y3-1   | Polyester         | Clear  | 0.56 (14.3)               | 0.19 (4.8)                 | 0.80 (20.3)                     | 0.40 (10.2)                   | 10          | 24          | 240              | 5              | 1000           |
| PLL-24-Y3-5   | Polyester         | Clear  | 0.56 (14.3)               | 0.19 (4.8)                 | 0.80 (20.3)                     | 0.40 (10.2)                   | 10          | 24          | 240              | 21             | 5000           |
| PLL-23-Y2-1   | Polyester         | White  | 0.56 (14.3)               | 0.56 (14.3)                | 0.80 (20.3)                     | 0.80 (20.3)                   | 10          | 12          | 120              | 9              | 1000           |
| PLL-23-Y2-5   | Polyester         | White  | 0.56 (14.3)               | 0.56 (14.3)                | 0.80 (20.3)                     | 0.80 (20.3)                   | 10          | 12          | 120              | 42             | 5000           |
| PLL-23-Y3-1   | Polyester         | Clear  | 0.56 (14.3)               | 0.56 (14.3)                | 0.80 (20.3)                     | 0.80 (20.3)                   | 10          | 12          | 120              | 9              | 1000           |
| PLL-23-Y3-5   | Polyester         | Clear  | 0.56 (14.3)               | 0.56 (14.3)                | 0.80 (20.3)                     | 0.80 (20.3)                   | 10          | 12          | 120              | 42             | 5000           |
| PLL-32-Y2-10  | Polyester         | White  | 0.65 (16.5)               | 0.20 (5.1)                 | 0.80 (20.3)                     | 0.20 (5.1)                    | 10          | 48          | 480              | 21             | 10,000         |
| PLL-32-Y2Y-10 | Polyester         | Yellow | 0.65 (16.5)               | 0.20 (5.1)                 | 0.80 (20.3)                     | 0.20 (5.1)                    | 10          | 48          | 480              | 21             | 10,000         |
| PLL-4-Y2-10   | Polyester         | White  | 0.65 (16.5)               | 0.25 (6.4)                 | 0.80 (20.3)                     | 0.25 (6.4)                    | 10          | 39          | 390              | 26             | 10,000         |
| PLL-4-Y2Y-10  | Polyester         | Yellow | 0.65 (16.5)               | 0.25 (6.4)                 | 0.80 (20.3)                     | 0.25 (6.4)                    | 10          | 39          | 390              | 26             | 10,000         |
| PLL-20-Y2-10  | Polyester         | White  | 0.80 (20.3)               | 0.20 (5.1)                 | 1.00 (25.4)                     | 0.20 (5.1)                    | 8           | 45          | 360              | 28             | 10,000         |
| PLL-20-Y2Y-10 | Polyester         | Yellow | 0.80 (20.3)               | 0.20 (5.1)                 | 1.00 (25.4)                     | 0.20 (5.1)                    | 8           | 45          | 360              | 28             | 10,000         |
| PLL-5-Y2-10   | Polyester         | White  | 0.80 (20.3)               | 0.25 (6.4)                 | 1.00 (25.4)                     | 0.25 (6.4)                    | 8           | 39          | 312              | 33             | 10,000         |
| PLL-5-Y2Y-10  | Polyester         | Yellow | 0.80 (20.3)               | 0.25 (6.4)                 | 1.00 (25.4)                     | 0.25 (6.4)                    | 8           | 39          | 312              | 33             | 10,000         |
| PLL-6-Y2-5    | Polyester         | White  | 0.80 (20.3)               | 0.50 (12.7)                | 1.00 (25.4)                     | 0.50 (12.7)                   | 8           | 19          | 152              | 33             | 5000           |
| PLL-6-Y2-10   | Polyester         | White  | 0.80 (20.3)               | 0.50 (12.7)                | 1.00 (25.4)                     | 0.50 (12.7)                   | 8           | 19          | 152              | 66             | 10,000         |
| PLL-6-Y2Y-5   | Polyester         | Yellow | 0.80 (20.3)               | 0.50 (12.7)                | 1.00 (25.4)                     | 0.50 (12.7)                   | 8           | 19          | 152              | 66             | 5000           |
| PLL-6-Y2Y-10  | Polyester         | Yellow | 0.80 (20.3)               | 0.50 (12.7)                | 1.00 (25.4)                     | 0.50 (12.7)                   | 8           | 19          | 152              | 33             | 10,000         |
| PLL-7-Y2-10   | Polyester         | White  | 1.00 (25.4)               | 0.25 (6.4)                 | 1.10 (27.9)                     | 0.25 (6.4)                    | 7           | 39          | 273              | 37             | 10,000         |
| PLL-7-Y2Y-10  | Polyester         | Yellow | 1.00 (25.4)               | 0.25 (6.4)                 | 1.10 (27.9)                     | 0.25 (6.4)                    | 7           | 39          | 273              | 37             | 10,000         |
| PLL-8-Y2-5    | Polyester         | White  | 1.00 (25.4)               | 0.38 (9.5)                 | 1.10 (27.9)                     | 0.38 (9.5)                    | 7           | 25          | 175              | 58             | 5000           |
| PLL-8-Y2-10   | Polyester         | White  | 1.00 (25.4)               | 0.38 (9.5)                 | 1.10 (27.9)                     | 0.38 (9.5)                    | 7           | 25          | 175              | 29             | 10,000         |
| PLL-8-Y2Y-5   | Polyester         | Yellow | 1.00 (25.4)               | 0.38 (9.5)                 | 1.10 (27.9)                     | 0.38 (9.5)                    | 7           | 25          | 175              | 58             | 5000           |
| PLL-8-Y2Y-10  | Polyester         | Yellow | 1.00 (25.4)               | 0.38 (9.5)                 | 1.10 (27.9)                     | 0.38 (9.5)                    | 7           | 25          | 175              | 29             | 10,000         |
| PLL-8-P0-10   | Polyolefin        | White  | 1.00 (25.4)               | 0.38 (9.5)                 | 1.10 (27.9)                     | 0.38 (9.5)                    | 7           | 25          | 175              | 58             | 10,000         |

## Blank Labels by Size (cont.)




### U.S. Letter Sheet Format (8.5" x 11" / 215.9 mm x 279.4 mm)

| Part Number    | Material          | Color  | Label Width A<br>In. (mm) | Label Length B<br>In. (mm) | Horizontal Repeat D<br>In. (mm) | Vertical Repeat E<br>In. (mm) | No. of Col. | No. of Rows | Labels Per Sheet | Sheets Per Pkg | Std. Pkg. Qty* |
|----------------|-------------------|--------|---------------------------|----------------------------|---------------------------------|-------------------------------|-------------|-------------|------------------|----------------|----------------|
| PLL-9-Y2-5     | Polyester         | White  | 1.00 (25.4)               | 0.50 (12.7)                | 1.10 (27.9)                     | 0.50 (12.7)                   | 7           | 19          | 133              | 76             | 5000           |
| PLL-9-Y2-10    | Polyester         | White  | 1.00 (25.4)               | 0.50 (12.7)                | 1.10 (27.9)                     | 0.50 (12.7)                   | 7           | 19          | 133              | 38             | 10,000         |
| PLL-9-Y2S-10   | Polyester         | Silver | 1.00 (25.4)               | 0.50 (12.7)                | 1.10 (27.9)                     | 0.50 (12.7)                   | 7           | 19          | 133              | 76             | 10,000         |
| PLL-9-Y2Y-5    | Polyester         | Yellow | 1.00 (25.4)               | 0.50 (12.7)                | 1.10 (27.9)                     | 0.50 (12.7)                   | 7           | 19          | 133              | 76             | 5000           |
| PLL-9-Y2Y-10   | Polyester         | Yellow | 1.00 (25.4)               | 0.50 (12.7)                | 1.10 (27.9)                     | 0.50 (12.7)                   | 7           | 19          | 133              | 38             | 10,000         |
| PLL-9-Y3C-5    | Polyester         | Clear  | 1.00 (25.4)               | 0.50 (12.7)                | 1.10 (27.9)                     | 0.50 (12.7)                   | 7           | 19          | 133              | 38             | 5000           |
| PLL-9-POR-10   | Remov. Polyolefin | White  | 1.00 (25.4)               | 0.50 (12.7)                | 1.10 (27.9)                     | 0.50 (12.7)                   | 7           | 19          | 133              | 76             | 10,000         |
| PLL-10-Y2-2.5  | Polyester         | White  | 1.00 (25.4)               | 0.75 (19.1)                | 1.10 (27.9)                     | 0.75 (19.1)                   | 7           | 12          | 84               | 30             | 2500           |
| PLL-10-Y3C-2.5 | Polyester         | Clear  | 1.00 (25.4)               | 0.75 (19.1)                | 1.10 (27.9)                     | 0.75 (19.1)                   | 7           | 12          | 84               | 30             | 2500           |
| PLL-10-P0-5    | Polyolefin        | White  | 1.00 (25.4)               | 0.75 (19.1)                | 1.10 (27.9)                     | 0.75 (19.1)                   | 7           | 12          | 84               | 30             | 5000           |
| PLL-11-Y2-2.5  | Polyester         | White  | 1.00 (25.4)               | 1.00 (25.4)                | 1.10 (27.9)                     | 1.00 (25.4)                   | 7           | 10          | 70               | 36             | 2500           |
| PLL-11-Y3C-2.5 | Polyester         | Clear  | 1.00 (25.4)               | 1.00 (25.4)                | 1.10 (27.9)                     | 1.00 (25.4)                   | 7           | 10          | 70               | 36             | 2500           |
| PLL-12-Y2-1    | Polyester         | White  | 1.00 (25.4)               | 1.33 (33.8)                | 1.10 (27.9)                     | 1.33 (33.8)                   | 7           | 7           | 49               | 21             | 1000           |
| PLL-12-Y2-2.5  | Polyester         | White  | 1.00 (25.4)               | 1.33 (33.8)                | 1.10 (27.9)                     | 1.33 (33.8)                   | 7           | 7           | 49               | 52             | 2500           |
| PLL-34-Y2-10   | Polyester         | White  | 1.25 (31.8)               | 0.38 (9.5)                 | 1.10 (27.9)                     | 0.38 (9.5)                    | 5           | 25          | 125              | 80             | 10,000         |
| PLL-34-Y2Y-10  | Polyester         | Yellow | 1.25 (31.8)               | 0.38 (9.5)                 | 1.60 (40.6)                     | 0.38 (9.5)                    | 5           | 25          | 125              | 80             | 10,000         |
| PLL-34-POR-10  | Remov. Polyolefin | White  | 1.25 (31.8)               | 0.38 (9.5)                 | 1.60 (40.6)                     | 0.38 (9.5)                    | 5           | 25          | 125              | 80             | 10,000         |
| PLL-14-Y2-5    | Polyester         | White  | 1.50 (38.1)               | 0.25 (6.4)                 | 1.60 (40.6)                     | 0.25 (6.4)                    | 5           | 39          | 195              | 52             | 5000           |
| PLL-14-Y2-10   | Polyester         | White  | 1.50 (38.1)               | 0.25 (6.4)                 | 1.60 (40.6)                     | 0.25 (6.4)                    | 5           | 39          | 195              | 26             | 10,000         |
| PLL-14-Y2Y-5   | Polyester         | Yellow | 1.50 (38.1)               | 0.25 (6.4)                 | 1.60 (40.6)                     | 0.25 (6.4)                    | 5           | 39          | 195              | 26             | 5000           |
| PLL-14-P0-5    | Polyolefin        | White  | 1.50 (38.1)               | 0.25 (6.4)                 | 1.60 (40.6)                     | 0.25 (6.4)                    | 5           | 39          | 195              | 26             | 5000           |
| PLL-14-POR-5   | Remov. Polyolefin | White  | 1.50 (38.1)               | 0.25 (6.4)                 | 1.60 (40.6)                     | 0.25 (6.4)                    | 5           | 39          | 195              | 26             | 5000           |
| PLL-35-Y2S-2.5 | Polyester         | Silver | 1.50 (38.1)               | 0.75 (19.1)                | 1.60 (40.6)                     | 0.75 (19.1)                   | 5           | 12          | 60               | 42             | 2500           |
| PLL-35-P0-2.5  | Polyolefin        | White  | 1.50 (38.1)               | 0.75 (19.1)                | 1.60 (40.6)                     | 0.75 (19.1)                   | 5           | 12          | 60               | 42             | 2500           |
| PLL-35-POR-2.5 | Remov. Polyolefin | White  | 1.50 (38.1)               | 0.75 (19.1)                | 1.60 (40.6)                     | 0.75 (19.1)                   | 5           | 12          | 60               | 42             | 2500           |
| PLL-15-Y2-5    | Polyester         | White  | 1.88 (47.6)               | 0.25 (6.4)                 | 2.00 (50.8)                     | 0.25 (6.4)                    | 4           | 39          | 156              | 65             | 5000           |
| PLL-15-Y2-10   | Polyester         | White  | 1.88 (47.6)               | 0.25 (6.4)                 | 2.00 (50.8)                     | 0.25 (6.4)                    | 4           | 39          | 156              | 33             | 10,000         |
| PLL-15-Y2Y-5   | Polyester         | Yellow | 1.88 (47.6)               | 0.25 (6.4)                 | 2.00 (50.8)                     | 0.25 (6.4)                    | 4           | 39          | 156              | 33             | 5000           |
| PLL-16-Y2-2.5  | Polyester         | White  | 1.88 (47.6)               | 0.38 (9.5)                 | 2.00 (50.8)                     | 0.38 (9.5)                    | 4           | 25          | 100              | 25             | 2500           |
| PLL-16-Y2-5    | Polyester         | White  | 1.88 (47.6)               | 0.38 (9.5)                 | 2.00 (50.8)                     | 0.38 (9.5)                    | 4           | 25          | 100              | 50             | 5000           |
| PLL-16-Y2Y-2.5 | Polyester         | Yellow | 1.88 (47.6)               | 0.38 (9.5)                 | 2.00 (50.8)                     | 0.38 (9.5)                    | 4           | 25          | 100              | 25             | 2500           |
| PLL-16-Y2Y-5   | Polyester         | Yellow | 1.88 (47.6)               | 0.38 (9.5)                 | 2.00 (50.8)                     | 0.38 (9.5)                    | 4           | 25          | 100              | 50             | 5000           |
| PLL-16-P0-2.5  | Polyolefin        | White  | 1.88 (47.6)               | 0.38 (9.5)                 | 2.00 (50.8)                     | 0.38 (9.5)                    | 4           | 25          | 100              | 25             | 2500           |
| PLL-17-Y2-1    | Polyester         | White  | 1.88 (47.6)               | 0.83 (21.1)                | 2.00 (50.8)                     | 0.83 (21.1)                   | 4           | 11          | 44               | 23             | 1000           |
| PLL-17-Y2-2.5  | Polyester         | White  | 1.88 (47.6)               | 0.83 (21.1)                | 2.00 (50.8)                     | 0.83 (21.1)                   | 4           | 11          | 44               | 57             | 2500           |
| PLL-17-Y2Y-2.5 | Polyester         | Yellow | 1.88 (47.6)               | 0.83 (21.1)                | 2.00 (50.8)                     | 0.83 (21.1)                   | 4           | 11          | 44               | 57             | 2500           |
| PLL-17-P0-2.5  | Polyolefin        | White  | 1.88 (47.6)               | 0.83 (21.1)                | 2.00 (50.8)                     | 0.83 (21.1)                   | 4           | 11          | 44               | 57             | 2500           |

\*Order number of labels required in multiples of Std. Pkg. Qty.

## Blank Labels by Size (cont.)




### U.S. Letter Sheet Format (8.5" x 11" / 215.9 mm x 279.4 mm)

| Part Number    | Material          | Color  | Label Width A<br>In. (mm) | Label Length B<br>In. (mm) | Horizontal Repeat D<br>In. (mm) | Vertical Repeat E<br>In. (mm) | No. of Col. | No. of Rows | Labels Per Sheet | Sheets Per Pkg | Std. Pkg. Qty* |
|----------------|-------------------|--------|---------------------------|----------------------------|---------------------------------|-------------------------------|-------------|-------------|------------------|----------------|----------------|
| PLL-18-Y2-1    | Polyester         | White  | 1.88 (47.6)               | 1.33 (33.8)                | 2.00 (50.8)                     | 1.33 (33.8)                   | 4           | 7           | 28               | 36             | 1000           |
| PLL-18-Y2-1.5  | Polyester         | White  | 1.88 (47.6)               | 1.33 (33.8)                | 2.00 (50.8)                     | 1.33 (33.8)                   | 4           | 7           | 28               | 54             | 1500           |
| PLL-18-Y2Y-1   | Polyester         | Yellow | 1.88 (47.6)               | 1.33 (33.8)                | 2.00 (50.8)                     | 1.33 (33.8)                   | 4           | 7           | 28               | 36             | 1000           |
| PLL-18-Y2Y-1.5 | Polyester         | Yellow | 1.88 (47.6)               | 1.33 (33.8)                | 2.00 (50.8)                     | 1.33 (33.8)                   | 4           | 7           | 28               | 54             | 1500           |
| PLL-36-Y2-1    | Polyester         | White  | 2.50 (63.5)               | 1.00 (25.4)                | 2.60 (66.0)                     | 1.00 (25.4)                   | 3           | 9           | 27               | 38             | 1000           |
| PLL-36-Y2S-1   | Polyester         | Silver | 2.50 (63.5)               | 1.00 (25.4)                | 2.60 (66.0)                     | 1.00 (25.4)                   | 3           | 9           | 27               | 38             | 1000           |
| PLL-36-P0-1    | Polyolefin        | White  | 2.50 (63.5)               | 1.00 (25.4)                | 2.60 (66.0)                     | 1.00 (25.4)                   | 3           | 9           | 27               | 38             | 1000           |
| PLL-36-P0R-1   | Remov. Polyolefin | White  | 2.50 (63.5)               | 1.00 (25.4)                | 2.60 (66.0)                     | 1.00 (25.4)                   | 3           | 9           | 27               | 38             | 1000           |
| PLL-26-Y2-1    | Polyester         | White  | 2.83 (72.0)               | 1.00 (25.4)                | 2.83 (72.0)                     | 1.00 (25.4)                   | 3           | 11          | 33               | 31             | 1000           |
| PLL-27-Y2-1    | Polyester         | White  | 2.83 (72.0)               | 1.38 (34.9)                | 2.83 (72.0)                     | 1.38 (34.9)                   | 3           | 8           | 24               | 42             | 1000           |
| PLL-28-Y2-1    | Polyester         | White  | 2.83 (72.0)               | 1.50 (38.1)                | 2.83 (72.0)                     | 1.50 (38.1)                   | 3           | 7           | 21               | 48             | 1000           |
| PLL-19-Y2-1    | Polyester         | White  | 3.00 (76.2)               | 0.38 (9.5)                 | 3.20 (81.3)                     | 0.38 (9.5)                    | 2           | 25          | 50               | 20             | 1000           |
| PLL-19-Y2-2.5  | Polyester         | White  | 3.00 (76.2)               | 0.38 (9.5)                 | 3.20 (81.3)                     | 0.38 (9.5)                    | 2           | 25          | 50               | 50             | 2500           |
| PLL-19-Y2Y-1   | Polyester         | Yellow | 3.00 (76.2)               | 0.38 (9.5)                 | 3.20 (81.3)                     | 0.38 (9.5)                    | 2           | 25          | 50               | 20             | 1000           |
| PLL-19-Y2Y-2.5 | Polyester         | Yellow | 3.00 (76.2)               | 0.38 (9.5)                 | 3.20 (81.3)                     | 0.38 (9.5)                    | 2           | 25          | 50               | 50             | 2500           |
| PLL-19-P0R-2.5 | Remov. Polyolefin | White  | 3.00 (76.2)               | 0.38 (9.5)                 | 3.20 (81.3)                     | 0.38 (9.5)                    | 2           | 25          | 50               | 50             | 2500           |
| PLL-29-Y2-1    | Polyester         | White  | 4.25 (108.0)              | 2.00 (50.8)                | 4.25 (108.0)                    | 2.00 (50.8)                   | 2           | 5           | 10               | 100            | 1000           |
| PLL-22-Y2-1    | Polyester         | White  | 7.88 (200.0)              | 0.50 (12.7)                | —                               | 0.50 (12.7)                   | 1           | 20          | 20               | 50             | 1000           |
| PLL-22-Y3-1    | Polyester         | Clear  | 7.88 (200.0)              | 0.50 (12.7)                | —                               | 0.50 (12.7)                   | 1           | 20          | 20               | 50             | 1000           |
| PLL-22-P0-1    | Polyolefin        | White  | 7.88 (200.0)              | 0.50 (12.7)                | —                               | 0.50 (12.7)                   | 1           | 20          | 20               | 50             | 1000           |
| PLL-22-P0-1B   | Polyolefin        | Blue   | 7.88 (200.0)              | 0.50 (12.7)                | —                               | 0.50 (12.7)                   | 1           | 20          | 20               | 50             | 1000           |
| PLL-22-P0-1BR  | Polyolefin        | Brown  | 7.88 (200.0)              | 0.50 (12.7)                | —                               | 0.50 (12.7)                   | 1           | 20          | 20               | 50             | 1000           |
| PLL-22-P0-1G   | Polyolefin        | Green  | 7.88 (200.0)              | 0.50 (12.7)                | —                               | 0.50 (12.7)                   | 1           | 20          | 20               | 50             | 1000           |
| PLL-22-P0-1GR  | Polyolefin        | Gray   | 7.88 (200.0)              | 0.50 (12.7)                | —                               | 0.50 (12.7)                   | 1           | 20          | 20               | 50             | 1000           |
| PLL-22-P0-1OR  | Polyolefin        | Orange | 7.88 (200.0)              | 0.50 (12.7)                | —                               | 0.50 (12.7)                   | 1           | 20          | 20               | 50             | 1000           |
| PLL-22-P0-1PR  | Polyolefin        | Purple | 7.88 (200.0)              | 0.50 (12.7)                | —                               | 0.50 (12.7)                   | 1           | 20          | 20               | 50             | 1000           |
| PLL-22-P0-1R   | Polyolefin        | Red    | 7.88 (200.0)              | 0.50 (12.7)                | —                               | 0.50 (12.7)                   | 1           | 20          | 20               | 50             | 1000           |
| PLL-22-P0-1Y   | Polyolefin        | Yellow | 7.88 (200.0)              | 0.50 (12.7)                | —                               | 0.50 (12.7)                   | 1           | 20          | 20               | 50             | 1000           |
| PLL-25-Y2-SH   | Polyester         | White  | 8.50 (215.9)              | 11.00 (279.4)              | —                               | —                             | 1           | 1           | 1                | 25             | 25             |
| PLL-25-Y2S-SH  | Polyester         | Silver | 8.50 (215.9)              | 11.00 (279.4)              | —                               | —                             | 1           | 1           | 1                | 25             | 25             |
| PLL-25-Y2Y-SH  | Polyester         | Yellow | 8.50 (215.9)              | 11.00 (279.4)              | —                               | —                             | 1           | 1           | 1                | 25             | 25             |
| PLL-25-Y3C-SH  | Polyester         | Clear  | 8.50 (215.9)              | 11.00 (279.4)              | —                               | —                             | 1           | 1           | 1                | 25             | 25             |
| PLL-25-P0-SH   | Polyolefin        | White  | 8.50 (215.9)              | 11.00 (279.4)              | —                               | —                             | 1           | 1           | 1                | 25             | 25             |
| PLL-25-P0R-SH  | Remov. Polyolefin | White  | 8.50 (215.9)              | 11.00 (279.4)              | —                               | —                             | 1           | 1           | 1                | 25             | 25             |

## Blank Labels by Size (cont.)

### Multiple Across – Double Butt-Cut



| Part Number  | Material  | Color  | Label Width A<br>In. (mm) | Label Length B<br>In. (mm) | Horizontal Repeat D<br>In. (mm) | Vertical Repeat E<br>In. (mm) | No. of Col. | No. of Rows | Labels Per Sheet | Sheets Per Pkg | Std. Pkg. Qty* |
|--------------|-----------|--------|---------------------------|----------------------------|---------------------------------|-------------------------------|-------------|-------------|------------------|----------------|----------------|
| PLL-30-Y2-10 | Polyester | White  | 0.25 (6.4)                | 0.25 (6.4)                 | 0.60 (15.2)                     | 0.25 (6.4)                    | 26          | 36          | 936              | 11             | 10,000         |
| PLL-1-Y2-10  | Polyester | White  | 0.30 (7.6)                | 0.25 (6.4)                 | 0.70 (17.8)                     | 0.25 (6.4)                    | 22          | 38          | 836              | 12             | 10,000         |
| PLL-1-Y2Y-10 | Polyester | Yellow | 0.30 (7.6)                | 0.25 (6.4)                 | 0.70 (17.8)                     | 0.25 (6.4)                    | 22          | 38          | 836              | 12             | 10,000         |

\*Order number of labels required in multiples of Std. Pkg. Qty.

### Blank Paper Labels (LL) - Drawings and Specifications


|                      |             |               |              |
|----------------------|-------------|---------------|--------------|
|                      |             |               |              |
| LL2561-100, 250, 500 | LL2561-100G | LL2561138-100 | LL25615-100G |
|                      |             |               |              |
| LL4252-100G          | LL42575-250 | LL8511-100    | LL42513-100G |

| Part Number  | Material    | Color | Label Width A<br>In. (mm) | Label Length B<br>In. (mm) | Horizontal Repeat D<br>In. (mm) | Vertical Repeat E<br>In. (mm) | No. of Col. | No. of Rows | Labels Per Sheet | Sheets Per Pkg | Labels Per Pkg. | Std. Pkg. Qty* |
|--------------|-------------|-------|---------------------------|----------------------------|---------------------------------|-------------------------------|-------------|-------------|------------------|----------------|-----------------|----------------|
| LL2561-100G  | Litho Paper | White | 2.83 (72.0)               | 1.00 (25.4)                | 2.83 (72.0)                     | 1.00 (25.4)                   | 3           | 10          | 30               | 100            | 3000            | 1 Pkg.         |
| LL2561-100   | Litho Paper | White | 2.83 (72.0)               | 1.00 (25.4)                | 2.83 (72.0)                     | 1.00 (25.4)                   | 3           | 11          | 33               | 100            | 3300            | 1 Pkg.         |
| LL2561-250   | Litho Paper | White | 2.83 (72.0)               | 1.00 (25.4)                | 2.83 (72.0)                     | 1.00 (25.4)                   | 3           | 11          | 33               | 250            | 8250            | 1 Pkg.         |
| LL2561-500   | Litho Paper | White | 2.83 (72.0)               | 1.00 (25.4)                | 2.83 (72.0)                     | 1.00 (25.4)                   | 3           | 11          | 33               | 500            | 16,500          | 1 Pkg.         |
| LL256138-100 | Litho Paper | White | 2.83 (72.0)               | 1.38 (34.9)                | 2.83 (72.0)                     | 1.38 (34.9)                   | 3           | 8           | 24               | 100            | 2400            | 1 Pkg.         |
| LL25615-100G | Litho Paper | White | 2.83 (72.0)               | 1.50 (38.1)                | 2.83 (72.0)                     | 1.50 (38.1)                   | 3           | 7           | 21               | 100            | 2100            | 1 Pkg.         |
| LL4252-100G  | Litho Paper | White | 4.25 (108.0)              | 2.00 (50.8)                | 4.25 (108.0)                    | 2.00 (50.8)                   | 2           | 5           | 10               | 100            | 1000            | 1 Pkg.         |
| LL42575-250  | Litho Paper | White | 4.25 (108.0)              | 2.75 (69.9)                | 4.25 (108.0)                    | 2.75 (69.9)                   | 2           | 4           | 8                | 250            | 2000            | 1 Pkg.         |
| LL42513-100G | Litho Paper | White | 4.25 (108.0)              | 13.00 (330.2)              | 4.25 (108.0)                    | 13.00 (330.2)                 | 2           | 2           | 4                | 100            | 400             | 1 Pkg.         |
| LL8511-100   | Litho Paper | White | 8.50 (215.9)              | 11.00 (279.4)              | 8.50 (215.9)                    | 11.00 (279.4)                 | 1           | 1           | 1                | 100            | 100             | 1 Pkg.         |

"G" in above part numbers indicates gripper areas (top and bottom margins per sheet), not available for printing.

\*Order number of packages required in multiples of Std. Pkg. Qty.


## Blank Labels by Size (cont.)



### DIN A4 Sheet Format (8.26" x 11.69" / 210 mm x 297 mm)

| Part Number   | Material                 | Color       | Label Width A<br>In. (mm) | Label Length B<br>In. (mm) | Horizontal Repeat D<br>In. (mm) | Vertical Repeat E<br>In. (mm) | No. of Col. | No. of Rows | Labels Per Sheet | Sheets Per Pkg | Std. Pkg. Qty* |
|---------------|--------------------------|-------------|---------------------------|----------------------------|---------------------------------|-------------------------------|-------------|-------------|------------------|----------------|----------------|
| PEL-25-Y2Y-10 | Polyester                | Yellow      | 0.35 (9.0)                | 0.59 (15.0)                | 0.35 (9.0)                      | 0.59 (15.0)                   | 12          | 31          | 372              | 27             | 10,000         |
| PEL-26-Y2Y-5  | Polyester                | Yellow      | 0.43 (11.0)               | 0.75 (19.1)                | 0.43 (11.0)                     | 0.75 (19.1)                   | 10          | 25          | 250              | 20             | 5000           |
| PEL-27-Y2Y-5  | Polyester                | Yellow      | 0.43 (11.0)               | 1.50 (38.1)                | 0.43 (11.0)                     | 1.50 (38.1)                   | 5           | 25          | 125              | 40             | 5000           |
| PEL-9-Y1-10   | Polyester                | Silver      | 0.50 (12.7)               | 0.50 (12.7)                | 0.50 (12.7)                     | 0.50 (12.7)                   | 14          | 22          | 308              | 33             | 10,000         |
| PEL-9-Y2-10   | Polyester                | White       | 0.50 (12.7)               | 0.50 (12.7)                | 0.50 (12.7)                     | 0.50 (12.7)                   | 14          | 22          | 308              | 33             | 10,000         |
| PEL-9-Y1C-10  | Tamper Evident Polyester | Silver      | 0.50 (12.7)               | 0.50 (12.7)                | 0.50 (12.7)                     | 0.50 (12.7)                   | 14          | 22          | 308              | 33             | 10,000         |
| PEL-29-Y2-10  | Polyester                | White       | 0.56 (14.3)               | 0.25 (6.4)                 | 0.56 (14.3)                     | 0.25 (6.4)                    | 13          | 43          | 559              | 18             | 10,000         |
| PEL-29-Y3M-10 | Polyester                | Matte Clear | 0.56 (14.3)               | 0.25 (6.4)                 | 0.56 (14.3)                     | 0.25 (6.4)                    | 13          | 43          | 559              | 18             | 10,000         |
| PEL-28-Y2-5   | Polyester                | White       | 0.56 (14.3)               | 0.56 (14.3)                | 0.56 (14.3)                     | 0.56 (14.3)                   | 13          | 19          | 247              | 41             | 5000           |
| PEL-28-Y3M-5  | Polyester                | Matte Clear | 0.56 (14.3)               | 0.56 (14.3)                | 0.56 (14.3)                     | 0.56 (14.3)                   | 13          | 19          | 247              | 41             | 5000           |
| PEL-1-Y1-10   | Polyester                | Silver      | 0.70 (17.8)               | 0.25 (6.4)                 | 0.70 (17.8)                     | 0.25 (6.4)                    | 10          | 45          | 450              | 23             | 10,000         |
| PEL-1-Y2-10   | Polyester                | White       | 0.70 (17.8)               | 0.25 (6.4)                 | 0.70 (17.8)                     | 0.25 (6.4)                    | 10          | 45          | 450              | 23             | 10,000         |
| PEL-4-Y1-10   | Polyester                | Silver      | 0.70 (17.8)               | 0.33 (8.5)                 | 0.70 (17.8)                     | 0.33 (8.5)                    | 10          | 33          | 330              | 31             | 10,000         |
| PEL-4-Y2-10   | Polyester                | White       | 0.70 (17.8)               | 0.33 (8.5)                 | 0.70 (17.8)                     | 0.33 (8.5)                    | 10          | 33          | 330              | 31             | 10,000         |
| PEL-4-Y2Y-10  | Polyester                | Yellow      | 0.70 (17.8)               | 0.33 (8.5)                 | 0.70 (17.8)                     | 0.33 (8.5)                    | 10          | 33          | 330              | 31             | 10,000         |
| PEL-4-Y1C-10  | Tamper Evident Polyester | Silver      | 0.70 (17.8)               | 0.33 (8.5)                 | 0.70 (17.8)                     | 0.33 (8.5)                    | 10          | 33          | 330              | 31             | 10,000         |
| PEL-10-Y1-5   | Polyester                | Silver      | 0.70 (17.8)               | 0.50 (12.7)                | 0.70 (17.8)                     | 0.50 (12.7)                   | 10          | 22          | 220              | 23             | 5000           |
| PEL-10-Y2-5   | Polyester                | White       | 0.70 (17.8)               | 0.50 (12.7)                | 0.70 (17.8)                     | 0.50 (12.7)                   | 10          | 22          | 220              | 23             | 5000           |
| PEL-10-Y2Y-5  | Polyester                | Yellow      | 0.70 (17.8)               | 0.50 (12.7)                | 0.70 (17.8)                     | 0.50 (12.7)                   | 10          | 22          | 220              | 23             | 5000           |
| PEL-10-Y3M-5  | Polyester                | Matte Clear | 0.70 (17.8)               | 0.50 (12.7)                | 0.70 (17.8)                     | 0.50 (12.7)                   | 10          | 22          | 220              | 23             | 5000           |
| PEL-24-Y2Y-10 | Polyester                | Yellow      | 0.79 (20.0)               | 0.31 (8.0)                 | 0.79 (20.2)                     | 0.31 (8.0)                    | 9           | 35          | 315              | 32             | 10,000         |
| PEL-5-Y1-10   | Polyester                | Silver      | 0.80 (20.3)               | 0.33 (8.5)                 | 0.80 (20.3)                     | 0.33 (8.5)                    | 9           | 33          | 297              | 34             | 10,000         |
| PEL-5-Y2-10   | Polyester                | White       | 0.80 (20.3)               | 0.33 (8.5)                 | 0.80 (20.3)                     | 0.33 (8.5)                    | 9           | 33          | 297              | 34             | 10,000         |
| PEL-5-Y2Y-10  | Polyester                | Yellow      | 0.80 (20.3)               | 0.33 (8.5)                 | 0.80 (20.3)                     | 0.33 (8.5)                    | 9           | 33          | 297              | 34             | 10,000         |
| PEL-2-Y1-10   | Polyester                | Silver      | 1.00 (25.4)               | 0.25 (6.4)                 | 1.00 (25.4)                     | 0.25 (6.4)                    | 7           | 45          | 315              | 32             | 10,000         |
| PEL-2-Y2-10   | Polyester                | White       | 1.00 (25.4)               | 0.25 (6.4)                 | 1.00 (25.4)                     | 0.25 (6.4)                    | 7           | 45          | 315              | 32             | 10,000         |
| PEL-2-Y2Y-10  | Polyester                | Yellow      | 1.00 (25.4)               | 0.25 (6.4)                 | 1.00 (25.4)                     | 0.25 (6.4)                    | 7           | 45          | 315              | 32             | 10,000         |
| PEL-2-Y3M-10  | Polyester                | Matte Clear | 1.00 (25.4)               | 0.25 (6.4)                 | 1.00 (25.4)                     | 0.25 (6.4)                    | 7           | 45          | 315              | 32             | 10,000         |
| PEL-6-Y1-5    | Polyester                | Silver      | 1.00 (25.4)               | 0.33 (8.5)                 | 1.00 (25.4)                     | 0.33 (8.5)                    | 7           | 33          | 231              | 22             | 5000           |
| PEL-6-Y2-5    | Polyester                | White       | 1.00 (25.4)               | 0.33 (8.5)                 | 1.00 (25.4)                     | 0.33 (8.5)                    | 7           | 33          | 231              | 22             | 5000           |
| PEL-6-Y1C-5   | Tamper Evident Polyester | Silver      | 1.00 (25.4)               | 0.33 (8.5)                 | 1.00 (25.4)                     | 0.33 (8.5)                    | 7           | 33          | 231              | 22             | 5000           |
| PEL-11-Y1-5   | Polyester                | Silver      | 1.00 (25.4)               | 0.50 (12.7)                | 1.00 (25.4)                     | 0.50 (12.7)                   | 7           | 22          | 154              | 33             | 5000           |
| PEL-11-Y2-5   | Polyester                | White       | 1.00 (25.4)               | 0.50 (12.7)                | 1.00 (25.4)                     | 0.50 (12.7)                   | 7           | 22          | 154              | 33             | 5000           |
| PEL-11-Y2Y-5  | Polyester                | Yellow      | 1.00 (25.4)               | 0.50 (12.7)                | 1.00 (25.4)                     | 0.50 (12.7)                   | 7           | 22          | 154              | 33             | 5000           |
| PEL-11-Y1C-5  | Tamper Evident Polyester | Silver      | 1.00 (25.4)               | 0.50 (12.7)                | 1.00 (25.4)                     | 0.50 (12.7)                   | 7           | 22          | 154              | 33             | 5000           |

## Blank Labels by Size



### DIN A4 Sheet Format (8.26" x 11.69" / 210 mm x 297 mm)

| Part Number                                                                             | Material                 | Color       | Label Width A<br>In. (mm) | Label Length B<br>In. (mm) | Horizontal Repeat D<br>In. (mm) | Vertical Repeat E<br>In. (mm) | No. of Col. | No. of Rows | Labels Per Sheet | Sheets Per Pkg | Std. Pkg. Qty* |
|-----------------------------------------------------------------------------------------|--------------------------|-------------|---------------------------|----------------------------|---------------------------------|-------------------------------|-------------|-------------|------------------|----------------|----------------|
| PESS-SEL has Static Sensitive Warning printed on top half of label (see drawing below). |                          |             |                           |                            |                                 |                               |             |             |                  |                |                |
| PESS-SEL                                                                                | Polyester                | Yellow      | 1.00 (25.4)               | 0.50 (12.7)                | 1.00 (25.4)                     | 0.50 (12.7)                   | 7           | 22          | 154              | 33             | 2500           |
| PEL-3-Y1-5                                                                              | Polyester                | Silver      | 1.44 (36.5)               | 0.25 (6.4)                 | 1.44 (36.5)                     | 0.25 (6.4)                    | 5           | 45          | 225              | 23             | 5000           |
| PEL-3-Y2-5                                                                              | Polyester                | White       | 1.44 (36.5)               | 0.25 (6.4)                 | 1.44 (36.5)                     | 0.25 (6.4)                    | 5           | 45          | 225              | 23             | 5000           |
| PEL-3-Y1C-5                                                                             | Tamper Evident Polyester | Silver      | 1.44 (36.5)               | 0.25 (6.4)                 | 1.44 (36.5)                     | 0.25 (6.4)                    | 5           | 45          | 225              | 23             | 5000           |
| PEL-7-Y1-5                                                                              | Polyester                | Silver      | 1.50 (38.1)               | 0.33 (8.5)                 | 1.50 (38.1)                     | 0.33 (8.5)                    | 5           | 33          | 165              | 31             | 5000           |
| PEL-7-Y2-5                                                                              | Polyester                | White       | 1.50 (38.1)               | 0.33 (8.5)                 | 1.50 (38.1)                     | 0.33 (8.5)                    | 5           | 33          | 165              | 31             | 5000           |
| PEL-7-Y2Y-5                                                                             | Polyester                | Yellow      | 1.50 (38.1)               | 0.33 (8.5)                 | 1.50 (38.1)                     | 0.33 (8.5)                    | 5           | 33          | 165              | 31             | 5000           |
| PEL-7-Y3M-5                                                                             | Polyester                | Matte Clear | 1.50 (38.1)               | 0.33 (8.5)                 | 1.50 (38.1)                     | 0.33 (8.5)                    | 5           | 33          | 165              | 31             | 5000           |
| PEL-12-Y1-2.5                                                                           | Polyester                | Silver      | 1.50 (38.1)               | 0.50 (12.7)                | 1.50 (38.1)                     | 0.50 (12.7)                   | 5           | 22          | 110              | 23             | 2500           |
| PEL-12-Y2-2.5                                                                           | Polyester                | White       | 1.50 (38.1)               | 0.50 (12.7)                | 1.50 (38.1)                     | 0.50 (12.7)                   | 5           | 22          | 110              | 23             | 2500           |
| PEL-12-Y2Y-2.5                                                                          | Polyester                | Yellow      | 1.50 (38.1)               | 0.50 (12.7)                | 1.50 (38.1)                     | 0.50 (12.7)                   | 5           | 22          | 110              | 23             | 2500           |
| PEL-8-Y1-2.5                                                                            | Polyester                | Silver      | 2.00 (50.8)               | 0.33 (8.5)                 | 2.00 (50.8)                     | 0.33 (8.5)                    | 3           | 33          | 99               | 26             | 2500           |
| PEL-8-Y2-2.5                                                                            | Polyester                | White       | 2.00 (50.8)               | 0.33 (8.5)                 | 2.00 (50.8)                     | 0.33 (8.5)                    | 3           | 33          | 99               | 26             | 2500           |
| PEL-8-Y1C-2.5                                                                           | Tamper Evident Polyester | Silver      | 2.00 (50.8)               | 0.33 (8.5)                 | 2.00 (50.8)                     | 0.33 (8.5)                    | 3           | 33          | 99               | 26             | 2500           |
| PEL-13-Y1-2.5                                                                           | Polyester                | Silver      | 2.00 (50.8)               | 0.50 (12.7)                | 2.00 (50.8)                     | 0.50 (12.7)                   | 3           | 22          | 66               | 38             | 2500           |
| PEL-13-Y2-2.5                                                                           | Polyester                | White       | 2.00 (50.8)               | 0.50 (12.7)                | 2.00 (50.8)                     | 0.50 (12.7)                   | 3           | 22          | 66               | 38             | 2500           |
| PEL-14-Y1-1                                                                             | Polyester                | Silver      | 2.00 (50.8)               | 0.83 (21.1)                | 2.00 (50.8)                     | 0.83 (21.1)                   | 3           | 13          | 39               | 26             | 1000           |
| PEL-14-Y2-1                                                                             | Polyester                | White       | 2.00 (50.8)               | 0.83 (21.1)                | 2.00 (50.8)                     | 0.83 (21.1)                   | 3           | 13          | 39               | 26             | 1000           |
| PEL-15-Y1-1                                                                             | Polyester                | Silver      | 2.00 (50.8)               | 1.00 (25.4)                | 2.00 (50.8)                     | 1.00 (25.4)                   | 3           | 11          | 33               | 31             | 1000           |
| PEL-15-Y2-1                                                                             | Polyester                | White       | 2.00 (50.8)               | 1.00 (25.4)                | 2.00 (50.8)                     | 1.00 (25.4)                   | 3           | 11          | 33               | 31             | 1000           |
| PEL-15-Y2Y-1                                                                            | Polyester                | Yellow      | 2.00 (50.8)               | 1.00 (25.4)                | 2.00 (50.8)                     | 1.00 (25.4)                   | 3           | 11          | 33               | 31             | 1000           |
| PEL-15-Y1C-1                                                                            | Tamper Evident Polyester | Silver      | 2.00 (50.8)               | 1.00 (25.4)                | 2.00 (50.8)                     | 1.00 (25.4)                   | 3           | 11          | 33               | 31             | 1000           |
| PEL-16-Y1-0.5                                                                           | Polyester                | Silver      | 2.50 (63.5)               | 1.33 (33.8)                | 2.50 (63.5)                     | 1.33 (33.9)                   | 3           | 8           | 24               | 21             | 500            |
| PEL-16-Y2-0.5                                                                           | Polyester                | White       | 2.50 (63.5)               | 1.33 (33.8)                | 2.50 (63.5)                     | 1.33 (33.9)                   | 3           | 8           | 24               | 21             | 500            |
| PEL-16-Y1C-0.5                                                                          | Tamper Evident Polyester | Silver      | 2.50 (63.5)               | 1.33 (33.8)                | 2.50 (63.5)                     | 1.33 (33.9)                   | 3           | 8           | 24               | 21             | 500            |
| PEL-A4-Y1-25                                                                            | Polyester                | Silver      | 8.27 (210.0)              | 11.69 (297.0)              | —                               | —                             | 1           | 1           | 1                | 25             | 25             |
| PEL-A4-Y2-25                                                                            | Polyester                | White       | 8.27 (210.0)              | 11.69 (297.0)              | —                               | —                             | 1           | 1           | 1                | 25             | 25             |
| PEL-A4-Y2Y-25                                                                           | Polyester                | Yellow      | 8.27 (210.0)              | 11.69 (297.0)              | —                               | —                             | 1           | 1           | 1                | 25             | 25             |
| PEL-A4-Y3-25                                                                            | Polyester                | Clear       | 8.27 (210.0)              | 11.69 (297.0)              | —                               | —                             | 1           | 1           | 1                | 25             | 25             |
| PEL-A4-Y3M-25                                                                           | Polyester                | Matte Clear | 8.27 (210.0)              | 11.69 (297.0)              | —                               | —                             | 1           | 1           | 1                | 25             | 25             |
| PEL-A4-Y1C-25                                                                           | Tamper Evident Polyester | Silver      | 8.27 (210.0)              | 11.69 (297.0)              | —                               | —                             | 1           | 1           | 1                | 25             | 25             |

PESS-SEL

