

NEMA Rated LED Signal Towers

NEMA Type 4, 4X, 13

The NEMA standard is dedicated to the manufacture of effective, safe products.



**LCE
Series**



**LME
Series**



**LU7
Series**

For Packaging Applications and more....
(see back for product details)



LCE Series

ø40mm
(1.57 in)



- ◆ Direct mount models.
- ◆ Colors are available in Red, Yellow, Green, Blue, and Clear.
- ◆ LED modules are stackable and interchangeable after purchase (up to 5 LED modules).
- ◆ UL component recognized, CE compliant, and meets IP-65 standards (IP-54 for FB versions).
- ◆ NPN and PNP open collector transistor compatible (24V type), and NPN open collector (90~250V type).
- ◆ FB types: Two selectable single-tone, intermittent alarms with adjustable volume to 85dB (at 1m), and light has 60 flashes per minute.



IP-65*

*FB types: IP-54

AC/DC24V
AC90~250V

- ◆ Modular, direct mount design.
- ◆ Colors are available in Red, Yellow, Green, Blue, and Clear.
- ◆ LED modules are stackable and interchangeable after purchase (up to 5 LED modules).
- ◆ UL component recognized, CE compliant, and meets IP-65 standards.
- ◆ NPN and PNP open collector transistor compatible (24V type), and NPN collector (90~250V type).
- ◆ FB types: Two selectable single-tone, intermittent alarms with adjustable volume to 90dB (at 1m) and light has 60 flashes per minute.



IP-65

DC24V
AC90~250V

LU7 Series

ø70mm
(2.76 in)



LME Series

ø60mm
(2.36 in)



- ◆ Direct and (Aluminum) Pole mount models available.
- ◆ Colors are available in Red, Yellow, Green, Blue, and Clear.
- ◆ LED modules are stackable and interchangeable after purchase, up to 5 LED modules (New shaft purchase is required).
- ◆ UL component recognized, CE compliant, and meets IP-65 standards (FB type: IP-54).
- ◆ NPN and PNP open collector transistor compatible (24V type), and NPN open collector (120V type).
- ◆ FB types: Two selectable single-tone, intermittent alarms with adjustable volume to 90dB (at 1m) and light has 60 flashes per minute.
- ◆ Pole mount types include 300mm (11-3/4 in) aluminum pole and plastic topmount bracket.



IP-65*

*FB types: IP-54

AC/DC24V
AC120V

PATLITE

PATLITE (U.S.A.) Corporation

3860 Del Amo Blvd, Suite 401
Torrance, CA 90503

Tel: (310) 214-3222 / (888) 214-2580

Fax: (310) 214-9999

Chicago Office: Tel (847) 781-6999

www.patlite.com

e-mail: sales@patlite.com