




FEATURES:

- Cross Stacking Banana Plugs
- Mates to Model #1581, 2854 or any standard Banana jack.
- Ideal for providing jumpers or chassis boxes.

MATERIALS:

Conn: Banana Plug

Material: Spring, Beryllium Copper Berylco 25, per QQ-C-533, Cond. H.T.

Plug Body: Brass, per QQ-B-626, Alloy 360, ½ Hard.

Finish: Nickel plated per QQ-N-290 Class 2 (.0002/.0003).

Insulation: Polypropylene molded to plug body and wire.

Color: Matches color of wire.

Marking: "POMONA ELECTRONICS, CALIF."

Wire: 18 AWG, stranding 65 x 36 t.c., PVC insulated.

Marking: "POMONA 1440-XX"

RATINGS: (Entire Assembly)

Operating Voltage: Hand-held testing: 30VAC/60VDC Max.

Hands free testing in controlled voltage environments: 5000 WVDC Max.

Operating Temperature: +55°C. (+131°) Max.

Current: 15 Amperes Cont. Contact Res.: Less than .001Ohms per Banana Plug

ORDERING INFORMATION: Model 1440-XX-*

XX – Cable Lengths, Standard Lengths: 12" (305), 18" (457), 24" (610), 36" (914), 48" (1219) & 60" (1524).

*= Color, -0 Black, -2 Red. Ordering Example: 1440-60-2 Indicates 60" in length, color is Red.

Additional lengths and colors can be quoted upon request.

All dimensions are in inches. Tolerances (except noted): .xx = ±.02" (.51 mm), .xxx = ± .005" (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies. Made in USA

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Pomona:

[1440-48-0](#) [1440-48-2](#) [1440-12-0](#) [1440-12-2](#) [1440-18-2](#) [1440-18-0](#) [1440-60-2](#) [1440-60-0](#) [1440-24-0](#) [1440-24-2](#)
[1440-36-2](#) [1440-36-0](#)